

MVHB-220 series

HAND LEVER VALVE



Mindman

Specification

Model	MVHB-220-4TV MVHB-220-4TV-SP	MVHB-220-4TV* MVHB-220-4TV*-SP
Bore No. (Port size)	8A (1/4)	
No. of port	5	
No. of position	2	3
Medium	Air	
Operating pressure range	0~0.8 MPa	
Effective orifice	18 mm ²	16 mm ²
Ambient temperature	-5~+60°C (No freezing)	
Weight	193 g	234 g



Technical data



Caution for safety
(Read before installing)



Order example

MVHB - 220 - 4TVC - SP - M - □ - G

MODEL

BODY
WIDTH

4: 4way (5 port)

VALVE
TYPE

Blank: 5/2
C: Closed center (5/3)
P: Pressure center (5/3)
R: Exhaust center (5/3)

SPRING
RETURN

DUST COVER
MATERIAL
Blank: NBR
E: EPDM

Blank: Standard type
M: Panel mounting

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

*1. NBR: Good oil resistance and abrasion resistance, not suitable for using in polar solvents.

EPDM: Excellent water resistance and chemical resistance, not suitable for using oil place.

*2. Suitability of material

Panel mounting style

