



Technical data



Caution for safety
(Read before installing)



Specification

Model	MVHD-220-3P	MVHD-220-4P
Bore No.	8A	6A, 8A
Port size	1/4	1/8, 1/4
No. of port	3	5
No. of position	2	
Medium	Air	
Operating pressure range	0~0.8 MPa	
Effective orifice	18 mm ²	
Ambient temperature	-5~+50°C (No freezing)	
Weight	151 g	170 g

Order example

MVHD – 220 – 4P – NC – □ – SP – G

MODEL

BODY WIDTH

ACTUATOR TYPE

NC: Normally closed
NO: Normally open
 (Only for 3P)

BORE SIZE

Blank: 1/4
6A: 1/8 (Only for 4P)

SPRING RETURN

PORT THREAD

Blank: Rc thread
G: G thread
NPT: NPT thread

3: 3way (3 port)
4: 4way (5 port)

P: Push-pull

Panel mounting hole

