MVSC series Features



SOLENOID VALVE

Electric Connection

DIN terminal

Product feature

Contact spring

Contact spring makes wiring quick and easy. Also, it prevents wire damage.

Terminal material

Material of terminal housing is PA6 which has good chemical resistance and weather resistance.

Manual override

Drop-shaped manual override is easy for testing with one push or spin.

Applying SurTec 650

Nonoxidizable for 336hrs under neutral salt spray test.

No leakage

All products go through leakage test according to JIS regulation.



DISK seal and U-packing (NBR)

High wear resistance, wide working temperature $-30 \sim +100$ °C, excellent sealability.

Coil

Low power consumption, DC24V power 2W

Insulation	Coil	F class/ 155°C
class	Copper wire	H class/ 180°C

Plunger material

Resulfurized stainless steel with 17% chromium and 1.5% silicon. Provide a very low coercive magnetic field and a very high permeability.

Product specification

Effective orifice	18 mm ²
Max. operating perssure	0.8 MPa (8 kgf/cm ²)
Ambient temperature	-5 ~ +50°C (No freezing)
Lifetime	50 million cycles under normal service condition



