



## Drill Bits

### Double-Ended Drill Bits

Viking Double-Ended Drill Bits are constructed from high-speed steel (HSS) with a black oxide finish and a round shank for durability and reliable performance. Featuring a 135° split point, these heavy-duty twin-end drills are designed for efficient penetration and reduced walking on contact. Well-suited for drilling thin sheet metal, and they are particularly effective in applications such as drilling holes for components on an enclosure backplate. These shorter twin-ended drills are great for production work, saving time and money by having cutting points on both ends.

### For Use On:

- Aluminum
- Brass
- Plastic
- Steel
- Bronze
- Cast iron



[28570](#)

### Double-Ended Drill Bits - Split Point

Part Number	Pcs /Pkg	Price	Drill Size (A) (in)	Flute Length (B) (in)	Overall Length (C)	Point Angle (D)	Finish	Shank Type
<a href="#">28480</a>	10	\$21.00	7/64in	5/8in	1.9in (48mm)	135 degrees	Black oxide	round
<a href="#">28490</a>	10	\$21.75	1/8in	5/8in	1.9in (48mm)			
<a href="#">28500</a>	10	\$25.50	9/64in	5/8in	2in (51mm)			
<a href="#">28510</a>	10	\$27.00	5/32in	5/8in	2.1in (53mm)			
<a href="#">28530</a>	10	\$30.00	3/16in	5/8in	2.3in (58mm)			
<a href="#">28550</a>	10	\$37.75	7/32in	3/4in	2.6in (66mm)			
<a href="#">28570</a>	10	\$42.25	1/4in	13/16in	2.7in (69mm)			