

NEMA 1 Corner Mount Wiring Trough with Knockouts



S8824AT

Applications

S-AT Series Corner Troughs provide new options for wire distribution installations. Mount in any corner, taking up less room on the wall. Makes conduit installation faster by eliminating the need for conduit bending. Angled screw cover provides wide access for easier wire pulling during installation. Protects wiring in commercial and industrial applications.

Construction

- Trough and cover fabricated from 16-gauge carbon steel
- Drip shield top and smooth seamless sides, front and back, prevent rain, snow and sleet from entering the enclosure
- Embossed mounting holes are conveniently located on the back
- A slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are provided on front and bottom of enclosure

Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 870 [File E32576]
- Meets NEMA/EEMAC 1 requirements

NEMA 1 Corner Mount Wiring Trough with Knockouts

Part Number	Price	Dimensions HxDxL	Drawing Link
S6624AT	\$190.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
S6636AT	\$235.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
S6648AT	\$285.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
S8824AT	\$209.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
S8836AT	\$238.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
S8848AT	\$312.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF

Note: Dimensions in inches (millimeters).