

WCT Series NEMA 1 and 3R Screw-Cover Wall Mount



WCT Series NEMA 1 and 3R Screw-Cover Wall Mount			
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
WCT242412	\$216.00	14/14	24.07 x 24.50 x 12.45 [611 x 622 x 316]
WCT303012	\$282.00	12/12	30.09 x 30.50 x 12.47 [764 x 775 x 317]
WCT363012	\$379.00		36.09 x 30.50 x 12.47 [917 x 775 x 317]
WCT363612	\$415.00		36.09 x 36.50 x 12.47 [917 x 927 x 317]
WCT483616	\$668.00		48.09 x 36.50 x 16.47 [1221 x 927 x 418]

*Note: Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.*

Applications

Designed for use as transformer housing, junction boxes, and service boxes.

Construction

- Drip shield top and smooth seamless sides and front
- A slip-on removable cover is securely fastened with plated screws located along bottom edge
- No gasketing is required
- Mounting holes on back of cabinet
- Door handles provided
- Hasp for padlocking and provisions for meter seal are provided
- For removal of cover, move downward, then outward

Finish

- ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 50, Types 1 & 3R [UL file E23553]
- CSA Certified, Type 1 & 3R [CSA file LL66078]
- NEMA/EEMAC Type 1 & 3R




Enclosure Shipping Schedule				
Same day	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.