

# Wera Ratcheting T-Handles

## Ratcheting T-Handles

Wera's ratcheting T-handles is an integrated ratchet with fine tooththing (80 teeth/return angle 4.5°) that eases and accelerates screwdriving without having to reposition the tool. The ratchet mechanism completely embedded in the handle ensures very handy and comfortable work. With reversing lever for comfortable clockwise/counterclockwise direction change in one-hand operation. The ergonomic shape of the handle fills the ball of the hand well, the fingers lie securely in the softly rounded recessed grips. The whole hand comes into contact with the handle, friction loss between hand and handle is avoided.

### Features



- The integrated ratchet with fine tooththing ensures fast and safe working
- Reversing lever for comfortable clockwise/counterclockwise direction change
- Convenient working thanks to the ratchet mechanism fully embedded in the handle
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working
- Fast-rotating sleeve for extremely high working speed
- 1/4" socket mounting with secure ball lock or bitholder with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3



Ratcheting T-Handles						
Part Number	Part Image	Drive Size	Fastening Size	Shaft Length	Handle Type	Price
<a href="#"><u>05023460001</u></a>		1/4in	n/a	1.8in (45mm)	Ergonomic t-handle	\$66.00
<a href="#"><u>05023461001</u></a>		n/a	1/4in			\$66.00

# Wera Ratcheting T-Handles

## Ratcheting T-Handles - Cont'd

Ratcheting T-Handle Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<a href="#"><u>05023471001</u></a>	17		⊕ Phillips	#2 #3	(1) 1/4in t-handle ratchet bitholding screwdriver with Rapidaptor quick-release chuck, (16) 3.5 driver bits (Phillips: #2, #3 Pozidriv: #2, #3, torx: T10, T15, T20, T25, T30, T40, hex: 3mm, 4mm, 5mm, 6mm, 8mm, slotted: 5.5mm), (1) textile storage pouch	\$135.00
			⊕ Pozidriv	#2 #3		
			⊕ Torx	T10 T15 T20 T25 T30 T40		
			⊕ Hex	3.0mm 4.0mm 5.0mm 6.0mm 8.0mm		
			⊕ Slotted	5.5mm		
<a href="#"><u>05057473001</u></a>	17		⊕ Phillips	#2 #3	(1) 1/4in t-handle ratchet bitholding screwdriver with Rapidaptor quick-release chuck, (16) 3.5 driver bits (Phillips: #2, #3, torx: T10, T15, T20, T25, T30, T40, hex: 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, square: #2, #3, slotted: 5.5mm), (1) textile storage pouch	\$135.00
			⊕ Pozidriv	#2 #3		
			⊕ Torx	T10 T15 T20 T25 T30 T40		
			⊕ Hex	1/8in 5/32in 3/16in 7/32in 1/4in		
			⊕ Slotted	5.5mm		