Wera Bit Drivers, Bits, & Adapters

Tool-Check Tool Sets

Wera Tool-Check systems deliver very compact tool organization for manual and machine use. Green locking elements secure tools during transport, preventing movement and loss. The 1/4" bit ratchet features drop-forged solid steel construction with fine 60-tooth mechanism for a 6° return angle, enabling precise work in confined spaces. Ergonomically shaped ratchet head with easy clockwise/counterclockwise switching ensures comfortable operation. Zyklop sockets include ball stop grooves and rear-end knurling for secure retention and manual screwdriving control. Take it easy tool finder system uses color coding by size and profile for quick tool identification. BiTorsion bits feature integrated torsion zones that prevent premature breakage during high-torque applications. The 870/1 adapter enables 1/4" socket compatibility for all Tool-Check systems. Matte chrome-plated chrome-vanadium construction provides corrosion resistance and durability.

Features

- Green locking elements secure tools during transport and prevent loss
- Drop-forged 60-tooth bit ratchet with 6° return angle for precise work
- Ergonomically shaped ratchet head with easy clockwise/ counterclockwise switching
- BiTorsion bits feature torsion zones that prevent premature breakage
- Take it easy tool finder color coding for quick tool identification
- Zyklop sockets with ball stop grooves for secure retention
- Matte chrome-plated chrome-vanadium construction for corrosion resistance
- Includes 870/1 adapter for 1/4" socket compatibility
- Super-compact storage maximizes space efficiency
- Available in metric and imperial configurations

Lockable Storage

05049055001



Socket and Driver Bit Set





Rapidaptor Quick-Release System



Take-It-Easy Tool Finder

Great for Confined Spaces

Wera Bit Drivers, Bits, & Adapters

SWITCH | RAPIDAPTOR TECHNOLOGY | 6° FINE TOOTH | FULL STEEL | SPEED | LIMITED LIFETIME WARRANTY

Tool-Check PLUS Socket and Driver Bit Sets

05049055001

Type		Bit Size
Bitholding screwdriver		1/4in x 87mm
Zyklop mini bit ratchet		1/4in x 78mm
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
Phillips bit	Phillips bit, 25mm long	(2) #1, (3) #2, #3
Torx bit	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
Tamperproof Torx bit	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
Slotted bit	Slotted bit 25mm long	1.0 x 5.5mm
Hex-Plus bit	Hex-Plus bit 25mm long	3mm, 4mm, 5mm, 6mm, 8mm
6-point socket	6-point socket	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm

Description	Price
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.	$150.00

Tool-Check PLUS Socket and Driver Bit Sets

05049060001

Type		Bit Size
Bitholding screwdriver		1/4in x 78mm
Zyklop mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
Phillips bit	Phillips bit, 25mm long	(2) #1, (3) #2, #3
Slotted bit	Slotted bit 25mm long	1.0 x 5.5mm
Torx bit	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
Tamperproof Torx bit	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
Square bit	Square bit 25mm long	#1, (3) #2, #3
Hex-Plus bit	Hex-Plus bit 25mm long	3/32in, 1/8in, 5/32in, 3/16in, 1/4in
6-point socket	6-point socket	3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in

Description	Price
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, imperial, compact Tool-Check storage system.	$150.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.

Wera Bit Drivers, Bits, & Adapters

SWITCH | RAPIDAPTOR TECHNOLOGY | 6° FINE TOOTH | FULL STEEL | SPEED | LIMITED LIFETIME WARRANTY

Tool-Check PLUS Socket and Driver Bit Sets

05056490001

Product Image	*Description*	*Price*
	Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.	Retired

Type		*Bit Size*
Bitholding screwdriver		1/4in x 78mm
Zyklop mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
Phillips	Phillips bit, 25mm long	(2) #1, (3) #2, #3
Pozidriv	Pozidriv bit, 25mm long	#1, (3) #2, #3
Torx	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
Tamperproof Torx	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
Slotted	Slotted bit 25mm long	1.0 x 5.5mm
Hex-Plus	Hex-Plus bit 25mm long	3.0. 4.0, 5.0, 6.0, 8.0mm
6-point	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm

Tool-Check Socket and Driver Bit Sets

05056491001

Product Image	*Description*	*Price*
	Wera Tool-Check standard socket and driver bit set, ratcheting, Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex, 39 pieces, 1in bit length, 1/4in drive, imperial.	Retired

Type		*Bit Size*
Bitholding screwdriver		1/4in x 78mm
Zyklop mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
Phillips	Phillips bit, 25mm long	(2) #1, (3) #2, #3
Torx	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
Tamperproof Torx	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
Slotted	Slotted bit 25mm long	1.0 x 5.5mm
Hex-Plus	Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
6-point	6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.

Wera Bit Drivers, Bits, & Adapters

SWITCH | RAPIDAPTOR TECHNOLOGY | 6° FINE TOOTH | FULL STEEL | SPEED | LIMITED LIFETIME WARRANTY

Tool-Check Socket and Driver Bit Sets

05049050001

Product Image	*Description*	*Price*
	Wera Tool-Check standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, external hex, internal hex, slotted and square, 38 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.	$143.00

Type		*Bit Size*
Zyklop Mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
	Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Slotted bit 25mm long	1.0 x 5.5mm
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Pozidriv bit, 25mm long	#1, (3) #2, #3
	Hex-Plus bit 25mm long	3mm, 4mm, 5mm, 6mm, 8mm
	6-point socket	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm

Tool-Check Socket and Driver Bit Sets

05073220055

Product Image	*Description*	*Price*
	Wera Tool-Check driver bit and socket set, ratcheting, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.	Retired

Type		*Bit Size*
Zyklop Mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm
	Slotted bit 25mm long	1.0 x 5.5mm
	Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm
	Phillips bit, 25mm long	(2) P#1, (3) #2, #3
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Pozidriv bit 25mm long	#1, (3) #2, #3
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.

Wera Bit Drivers, Bits, & Adapters

SWITCH | RAPIDAPTOR TECHNOLOGY | 6° FINE TOOTH | FULL STEEL | SPEED | LIMITED LIFETIME WARRANTY

Bit-Check Socket and Driver Bit Sets

TW-DB-SET-28R

Product Image	*Type*		*Bit Size*
	Zyklop Mini bit ratchet		1/4in
	Rapidaptor bit holder		1/4in x 50mm
	Socket adaptor		1/4in x 25mm
	Phillips bit, 25mm long		(2) PH1, (3) PH2, PH3
	Torx bit, 25mm long		T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit, 25mm long		T10, T15, T20, T25, T30
	Slotted bit 25mm long		1.0 x 5.5mm
	Hex-Plus bit 25mm long		3/32, 1/8, 5/32, 3/16, 1/4in
	Square bit 25mm long		#1, (3) #2, #3

Description	*Price*
Wera Bit-Check standard driver bit set, ratcheting, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.	$93.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.