



# Wera Torque Screwdrivers

## Torque Screwdrivers


Wera torque tools permit torque-controlled tightening to prevent damage to screws or work pieces and to guarantee the safety of screw connection. This makes labor-intensive drilling, re-tapping and production downtimes a thing of the past.

## Features

- Simple setting of the required torque by hand. Easy-to-read scale value.
- Measurement accuracy is  $\pm 6\%$  in accordance with the standard EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.
- All Wera torque tools are supplied with a calibration certificate.



Torque Screwdrivers			
Part Number	Part Image	Description	Price
<a href="#"><u>TW-TD-2-11</u></a>		Wera Kraftform 7400 series adjustable torque screwdriver, 2.5-11.5 in-lb set point, numerical torque value, 1/4in hex socket drive. Driver bits not included. Manufacturer part number 074710.	\$96.00
<a href="#"><u>TW-TD-11-29</u></a>		Wera Kraftform 7400 series adjustable torque screwdriver, 11-29 in-lb set point, numerical torque value, 1/4in hex socket drive. Driver bits not included. Manufacturer part number 074711.	\$96.00
<a href="#"><u>05074712055</u></a>		Wera Kraftform 7400 series adjustable torque screwdriver, 25-55 in-lb set point, numerical torque value, 1/4in hex socket drive. Driver bits not included. Manufacturer part number 074712.	\$146.00



Torque Screwdriver Sets			
Part Number	Part Image	Description	Price
<a href="#"><u>05350451055</u></a>		Wera Kraftform 7400 series adjustable torque screwdriver set, 1/4in hex socket drive. 27 pieces. Includes sturdy plastic case. Manufacturer part number 350451.	\$391.00

Note: Screwdriver bits are warranted against manufacturer defect only.

## 05350451055 Contents

	Torque screwdriver 2.5-11.5 in-lb	
	Torque screwdriver 11-29 in-lb	
	25-55 in-lb pistol grip torque screwdriver	
	Hex-Plus bits, 25mm long	2, 2.5, 3, 4, 5, 6
	Torx® bits, 25mm long	TX6, TX7, TX8, TX9, TX10, TX15, TX20, TX25, TX30
	Torx® Plus bits, 25mm long	TX6, TX7, TX8, TX9, TX10, TX15, TX20, TX25, TX30