



Screwdrivers for Hexagon Socket Screws

L-Keys

Hex-Plus L-keys for hexagon socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but they must not twist to any great extent, or shear off, to minimize the risk of injuries. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection and refined hardening technologies delivers maximum safety at work.

L-Keys for Hexagon Socket Screws		
Part Number	Description	Price Each
TW-HK-SET-MM	Wera hex key set, nine-piece, includes metric sizes 1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10 mm. Holder included. Manufacturer part number 022086.	\$12.00
TW-HK-SET-STD	Wera hex key set, 13-piece, includes inch sizes 0.05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16 and 3/8 inch. Holder included. Manufacturer part number 022171.	\$21.00
05022089055	Wera hex key set, nine-piece, multicolor, L-key hexdriver set. Includes metric sizes 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm. Two-component clip included. Manufacturer part number 022089.	\$44.50
05022639055	Wera hex key set, nine-piece, multicolor, L-key hexdriver set. Includes imperial sizes 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, and 3/8 inch. Includes durable cloth pouch. Manufacturer part number 022639.	\$44.50

Note: L-keys are warranted against manufacturer defect only.



TW-HK-SET-MM



TW-HK-SET-STD



05022089055



05022639055

Hexagon ball tip

The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

T-Handle Hex Drivers

The T-handle is useful whenever higher tightening or loosening torque needs to be applied. The exclusive use of hard material in combination with the large contact surface area in the hand ensures an efficient, positive transfer of power.

T-Handle Hex Drivers		
Part Number	Description	Price Each
05344547001	Wera T-handle hexdriver set, 8 pieces. Includes metric sizes 2, 2.5, 3, 4, 5, 6, 8, and 10 mm. Manufacturer part number 344547.	\$47.00
05344548001	Wera T-handle hexdriver set, 10 pieces. Includes imperial sizes 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, and 3/8 inch. Manufacturer part number 344548.	\$61.00



05344547001




05344548001



Wera Wrenches
BE A TOOL REBEL



Joker - Does it all. Better.



Practical holding function

The Joker's holding function means that nuts and bolts can be directly and reliably positioned where they are needed. The metal jaw plate holds nuts securely for one hand placement reducing the risk of dropping.




Limit Stop for faster assembly

Joker's limit stop plate keeps the wrench from slipping off of the bolt head or nut preventing constant repositioning of the wrench.



Safer due to anti-slip effect

The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts – it's a perfect fit. The exchangeable, hardened metal gripping plate in the Joker's mouth literally bites itself into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.



Small return angle

Conventional open-end wrenches have a 60° return angle. The Joker works twice as fast having a 30° return angle with a double hex design. This, along with the Joker's straight head eliminate turning the wrench over. The fine 80 tooth ratchet mechanism in the box-end wrench provides even greater flexibility working in confined spaces.