

# WERMA SIGNALTECHNIK Optical Signal Devices

## 57/58mm Base Mount Beacons

### Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon model
- Base mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included on incandescent models
- 2-year warranty



### 200, 201 and 202 Series Beacons Technical Specifications

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
<b>35.5 mm Base Mount</b>													
<a href="#">20010000</a>	\$17.00	Red	<a href="#">PDF</a>	Incandescent Permanent Light 57mm	12-240 V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		50 [1.76]		
<a href="#">20020000</a>	\$17.00	Green	<a href="#">PDF</a>										
<a href="#">20030000</a>	\$17.00	Yellow	<a href="#">PDF</a>										
<a href="#">20040000</a>	\$17.00	Clear	<a href="#">PDF</a>										
<a href="#">20050000</a>	\$17.00	Blue	<a href="#">PDF</a>										
<a href="#">20110067</a>	\$78.00	Red	<a href="#">PDF</a>	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap Polyamide base	66 [2.33]	Up to 2.5 mm <sup>2</sup> Screwless CAGE CLAMP® - technology (8-14 AWG)	cULus file E164155, CE, RoHS
<a href="#">20120067</a>	\$78.00	Green	<a href="#">PDF</a>										
<a href="#">20130067</a>	\$78.00	Yellow	<a href="#">PDF</a>										
<a href="#">20140067</a>	\$109.00	Clear	<a href="#">PDF</a>										
<a href="#">20150067</a>	\$119.00	Blue	<a href="#">PDF</a>										
<a href="#">20110075</a>	\$62.00	Red	<a href="#">PDF</a>		24V AC/DC	< 45mA							
<a href="#">20120075</a>	\$62.00	Green	<a href="#">PDF</a>										
<a href="#">20130075</a>	\$62.00	Yellow	<a href="#">PDF</a>										
<a href="#">20140075</a>	\$123.00	Clear	<a href="#">PDF</a>										
<a href="#">20150075</a>	\$123.00	Blue	<a href="#">PDF</a>										
<a href="#">20210055</a>	\$100.00	Red	<a href="#">PDF</a>	Xenon Flashing Light (0.75 Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100mA	-		4,000,000 flashes		82 [2.89]		
<a href="#">20220055</a>	\$106.00	Green	<a href="#">PDF</a>										
<a href="#">20230055</a>	\$100.00	Yellow	<a href="#">PDF</a>										
<a href="#">20240055</a>	\$106.00	Clear	<a href="#">PDF</a>										
<a href="#">20250055</a>	\$106.00	Blue	<a href="#">PDF</a>										
<a href="#">20210067</a>	\$100.00	Red	<a href="#">PDF</a>		115VAC	< 20mA							
<a href="#">20220067</a>	\$106.00	Green	<a href="#">PDF</a>										
<a href="#">20230067</a>	\$100.00	Yellow	<a href="#">PDF</a>										
<a href="#">20240067</a>	\$106.00	Clear	<a href="#">PDF</a>										
<a href="#">20250067</a>	\$106.00	Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



Bulbs for Incandescent Permanent Optical Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95584035</a>	\$8.25	Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h
<a href="#">95584038</a>	\$8.25			230VAC	
<a href="#">95584057</a>	\$8.25			115VAC	



# Optical Signal Devices

## Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
<b>Installation Beacon Accessories</b>						
<a href="#">97581201</a>	\$14.50	<a href="#">PDF</a>	Tube adapter for beacons with 37mm (PG29) mounting installation. Find tube adapter accessories in WERMA Stack light catalog section.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.00	<a href="#">PDF</a>	Surface mounting base for beacons with 37mm (PG29) mounting installation		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$44.00	<a href="#">PDF</a>	Surface mounting enclosure for 1 beacon with 37mm (PG29) mounting installation		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$61.00	<a href="#">PDF</a>	Surface mounting enclosure for 2 beacons with 37mm (PG29) mounting installation			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$80.00	<a href="#">PDF</a>	Surface mounting enclosure for 3 beacons with 37mm (PG29) mounting installation			17g [0.6 oz]
<a href="#">97581522</a>	\$5.75	<a href="#">PDF</a>	Anti-twist washer for beacons with 37mm (PG29) mounting installation		304 Stainless steel	0.57 g [0.02 oz]
<b>Freestanding Beacon Accessories</b>						
<a href="#">96000001</a>	\$17.00	<a href="#">PDF</a>	Bracket for tube mounting - for use with for use with 219 and 209 series industrial signal beacons.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$20.50	<a href="#">PDF</a>	Plastic Base with integrated tube for WERMA industrial signal beacons- for use with 209 and 219 series beacons		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$5.75	<a href="#">PDF</a>	Cable gland for WERMA industrial signal beacons: M25x1.5, plastic - for use with 209 and 219 series industrial signal beacons		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$43.00	<a href="#">PDF</a>	Galvanized Wire Guard for WERMA industrial signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.00	<a href="#">PDF</a>	Plastic Bracket for wall mounting for use with WERMA signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Polycarbonate/ ABS blend	62g [2.19 oz]

