

# WERMA SIGNALTECHNIK Optical Signal Devices

## 57/58 mm Bracket Mount Beacons (Tall Lens)

### Features

- Beacon with tall lens
- Bracket mount installation
- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- 2-year warranty



### 213, 214, and 215 Series Beacons Technical Specifications

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
<b>25.8 mm (Bracket Mount)</b>													
<a href="#">21310000</a>	\$21.50	Red	<a href="#">PDF</a>	Incandescent Permanent Light 57mm	12-240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		61 [2.15]		
<a href="#">21320000</a>	\$21.50	Green	<a href="#">PDF</a>										
<a href="#">21330000</a>	\$21.50	Yellow	<a href="#">PDF</a>										
<a href="#">21340000</a>	\$21.50	Clear	<a href="#">PDF</a>										
<a href="#">21350000</a>	\$21.50	Blue	<a href="#">PDF</a>										
<a href="#">21410067</a>	\$89.00	Red	<a href="#">PDF</a>	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65 when mounted	up to 100,000h	Polycarbonate cap Polyamide base	78 [2.75]	2.5 mm <sup>2</sup> Screwless CAGE CLAMP® - technology (18-14 AWG)  Cable gland: m12 x1.5 Cable diameter: 3-6 mm	cULus file E164155, CE, RoHS
<a href="#">21420067</a>	\$89.00	Green	<a href="#">PDF</a>										
<a href="#">21430067</a>	\$89.00	Yellow	<a href="#">PDF</a>										
<a href="#">21440067</a>	\$133.00	Clear	<a href="#">PDF</a>										
<a href="#">21450067</a>	\$133.00	Blue	<a href="#">PDF</a>										
<a href="#">21410075</a>	\$75.00	Red	<a href="#">PDF</a>		24V AC/DC	< 45mA							
<a href="#">21420075</a>	\$75.00	Green	<a href="#">PDF</a>										
<a href="#">21430075</a>	\$75.00	Yellow	<a href="#">PDF</a>										
<a href="#">21440075</a>	\$119.00	Clear	<a href="#">PDF</a>										
<a href="#">21450075</a>	\$119.00	Blue	<a href="#">PDF</a>										
<a href="#">21510055</a>	\$109.00	Red	<a href="#">PDF</a>	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100mA	-	4,000,000 flashes		94 [3.32]			
<a href="#">21520055</a>	\$119.00	Green	<a href="#">PDF</a>										
<a href="#">21530055</a>	\$109.00	Yellow	<a href="#">PDF</a>										
<a href="#">21540055</a>	\$119.00	Clear	<a href="#">PDF</a>										
<a href="#">21550055</a>	\$119.00	Blue	<a href="#">PDF</a>										
<a href="#">21510067</a>	\$109.00	Red	<a href="#">PDF</a>		115VAC	< 20mA							
<a href="#">21520067</a>	\$119.00	Green	<a href="#">PDF</a>										
<a href="#">21530067</a>	\$109.00	Yellow	<a href="#">PDF</a>										
<a href="#">21540067</a>	\$119.00	Clear	<a href="#">PDF</a>										
<a href="#">21550067</a>	\$119.00	Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



Bulbs for Incandescent Permanent Optical Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95584035</a>	\$8.25	Bulb for Incandescent Light BA15d Bayonet Socket	7W	24V AC/DC	up to 5,000h
<a href="#">95584038</a>	\$8.25			115VAC	
<a href="#">95584057</a>	\$8.25			230VAC	



# Optical Signal Devices

## Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
<b>Installation Beacon Accessories</b>						
<a href="#">97581201</a>	\$14.50	<a href="#">PDF</a>	Tube adapter for beacons with 37mm (PG29) mounting installation. Find tube adapter accessories in WERMA Stack light catalog section.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.00	<a href="#">PDF</a>	Surface mounting base for beacons with 37mm (PG29) mounting installation		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$44.00	<a href="#">PDF</a>	Surface mounting enclosure for 1 beacon with 37mm (PG29) mounting installation		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$61.00	<a href="#">PDF</a>	Surface mounting enclosure for 2 beacons with 37mm (PG29) mounting installation			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$80.00	<a href="#">PDF</a>	Surface mounting enclosure for 3 beacons with 37mm (PG29) mounting installation			17g [0.6 oz]
<a href="#">97581522</a>	\$5.75	<a href="#">PDF</a>	Anti-twist washer for beacons with 37mm (PG29) mounting installation		304 Stainless steel	0.57 g [0.02 oz]
<b>Freestanding Beacon Accessories</b>						
<a href="#">96000001</a>	\$17.00	<a href="#">PDF</a>	Bracket for tube mounting - for use with use with 219 and 209 series industrial signal beacons.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$20.50	<a href="#">PDF</a>	Plastic Base with integrated tube for WERMA industrial signal beacons- for use with 209 and 219 series beacons		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$5.75	<a href="#">PDF</a>	Cable gland for WERMA industrial signal beacons: M25x1.5, plastic - for use with 209 and 219 series industrial signal beacons		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$43.00	<a href="#">PDF</a>	Galvanized Wire Guard for WERMA industrial signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.00	<a href="#">PDF</a>	Plastic Bracket for wall mounting for use with WERMA signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Polycarbonate/ ABS blend	62g [2.19 oz]

