



# Optical Signal Devices

## 75mm Beacons (PG29 Mount)

### Features

- Choose from blinking, rotating or permanent LED models, flashing Xenon model, or permanent Incandescent model
- Light-intensive Xenon flash in flash models
- High-impact polycarbonate lens (up to 20 joules)

- Various mounting accessories available
- Bulb not included with incandescent models
- Tamper-proof bulb change via rear access with bayonet mechanism on incandescent bulbs only
- 2-year warranty



### 815, 816 and 817 Series 75mm Beacons Technical Specifications

Part Number	Price	Color	Drawing Links	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g[oz]	Connection	Agency Approvals
<b>37mm (PG29 Mount)</b>													
<a href="#">81510000</a>	\$42.00	Red	<a href="#">PDF</a>	Incandescent Permanent Light	12-240V Depends on bulb selection. (bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-	-4 to 140°F [-20 to 60°C]  IP65	Up to 5,000h		96 [3.39]		
<a href="#">81520000</a>	\$42.00	Green	<a href="#">PDF</a>										
<a href="#">81530000</a>	\$42.00	Yellow	<a href="#">PDF</a>										
<a href="#">81540000</a>	\$49.00	Clear	<a href="#">PDF</a>										
<a href="#">81550000</a>	\$49.00	Blue	<a href="#">PDF</a>										
<a href="#">81610055</a>	\$89.00	Red	<a href="#">PDF</a>	LED Permanent Light	24V AC/DC	< 45mA	≤ 0.5 A		up to 100,000h	Polycarbonate cap	107 [3.77]	37mm (PG29) mount	cULus file E164155, CE, RoHS
<a href="#">81620055</a>	\$89.00	Green	<a href="#">PDF</a>										
<a href="#">81630055</a>	\$89.00	Yellow	<a href="#">PDF</a>										
<a href="#">81640055</a>	\$150.00	Clear	<a href="#">PDF</a>										
<a href="#">81650055</a>	\$150.00	Blue	<a href="#">PDF</a>										
<a href="#">81610067</a>	\$104.00	Red	<a href="#">PDF</a>										
<a href="#">81620067</a>	\$104.00	Green	<a href="#">PDF</a>										
<a href="#">81630067</a>	\$104.00	Yellow	<a href="#">PDF</a>										
<a href="#">81640067</a>	\$165.00	Clear	<a href="#">PDF</a>										
<a href="#">81650067</a>	\$165.00	Blue	<a href="#">PDF</a>										
<a href="#">81611055</a>	\$145.00	Red	<a href="#">PDF</a>										
<a href="#">81621055</a>	\$145.00	Green	<a href="#">PDF</a>										
<a href="#">81631055</a>	\$145.00	Yellow	<a href="#">PDF</a>										
<a href="#">81641055</a>	\$264.00	Clear	<a href="#">PDF</a>										
<a href="#">81651055</a>	\$264.00	Blue	<a href="#">PDF</a>										
<a href="#">81613055</a>	\$145.00	Red	<a href="#">PDF</a>	LED Rotating Light (120 rotations/min flash frequency)	24V AC/DC	< 40mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C]  IP65	4,000,000 flashes	ABS/ Polycarbonate base	Terminal M3 ≤ 2.5 mm <sup>2</sup> AWG14		
<a href="#">81623055</a>	\$145.00	Green	<a href="#">PDF</a>										
<a href="#">81633055</a>	\$145.00	Yellow	<a href="#">PDF</a>										
<a href="#">81643055</a>	\$241.00	Clear	<a href="#">PDF</a>										
<a href="#">81653055</a>	\$241.00	Blue	<a href="#">PDF</a>										
<a href="#">81710055</a>	\$133.00	Red	<a href="#">PDF</a>	Xenon Flashing Light (1Hz flash frequency)	24VDC	< 125mA	≤ 0.5 A		4,000,000 flashes		116 [4.09]		
<a href="#">81720055</a>	\$133.00	Green	<a href="#">PDF</a>										
<a href="#">81730055</a>	\$133.00	Yellow	<a href="#">PDF</a>										
<a href="#">81740055</a>	\$139.00	Clear	<a href="#">PDF</a>										
<a href="#">81750055</a>	\$139.00	Blue	<a href="#">PDF</a>										
<a href="#">81710067</a>	\$133.00	Red	<a href="#">PDF</a>		115VAC	< 22mA							
<a href="#">81720067</a>	\$131.00	Green	<a href="#">PDF</a>										
<a href="#">81730067</a>	\$131.00	Yellow	<a href="#">PDF</a>										
<a href="#">81740067</a>	\$133.00	Clear	<a href="#">PDF</a>										
<a href="#">81750067</a>	\$133.00	Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



Bulbs for Incandescent Permanent Optical Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95584035</a>	\$8.25	Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h
<a href="#">95584038</a>	\$8.25			230VAC	
<a href="#">95584057</a>	\$8.25			115VAC	



# Optical Signal Devices

## Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
<b>Installation Beacon Accessories</b>						
<a href="#">97581201</a>	\$14.50	<a href="#">PDF</a>	Tube adapter for beacons with 37mm (PG29) mounting installation. Find tube adapter accessories in WERMA Stack light catalog section.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.00	<a href="#">PDF</a>	Surface mounting base for beacons with 37mm (PG29) mounting installation		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$44.00	<a href="#">PDF</a>	Surface mounting enclosure for 1 beacon with 37mm (PG29) mounting installation		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$61.00	<a href="#">PDF</a>	Surface mounting enclosure for 2 beacons with 37mm (PG29) mounting installation			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$80.00	<a href="#">PDF</a>	Surface mounting enclosure for 3 beacons with 37mm (PG29) mounting installation			17g [0.6 oz]
<a href="#">97581522</a>	\$5.75	<a href="#">PDF</a>	Anti-twist washer for beacons with 37mm (PG29) mounting installation		304 Stainless steel	0.57 g [0.02 oz]
<b>Freestanding Beacon Accessories</b>						
<a href="#">96000001</a>	\$17.00	<a href="#">PDF</a>	Bracket for tube mounting - for use with use with 219 and 209 series industrial signal beacons.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$20.50	<a href="#">PDF</a>	Plastic Base with integrated tube for WERMA industrial signal beacons- for use with 209 and 219 series beacons		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$5.75	<a href="#">PDF</a>	Cable gland for WERMA industrial signal beacons: M25x1.5, plastic - for use with 209 and 219 series industrial signal beacons		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$43.00	<a href="#">PDF</a>	Galvanized Wire Guard for WERMA industrial signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.00	<a href="#">PDF</a>	Plastic Bracket for wall mounting for use with WERMA signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Polycarbonate/ ABS blend	62g [2.19 oz]

