



# Insulated Multi-bit Screwdrivers

Tools that work for you





## PocketMax Screwdriver

The 6 Piece Insulated SlimLine PocketMax Multi-bit screwdriver is equipped with insulated SlimLine bits. Every single Wiha insulated tool is individually tested to 10,000 volts AC and rated to 1,000 volts AC (1,500 volts DC) for safety and peace of mind in energized applications. Wiha insulated tools are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance.



## Features

- SoftFinish® cushion grip handle for comfort and control
- Handle direct molded to blade for permanent bond
- SlimLine blades technology up to 33% narrower insulation diameter, ideal for jobs where access is limited
- Dual durometer construction for long-lasting durability
- Magnetic easy open top with all SlimLine bits secured and stowed away
- Parallel flats for roll-off prevention

Multi-bit Screwdrivers								
Part Number	Number of Pieces	Part Image	Type	Bit Size	Overall Length	Handle Type	Set Includes	Price
<a href="#"><u>WT28345</u></a>	6		 Slotted	3.5 mm	6.8in (173mm)	Softfinish cushion grip handle with bit storage	(1) insulated Pocketmax handle with bit storage, (5) insulated SlimLine bits (slotted: 3.5mm, 6.5mm, Phillips: (#1, #2), square: (#2))	\$53.25
				6.5 mm				
			 Phillips	#1				
				#2				
 Square	#2							