

wiha Nut Setters

Tools that work for you



Nut Setters

Wiha's color coded nut setters are designed with high-visibility color-coding and laser-engraved size callouts for quick and easy identification. The nut setters have a solid shaft to provide strength and durability for long-lasting repetitive use. Wiha color coded nut setters are impact-rated for use in power tools. The nut setters feature industrial-strength magnets that securely retain fasteners to give you the freedom of one-handed work applications. Color coded nut setters are made of premium quality CrMo tool steel and have a durable finish for corrosion protection. Nut setters are precision-formed for exact-fit to reduce fastener cam-out that can lead to injury or damage to finished materials. The socket openings feature a beveled rim for easy fastener engagement with a broached and smooth finish for prolonged life.



Features

- High-visibility color coding for quick and easy size identification
- Industrial strength magnetic tip for secure fastener hold
- Impact rated to 700 in/lbs for maximum performance with Li-ion impact drivers
- Exact fit precision machined tip for reduced cam-out
- Standard 1/4-inch hex drive for universal application
- 6-inch (152mm) overall length for extended reach
- Radiused corners for preventing fastener head round-off
- Broached and clear-coated openings for added corrosion protection
- Cold forged from Chromium-molybdenum alloy steel (CrMo) for strength and durability

Nut Setters						
Part Number	Number of Pieces	Part Image	Set Type	Overall Length	Set Includes	Price
<u>WT70486</u>	6		Imperial	6in (152.4mm)	(6) color-coded 6in nut setters (1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in)	\$47.50
<u>WT70487</u>			Metric		(6) color-coded 6in nut setters (8mm, 10mm, 11mm, 12mm, 13mm, 14mm)	\$47.50