

wiha Precision Pliers

Tools that work for you




Precision Pliers

Wiha's precision pliers feature soft touch satin grips for maximum comfort and control. Every plier is constructed of premium quality tool steel with induction hardened jaws and cutting edges for superior sharpness and service life.

Features

- Soft Touch satin grips for maximum comfort
- Black anti-glare finish, precise cutting edges
- Soft Touch tension return springs
- Induction-hardened cutting edges and jaws for superior sharpness and longevity, approximately 64HRC
- Premium quality C70 tool steel for strength and durability



Precision Pliers										
Part Number	Part Image	Pliers Type	Handle Type	Overall Length	Handle Length	Jaw Length	Jaw Thickness	Jaw Width	Material	Price
<u>WT56801</u>		Pointed Short Nose	Electronic cushion grip handles	5.5in (140mm)	3.9in (99mm)	0.79in (20.0mm)	0.24in (6.0mm)	0.51in (13.0mm)	C70 Steel	\$34.75
<u>WT56812</u>		Precision Diagonal		4.5in (114mm)		0.32in (8.0mm)	0.16in (4.0mm)	0.37in (9.5mm)		\$34.00
<u>WT56813</u>		Precision Diagonal Full Flush		5.0in (127mm)		0.20in (5.0mm)	0.39in (10.0mm)	\$37.50		