

wiha Striking Tools

Tools that work for you

Split Head Mallet Set

Wiha split head mallets feature rugged malleable cast iron heads with a heavy-duty, non-slip hickory handle. Mallet faces are removable, and standard options include: TPE Soft, Latex Rubber MedSoft, Polyurethane MedHard, Cell Acetate Hard, and a Nylon Extra Hard. These mallets are ideal for construction, woodworking, automotive applications along with many more.

Features

- Rugged malleable cast iron heads
- Five head diameters: 1.2 in to 3.1 in
- Safety-ribbed housings for handle and faces
- Carefully crafted hickory handle with non-slip surface
- Multi-use mallet: made for construction, woodworking, automotive applications, and more



Blue: Soft



Red: Hard



White: Extra Hard



Black: Medium Soft



Yellow: Medium Hard



WT83256



WT83270

Split Head Mallet Sets				
Part Number	Number of Pieces	Part Image	Includes	Price
<u>WT83256</u>	9		(2) heavy duty mallet housings, (1) hickory handle, (1) 8 mm hex key, and (5) 50 mm faces: (blue TPE soft, black latex rubber medium-soft, yellow polyurethane medium-hard, red cell acetate hard, white nylon extra hard)	\$79.00
<u>WT83270</u>	14		(1) heavy duty 30 mm face mallet, (1) heavy duty 50 mm face mallet, (1) 8 mm hex key, (1) 5 mm hex key, (5) 50 mm and (5) 30 mm faces: (blue TPE soft, black latex rubber medium-soft, yellow polyurethane medium-hard, red cell acetate hard, white nylon extra hard), (1) foam tray for easy access and storage	\$145.00

wiha Striking Tools

Tools that work for you

Dead Blow Hammers

The Wiha Dead Blow Hammer series features durable tool steel construction with replaceable faces for extended tool life. Available in individual 49 oz and 72 oz models with 2.0 in and 2.3 in faces respectively, or as a complete 3-piece set including 30 mm, 40 mm, and 50 mm sizes. The dead blow design minimizes rebound and surface damage while delivering maximum striking force. These hammers are ideal for automotive work, metal fabrication, assembly applications, and general maintenance tasks.

Features

- Available individually or as a 3-piece set
- Durable tool steel construction for long-lasting performance
- Replaceable faces extend tool life and reduce replacement costs
- Dead blow design minimizes rebound and surface damage
- Precision-balanced weight distribution for controlled strikes
- Multi-use hammer: made for automotive work, metal fabrication, assembly applications and general maintenance



WT80290



All-steel body for incredible durability



Anti-vibration ergonomic grips

Dead Blow Hammers					
Part Number	Number of Pieces	Part Image	Size (in/mm)	Set Includes	Price
WT80290	3		1.2 / 30 1.6 / 40 2.0 / 50	(3) all steel body dead blow hammers with replaceable faces (30 mm, 40 mm, 50 mm)	\$175.00
WT80250	1		2.0 / 50	Wiha dead blow hammer 50 mm face	\$73.00
WT80260	1		2.3 / 58	Wiha dead blow hammer 2.3 in face	\$95.00