

Measuring Tools

Tape Measures

The 25-Foot DualMax Tape Measure combines high-visibility design with versatile functionality for accurate measurements in any setting. The bright yellow top and white bottom provide excellent contrast for easy reading in varying light conditions. Ideal for installation work, maintenance tasks, job site measurements, and general industrial applications.

Features

- 25-foot tape length
- High-visibility yellow top and white bottom for easy reading in varying light conditions
- Standoff dimension of 3-1/4 in (82 mm) for accurate inside measurements
- Dual-access design with standard hook and convenient top tab for bottom tape deployment
- Smooth, robust locking mechanism for secure blade positioning
- · Easy one-handed operation for increased productivity
- Durable construction for long-lasting performance
- Standard belt clip







Tape Measures						
Part Number	Length	Measurement	Increments	Standout Length	Material	Price
<u>WT61680</u>	25 ft	Imperial	1/16 in	10 ft	Rubber overmold	\$26.00