

Weidmüller Pliers & Cutting Tools

Cable Shears and Cutters

Cable shears and cutters deliver clean, precise cuts through copper and aluminum conductors with minimum physical effort. The special blade geometry provides pinch-free cutting that prevents conductor deformation and fraying. Select models feature VDE and GS-tested protective insulation rated to 1000V in accordance with EN/IEC 60900 for safe work on or near live circuits. Available in multiple sizes from compact mini shears to heavy-duty cutters for large-diameter cables.

Features

- Special blade geometry for pinch-free cutting with minimum physical effort
- VDE/GS-tested 1000V insulation on select models per EN/IEC 60900
- One-hand mechanical operation for convenient use in tight spaces
- Cuts copper and aluminum conductors in flexible, solid, and stranded configurations
- Insulated cushion grip handles reduce fatigue during extended use
- Multiple sizes available for conductor diameters from 7mm to 22mm



Cable Shears and Cutters											
Part Number	Part Image	Pliers Type	Insulation Rating	Capacity	Handle Type	Overall Length	Handle Length	Jaw Length	Jaw Thickness	Jaw Width	Price
9002650000		Cable Shears: curved shear cutting edges	1000V	2 AWG	Insulated cushion grip handles	7.3in [185mm]	4.9in [124.7mm]	1.0in [25.4mm]	0.39in [10.0mm]	0.89in [22.6mm]	\$55.00
1157820000		Cable Shears: straight shear cutting edges	1000V	3/0 AWG	Insulated cushion grip handles	8.8in [225mm]	5.6in [142.3mm]	1.1in [28.0mm]	0.50in [12.7mm]	1.16in [29.5mm]	\$72.00
9002660000		Cable Shears: pinch free shear cutting edges	1000V	2/0 AWG	Insulated cushion grip handles	8.8in [225mm]	5.6in [142.3mm]	1.1in [28.0mm]	0.50in [12.7mm]	1.16in [29.5mm]	\$62.00
1157830000		Cable Shears: curved shear cutting edges	1000V	2/0 AWG	Insulated cushion grip handles	9.8in [249mm]	5.9in [150mm]	1.7in [43.2mm]	0.52in [13.2mm]	1.81in [46.0mm]	\$82.00
2876460000*		KT MINI Cable Shears: induction hardened shear cutting edges	N/A	4 AWG	Classic grip vinyl handles	4.7in [120mm]	2.9in [72.8mm]	0.80in [20.3mm]	0.24in [6.0mm]	0.79in [20.1mm]	\$38.00
9205150000*		SUPER CUT Cutters: ultra full flush cutting edge	N/A	14 AWG	Comfort grip handles	5.0in [128mm]	3.5in [89.0mm]	0.68in [17.3mm]	0.16in [4.0mm]	0.55in [14.0mm]	\$47.50

*EN/IEC 60900 not applicable