



Product Advisory

Product Families:	Leeson and Marathon Motors	Number:	PA-MRM-001
Part No.:	See table below	Date Issued:	07/08/2026
Subject:	Branding and Series Changes for Regal Motors	Revision:	Original

Description of Problem

Due to business changes at Regal Rexnord and Marathon, several motors under the Marathon and Leeson brand names have changed their series/branding. Customers may receive motors with either Marathon or Leeson branding that may be different from when the identical part numbers were purchased in the past. All specifications and equipment are the same – only the brand name has changed.



Branding Changes will show up on the Nameplate of the motor, and on the product packaging



LEESON® BRAND GROWS TO BRING ENHANCED PERFORMANCE AND INNOVATION TO REGAL REXNORD CUSTOMERS



MILWAUKEE, WIS. — April 30, 2024 — Regal Rexnord Corporation (NYSE: RRX), a global leader in the engineering and manufacturing of electric motors and controls, power generation products and power transmission components, announces that the LEESON brand of Regal Rexnord will expand significantly as Marathon® NEMA® AC induction motors below 182T frame size are welcomed into the LEESON products family.

"From the first day of business in 1972, the people behind the LEESON brand have been deeply dedicated to innovating and delivering the highest quality motors to solve our customers' problems," said Brooke Lang, Executive Vice President & President of Power Efficiency Solutions at Regal Rexnord. "This integration further deepens the commitment of the LEESON brand to delivering optimized solutions that are engineered to solve our customers' business challenges through reliability, efficiency and performance."

All Marathon branded motor SKUs below 182T frame size will now be under the LEESON brand name. These include motors used in a wide range of applications. From lifting boats to powering treadmills, pitching machines, running water pumps, HVAC, fans, pumps, conveyors, material handling equipment and food processing equipment. The small motor products will continue to be manufactured in the same plants and the same legacy dedicated LEESON products sales team will be ready and available to serve customers.

From safeguarding warranties to enhancing customer support processes, a dedicated team is carefully managing every aspect of the transition to deliver the benefits of the LEESON brand to current Marathon product users. Known for durable, high-quality motors and solutions, customers can expect LEESON-branded products to meet the highest standards of excellence.

"Customers are at the heart of everything we do," says Lang. "Our goal is to deliver a better and more consistent experience across our portfolio of market-leading innovative solutions, while making the transition seamless to our valued customers."

For more information and updates on the transition, customers are encouraged to visit www.Regalrexnord.com and engage with the customer support team.



Product Advisory

Affected Products

The following motors are changing from the Marathon Brand to Leeson Brand

Part Number	Product Description
4354	Standard efficiency AC induction motor, general purpose, 1/4hp, 1-phase, 115 VAC, 1800rpm, ODP, NEMA 48 frame, rolled steel, rigid base mount.
4362	Standard efficiency AC induction motor, general purpose, 1/4hp, 1-phase, 115 VAC, 1800rpm, ODP, NEMA 48 frame, rolled steel, rigid base mount.
B319	Standard efficiency AC induction motor, fan and blower, 3/4hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, resilient base with extended studs mount.
B352	Standard efficiency AC induction motor, fan and blower, 2hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56H frame, rolled steel, resilient base with extended studs mount.
C1152	Standard efficiency AC induction motor, fan and blower, 1/2hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 48 frame, rolled steel, resilient base mount.
C1153	Standard efficiency AC induction motor, fan and blower, 1/2hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
C1155	Standard efficiency AC induction motor, fan and blower, 3/4hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
C1158	Standard efficiency AC induction motor, fan and blower, 1hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
C1160	Standard efficiency AC induction motor, fan and blower, 1-1/2hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56H frame, rolled steel, resilient base mount.
C1161	Standard efficiency AC induction motor, fan and blower, 2hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56H frame, rolled steel, resilient base mount.
C1336	Standard efficiency AC induction motor, centrifugal jet pump, 1/3hp, 1-phase, 115/230 VAC, 3600rpm, TEFC, NEMA 56J frame, rolled steel, C-face mount.
C147A	Premium efficiency AC induction motor, general purpose, 1/4hp, 1-phase, 115/230 VAC, suitable for 208 VAC at 60 Hz, 1800rpm, ODP, NEMA 48 frame, rolled steel, rigid base mount.
C167A	Standard efficiency AC induction motor, general purpose, 1/2hp, 1-phase, 115/230 VAC, suitable for 208 VAC at 60 Hz, 1800rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.
C169	Standard efficiency AC induction motor, air compressor definite purpose, 1/2hp, 1-phase, 115/230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.
C187A	Standard efficiency AC induction motor, general purpose, 2hp, 1-phase, 115/230 VAC, suitable for 208 VAC at 60 Hz, 3600rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.
C188A	Standard efficiency AC induction motor, general purpose, 1hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 143T frame, rolled steel, rigid base mount.



Product Advisory

C216	Standard efficiency AC induction motor, fan and blower, 1/3hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
C235	Standard efficiency AC induction motor, fan and blower, 1hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
D010	Standard efficiency AC induction motor, pressure washer definite purpose, 1hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.
D115	Standard efficiency AC induction motor, fan and blower, 1-1/2hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
D118	Standard efficiency AC induction motor, fan and blower, 1hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56 frame, rolled steel, resilient base mount.
D311	Standard efficiency AC induction motor, general purpose and 4-in-1, 1/2hp, 1-phase, 115/208-230 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
D312	Standard efficiency AC induction motor, general purpose and 4-in-1, 3/4hp, 1-phase, 115/208-230 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
D313	Premium efficiency AC induction motor, general purpose and 4-in-1, 1hp, 1-phase, 115/208-230 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
D314	Standard efficiency AC induction motor, general purpose and 4-in-1, 1-1/2hp, 1-phase, 115/208-230 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
D315	Standard efficiency AC induction motor, general purpose and 4-in-1, 2hp, 1-phase, 115/208-230 VAC, 3600rpm, TEFC, NEMA 56HC frame, rolled steel, C-face/removable rigid base mount.
D316	Standard efficiency AC induction motor, general purpose and 4-in-1, 3hp, 1-phase, 208-230 VAC, 3600rpm, TEFC, NEMA 56HC frame, rolled steel, C-face/removable rigid base mount.
E2001A	Premium efficiency AC induction motor, inverter rated, 1hp, 3-phase, 208-230/460 VAC, 1800rpm, TEFC, NEMA 143TC frame, rolled steel, C-face/rigid base mount.
E2002	Premium efficiency AC induction motor, inverter rated, 1hp, 3-phase, 208-230/460 VAC, 1200rpm, TEFC, NEMA 145TC frame, rolled steel, C-face/rigid base mount.
E2004A	Premium efficiency AC induction motor, inverter rated, 1-1/2hp, 3-phase, 208-230/460 VAC, 1800rpm, TEFC, NEMA 145TC frame, rolled steel, C-face/rigid base mount.
E2007A	Premium efficiency AC induction motor, inverter rated, 2hp, 3-phase, 208-230/460 VAC, 1800rpm, TEFC, NEMA 145TC frame, rolled steel, C-face/rigid base mount.
E261A	Standard efficiency AC induction motor, general purpose, 1/2hp, 1-phase, 100-120/200-240 VAC, 1800rpm, ODP, NEMA 56C frame, rolled steel, C-face/rigid base mount.
E268A	Premium efficiency AC induction motor, general purpose, 3/4hp, 1-phase, 100-120/200-240 VAC, 1800rpm, ODP, NEMA 56C frame, rolled steel, C-face/rigid base mount.
G1115	Standard efficiency AC induction motor, fan and blower, 1/4hp, 1-phase, 115/230 VAC, 1800rpm, ODP, NEMA 48 frame, rolled steel, resilient base mount.



Product Advisory

G570	Standard efficiency AC induction motor, general purpose and 4-in-1, 1/3hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
G571	Standard efficiency AC induction motor, general purpose and 4-in-1, 1/2hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
G572	Standard efficiency AC induction motor, general purpose and 4-in-1, 3/4hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
G573	Standard efficiency AC induction motor, general purpose and 4-in-1, 1hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56HC frame, rolled steel, C-face/removable rigid base mount.
G574	Standard efficiency AC induction motor, general purpose and 4-in-1, 1-1/2hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56HC frame, rolled steel, C-face/removable rigid base mount.
G575	Standard efficiency AC induction motor, general purpose and 4-in-1, 2hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56HC frame, rolled steel, C-face/removable rigid base mount.
G915A	Standard efficiency AC induction motor, general purpose, 3/4hp, 1-phase, 115/230 VAC, suitable for 208 VAC at 60 Hz, 3600rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.
I127	Standard efficiency AC induction motor, general purpose, 2hp, 1-phase, 115/208-230 VAC, 1800rpm, ODP, NEMA 145T frame, rolled steel, rigid base mount.
J061	Standard efficiency AC induction motor, centrifugal jet pump and inverter rated, 1/2hp, 3-phase, 208-230/460 VAC, 3600rpm, TEFC, NEMA 56J frame, rolled steel, C-face/rigid base mount.
J063A	Premium efficiency AC induction motor, centrifugal jet pump and inverter rated, 1hp, 3-phase, 230/460 VAC, suitable for 208 VAC at 60 Hz, 3600rpm, TEFC, NEMA 56J frame, rolled steel, C-face/rigid base mount.
J064A	Premium efficiency AC induction motor, centrifugal jet pump and inverter rated, 1-1/2hp, 3-phase, 208-230/460 VAC, 3600rpm, TEFC, NEMA 56J frame, rolled steel, C-face/rigid base mount.
J065A	Premium efficiency AC induction motor, centrifugal jet pump and inverter rated, 2hp, 3-phase, 230/460 VAC, suitable for 208 VAC at 60 Hz, 3600rpm, TEFC, NEMA 56J frame, rolled steel, C-face/rigid base mount.
J066A	Premium efficiency AC induction motor, centrifugal jet pump and inverter rated, 3hp, 3-phase, 230/460 VAC, 3600rpm, TEFC, NEMA 56HJ frame, rolled steel, C-face/rigid base mount. Drip cover and mounting hardware included.
SY001	Premium efficiency AC permanent magnet motor, high-performance inverter duty, 1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA S56C frame, rolled steel, C-face/rigid base mount. Requires drive.



Product Advisory

SY003	Premium efficiency AC permanent magnet motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA S56C frame, rolled steel, C-face/rigid base mount. Requires drive.
SY004	Premium efficiency AC permanent magnet motor, high-performance inverter duty, 1-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA S56C frame, rolled steel, C-face/rigid base mount. Requires drive.
SY005	Premium efficiency AC permanent magnet motor, high-performance inverter duty, 2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA S56C frame, rolled steel, C-face/rigid base mount. Requires drive.
Y280	Premium efficiency AC induction motor, high-performance inverter duty, 1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount. Dynapar HS20 encoder included.
Y281	Premium efficiency AC induction motor, high-performance inverter duty, 3/4hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount. Dynapar HS20 encoder included.
Y282	High efficiency AC induction motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount. Dynapar HS20 encoder included.
Y284	High efficiency AC induction motor, high-performance inverter duty, 1-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 145TC frame, rolled steel, C-face/removable rigid base mount. Dynapar HS20 encoder included.
Y285	High efficiency AC induction motor, high-performance inverter duty, 2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 145C frame, cast iron, C-face/removable rigid base mount. Dynapar HS20 encoder included.
Y360	Premium efficiency AC induction motor, high-performance inverter duty, 1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/rigid base mount.
Y362	Standard efficiency AC induction motor, high-performance inverter duty, 3/4hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/rigid base mount.
Y364	Standard efficiency AC induction motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/rigid base mount.
Y366	High efficiency AC induction motor, high-performance inverter duty, 1-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 145TC frame, rolled steel, C-face/removable rigid base mount.
Y368	Standard efficiency AC induction motor, high-performance inverter duty, 2hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 145TC frame, rolled steel, C-face/removable rigid base mount.
Y500	Premium efficiency AC induction motor, high-performance inverter duty, 1/4hp, 3-phase, 230 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/rigid base mount.
Y502	Premium efficiency AC induction motor, high-performance inverter duty, 1/3hp, 3-phase, 230 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/rigid base mount.
Y534	Premium efficiency AC induction motor, high-performance inverter duty, 1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.



Product Advisory

- Y535 High efficiency AC induction motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.
- Y536 High efficiency AC induction motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 143TC frame, rolled steel, C-face/removable rigid base mount.
- Y537 High efficiency AC induction motor, high-performance inverter duty, 1hp, 3-phase, 230/460 VAC, 1200rpm, TENV, NEMA 145TC frame, rolled steel, C-face/removable rigid base mount.
- Y538 High efficiency AC induction motor, high-performance inverter duty, 1-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 145TC frame, rolled steel, C-face/rigid base mount.
- Y551 High efficiency AC induction motor, high-performance inverter duty, 2hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 145TC frame, cast iron, C-face/rigid base mount.
- Y592 Standard efficiency AC induction motor, high-performance inverter duty, 1/4hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 56C frame, rolled steel, C-face/removable rigid base mount.



Product Advisory

The following motors are changing from the Leeson Brand to the Marathon Brand

External Id	ADC Descriptions//Primary Product Description
132440.00	Premium efficiency AC induction motor, washdown and inverter rated, 5hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 184TC frame, rolled steel, C-face mount.
140820.00	Premium efficiency AC induction motor, washdown and inverter rated, 10hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 215T frame, rolled steel, rigid base mount.
140821.00	Premium efficiency AC induction motor, washdown and inverter rated, 10hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 215TC frame, rolled steel, C-face/rigid base mount.
140822.00	Premium efficiency AC induction motor, washdown and inverter rated, 7-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 213TC frame, rolled steel, C-face/rigid base mount.
141266.00	Premium efficiency AC induction motor, washdown and inverter rated, 7-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 213TC frame, rolled steel, C-face mount.

The following motors will remain Marathon branded, but may have different series names

External Id	ADC Descriptions//Primary Product Description
SY067	Super premium efficiency AC permanent magnet motor, high-performance inverter duty, 5hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 184TC frame, rolled steel, C-face/rigid base mount. Requires drive.
SY068	Super premium efficiency AC permanent magnet motor, high-performance inverter duty, 7-1/2hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 213TC frame, rolled steel, C-face/rigid base mount. Requires drive.
SY069	Super premium efficiency AC permanent magnet motor, high-performance inverter duty, 10hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 215TC frame, rolled steel, C-face/rigid base mount. Requires drive.
Y286A	High efficiency AC induction motor, high-performance inverter duty, 3hp, 3-phase, 230/460 VAC, 1800rpm, TENV, NEMA 182TC frame, aluminum, C-face/rigid base mount. Dynapar HS20 encoder included.



Product Advisory

Solution for Problem

This is a permanent change – once existing branded inventory is sold, all new motors will follow the branding set forth in this product advisory. All motor specifications, constructions and performance will remain the same

Technical Assistance

If you have any questions regarding this Product Advisory, please contact Technical Support at 770-844-4200 or 800-633-0405 for further assistance.