


TABLE A	
PART NO	LENGTH
GS-485RJ12-CBL-2	2.0M [6.6FT]



NOTES:

1. UL2426 26AWG*3C + TALCUM
OD: 4.5MM, JACKET BLACK COLOR
2. RJ12 6P6C MODULAR PLUG
CONTACT: BRASS, GOLD FLASH
3. MINIMUM BEND RADIUS: 36mm [1.42in]
4. OPERATING TEMPERATURE: 0-60°C (32-140°F)

PIN-OUT DIAGRAM



GS-485RJ12-CBL-2	
Rev: original	Date: 06/2010
Units: mm [inches]	
Scale: none	
ZIPLINK GS Drive Cable	