



TABLE A

PART NO.	LENGTH
ZL-P1-CBL18	0.5m (1.7ft)
ZL-P1-CBL18-1	1.0m (3.3ft)
ZL-P1-CBL18-2	2.0m (6.6ft)

PIN-OUT DIAGRAM

P1	P2
NC	1
	13
2	3
3	4
4	5
5	6
10	7
	19
11	9
12	10
13	11
14	12
1	2
	14
6	15
7	16
8	17
9	18
NC	8
	20
15	21
16	22
17	23
18	24

NOTES:

- CABLE: 24 CONDUCTOR, 24 AWG, PVC JACKET INSULATION RATING 80°C (176°F), 300V
- CURRENT: 2A PER CONDUCTOR, 40A MAXIMUM CABLE CURRENT
- VOLTAGE
 - 240V AC/DC RATED OPERATING VOLTAGE
 - 265V AC/DC MAXIMUM VOLTAGE
- OPERATING TEMPERATURE: 0-60°C (32-140°F)
- P1 CONNECTOR: 18 POSITION TERMINAL BLOCK FOR PRODUCTIVITY1000 PLC
- P2 CONNECTOR: 24-PIN RECEPTACLE EQUIVALENT TO MOLEX MICRO-FIT3.0 (PART # 43025-2400)
- MINIMUM BEND RADIUS: 65.6MM [2.58IN]

HEAT-SHRINK TUBING

ZL-P1-CBL18-n	
Rev: B	Date: 6/28/2016
Units: mm [inches]	
Scale: 1:1	
ZIPLink Connector Module Cable	
AUTOMATIONDIRECT.com	