


Heartland Series – Polycarbonate Enclosures

Opaque Door with Polycarbonate Latches



AH12106



Construction


- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- 304 stainless steel cover screw
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in-lbs cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in-lbs mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability

Listings

- cULus File E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Temperature Range (-40°F to +248°F) (-40°C to +120°C)
- Flammability Rating UL94-5V

Certifications

- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Heartland Series – Polycarbonate Enclosures – Opaque Door with Polycarbonate Latches

Part Number	Price	Enclosure Overall Size HxWxD	Wt.	Carbon Steel Subpanel	Fiberglass Subpanel	Aluminum Subpanel	Drawing Link
AH664	\$88.00	7.40 x 7.41 x 5.35 [188 x 188 x 136]	2.50 [5.51]	BP66CS	—	BP66A	PDF
AH864	\$94.00	9.40 x 7.40 x 5.32 [239 x 188 x 135]	3.20 [7.06]	BP86CS	BP86FG	BP86A	PDF
AH884	\$98.00	9.41 x 9.41 x 5.36 [239 x 239 x 136]	3.80 [8.38]	BP88CS	—	—	PDF
AH1084	\$114.00	11.41 x 9.41 x 5.89 [290 x 239 x 150]	4.30 [9.48]	BP108CS	BP108FG	BP108A	PDF
AH1086	\$119.00	11.41 x 9.41 x 7.39 [290 x 239 x 188]	5.20 [11.47]	BP108CS	BP108FG	BP108A	PDF
AH10106	\$125.00	11.41 x 11.41 x 6.47 [290 x 290 x 164]	5.70 [12.57]	—	—	BP1010A	PDF
AH12106	\$158.00	13.41 x 11.41 x 7.38 [341 x 290 x 187]	6.20 [13.67]	BP1210CS	BP1210FG	BP1210A	PDF
AH14126	\$185.00	15.40 x 13.40 x 7.39 [391 x 340 x 188]	8.00 [17.64]	BP1412CS	BP1412FG	BP1412A	PDF
AH16148	\$209.00	17.41 x 15.41 x 9.40 [442 x 391 x 239]	10.00 [22.05]	BP1614CS	BP1614FG	BP1614A	PDF
AH18164	\$228.00	19.40 x 17.41 x 5.41 [493 x 442 x 137]	4.50 [9.92]	BP1816CS	BP1816FG	BP1816A	PDF
AH181610	\$247.00	19.41 x 17.41 x 11.41 [493 x 442 x 290]	11.25 [24.81]	BP1816CS	BP1816FG	BP1816A	PDF
AH20168	\$362.00	21.41 x 17.41 x 9.47 [544 x 442 x 241]	14.00 [30.87]	—	—	—	PDF
AH242410	\$649.00	25.41 x 25.41 x 11.41 [645 x 645 x 290]	23.60 [52.04]	—	—	—	PDF


Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Weight in pounds [kilograms].

Heartland Series – Polycarbonate Enclosures

Smoked Door with Polycarbonate Latches



AH12106C



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- 304 stainless steel cover screw
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in-lbs cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in-lbs mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability

Listings


- cULus File E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Temperature Range (-40°F to +248°F) (-40°C to +120°C)
- Flammability Rating UL94-5V

Certifications

- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



Dimensions



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Heartland Series – Polycarbonate Enclosures – Smoked Door with Polycarbonate Latches

Part Number	Price	Enclosure Overall Size HxWxD	Wt.	Carbon Steel Subpanel	Fiberglass Subpanel	Aluminum Subpanel	Drawing Link
AH664C	\$95.00	7.40 x 7.41 x 5.35 [188 x 188 x 136]	2.50 [5.51]	BP66CS	—	BP66A	PDF
AH864C	\$106.00	9.40 x 7.40 x 5.32 [239 x 188 x 135]	3.20 [7.06]	BP86CS	BP86FG	BP86A	PDF
AH884C	\$112.00	9.41 x 9.41 x 5.36 [239 x 239 x 136]	3.75 [8.27]	BP88CS	—	—	PDF
AH1084C	\$134.00	11.41 x 9.41 x 5.89 [290 x 239 x 150]	4.30 [9.48]	BP108CS	BP108FG	BP108A	PDF
AH1086C	\$139.00	11.41 x 9.41 x 7.39 [290 x 239 x 188]	5.20 [11.47]	BP108CS	BP108FG	BP108A	PDF
AH10106C	\$146.00	11.41 x 11.41 x 6.47 [290 x 290 x 164]	5.70 [12.57]	—	—	BP1010A	PDF
AH12106C	\$176.00	13.41 x 11.41 x 7.38 [341 x 290 x 187]	6.20 [13.67]	BP1210CS	BP1210FG	BP1210A	PDF
AH14126C	\$194.00	15.40 x 13.40 x 7.39 [391 x 340 x 188]	8.00 [17.64]	BP1412CS	BP1412FG	BP1412A	PDF
AH16148C	\$237.00	17.41 x 15.41 x 9.40 [442 x 391 x 239]	10.00 [22.05]	BP1614CS	BP1614FG	BP1614A	PDF
AH18164C	\$267.00	19.40 x 17.41 x 5.41 [493 x 442 x 137]	4.50 [9.92]	BP1816CS	BP1816FG	BP1816A	PDF
AH181610C	\$275.00	19.41 x 17.41 x 11.41 [493 x 442 x 290]	11.25 [24.81]	BP1816CS	BP1816FG	BP1816A	PDF
AH20168C	\$424.00	21.41 x 17.41 x 9.47 [544 x 442 x 241]	14.00 [30.87]	—	—	—	PDF
AH242410C	\$695.00	25.41 x 25.41 x 11.41 [645 x 645 x 290]	23.60 [52.04]	—	—	—	PDF


Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Weight in pounds [kilograms].

Heartland Series – Polycarbonate Enclosures

Opaque Door with Stainless Steel Latches



AH12106SS



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- 316 stainless steel cover screws and latches
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size - #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in-lbs cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in-lbs mounting feet torque
- Variable depth side mount capability

Listings


- cULus File E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Temperature Range (-40°F to +248°F) (-40°C to +120°C)
- Flammability Rating UL94-5V

Certifications

- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



Dimensions



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Heartland Series – Polycarbonate Enclosures – Opaque Door with Stainless Steel Latches

Part Number	Price	Enclosure Overall Size HxWxD	Wt.	Carbon Steel Subpanel	Fiberglass Subpanel	Aluminum Subpanel	Drawing Link
AH664SS	\$95.00	7.40 x 7.41 x 5.35 [188 x 188 x 136]	2.50 [5.51]	BP66CS	—	BP66A	PDF
AH864SS	\$101.00	9.40 x 7.40 x 5.32 [239 x 188 x 135]	3.20 [7.06]	BP86CS	BP86FG	BP86A	PDF
AH884SS	\$105.00	9.41 x 9.41 x 5.36 [239 x 239 x 136]	3.75 [8.27]	BP88CS	—	—	PDF
AH1084SS	\$123.00	11.41 x 9.41 x 5.89 [290 x 239 x 150]	4.30 [9.48]	BP108CS	BP108FG	BP108A	PDF
AH1086SS	\$128.00	11.41 x 9.41 x 7.39 [290 x 239 x 188]	5.20 [11.47]	BP108CS	BP108FG	BP108A	PDF
AH10106SS	\$135.00	11.41 x 11.41 x 6.47 [290 x 290 x 164]	5.70 [12.57]	—	—	BP1010A	PDF
AH12106SS	\$170.00	13.41 x 11.41 x 7.38 [341 x 290 x 187]	6.20 [13.67]	BP1210CS	BP1210FG	BP1210A	PDF
AH14126SS	\$199.00	15.40 x 13.40 x 7.39 [391 x 340 x 188]	8.00 [17.64]	BP1412CS	BP1412FG	BP1412A	PDF
AH16148SS	\$225.00	17.41 x 15.41 x 9.40 [442 x 391 x 239]	10.00 [22.05]	BP1614CS	BP1614FG	BP1614A	PDF
AH18164SS	\$245.00	19.40 x 17.41 x 5.41 [493 x 442 x 137]	4.50 [9.92]	BP1816CS	BP1816FG	BP1816A	PDF
AH181610SS	\$266.00	19.41 x 17.41 x 11.41 [493 x 442 x 290]	11.25 [24.81]	BP1816CS	BP1816FG	BP1816A	PDF
AH20168SS	\$390.00	21.41 x 17.41 x 9.47 [544 x 442 x 241]	14.00 [30.87]	—	—	—	PDF
AH242410SS	\$697.00	25.41 x 25.41 x 11.41 [645 x 645 x 290]	23.60 [52.04]	—	—	—	PDF

Notes: Subpanels must be ordered separately.

Dimensions in inches [millimeters].


Weight in pounds [kilograms].

Heartland Series – Polycarbonate Enclosures

Smoked Door with Stainless Steel Latches



AH12106CSS



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- 316 stainless steel cover screw and latches
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in-lbs cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in-lbs mounting feet torque
- Variable depth side mount capability

Listings


- cULus File E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Temperature Range (-40°F to +248°F) (-40°C to +120°C)
- Flammability Rating UL94-5V

Certifications

- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



Dimensions



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Heartland Series – Polycarbonate Enclosures – Smoked Door with Stainless Steel Latches

Part Number	Price	Enclosure Overall Size HxWxD	Wt.	Carbon Steel Subpanel	Fiberglass Subpanel	Aluminum Subpanel	Drawing Link
AH664CSS	\$103.00	7.40 x 7.41 x 5.35 [188 x 188 x 136]	2.50 [5.51]	BP66CS	—	BP66A	PDF
AH864CSS	\$114.00	9.40 x 7.40 x 5.32 [239 x 188 x 135]	3.20 [7.06]	BP86CS	BP86FG	BP86A	PDF
AH884CSS	\$121.00	9.41 x 9.41 x 5.36 [239 x 239 x 136]	3.75 [8.27]	BP88CS	—	—	PDF
AH1084CSS	\$144.00	11.41 x 9.41 x 5.89 [290 x 239 x 150]	4.30 [9.48]	BP108CS	BP108FG	BP108A	PDF
AH1086CSS	\$149.00	11.41 x 9.41 x 7.39 [290 x 239 x 188]	5.20 [11.47]	BP108CS	BP108FG	BP108A	PDF
AH10106CSS	\$157.00	11.41 x 11.41 x 6.47 [290 x 290 x 164]	5.70 [12.57]	—	—	BP1010A	PDF
AH12106CSS	\$189.00	13.41 x 11.41 x 7.38 [341 x 290 x 187]	6.20 [13.67]	BP1210CS	BP1210FG	BP1210A	PDF
AH14126CSS	\$208.00	15.40 x 13.40 x 7.39 [391 x 340 x 188]	8.00 [17.64]	BP1412CS	BP1412FG	BP1412A	PDF
AH16148CSS	\$255.00	17.41 x 15.41 x 9.40 [442 x 391 x 239]	10.00 [22.05]	BP1614CS	BP1614FG	BP1614A	PDF
AH18164CSS	\$287.00	19.40 x 17.41 x 5.41 [493 x 442 x 137]	4.50 [9.92]	BP1816CS	BP1816FG	BP1816A	PDF
AH181610CSS	\$296.00	19.41 x 17.41 x 11.41 [493 x 442 x 290]	11.25 [24.81]	BP1816CS	BP1816FG	BP1816A	PDF
AH20168CSS	\$456.00	21.41 x 17.41 x 9.47 [544 x 442 x 241]	14.00 [30.87]	—	—	—	PDF
AH242410CSS	\$747.00	25.41 x 25.41 x 11.41 [645 x 645 x 290]	23.60 [52.04]	—	—	—	PDF

Notes: Subpanels must be ordered separately.

Dimensions in inches [millimeters].

Weight in pounds [kilograms].

Heartland Series – Subpanels



Aluminum Swing Panel Kits

3003H14 aluminum

Includes panel, mounts and screws

**AH1210SPK**

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Aluminum Swing Panel Kits

Part Number	Price	Fits Enclosure Size [HxW]	Drawing Link
AH66SPK	\$52.50	6 x 6 [152 x 152]	PDF
AH86SPK	\$54.00	8 x 6 [203 x 152]	PDF
AH108SPK	\$59.00	10 x 8 [254 x 203]	PDF
AH1210SPK	\$63.00	12 x 10 [305 x 254]	PDF
AH1412SPK	\$68.00	14 x 12 [356 x 305]	PDF
AH1614SPK	\$73.00	16 x 14 [406 x 356]	PDF
AH88SPK	Retired	8 x 8 [203 x 203]	PDF
AH1816SPK	\$78.00	18 x 16 [457 x 406]	PDF
AH2016SPK	\$121.00	20 x 16 [508 x 406]	PDF
AH1010SPK	\$85.00	10 x 10 [254 x 254]	PDF
AH2424SPK	\$88.00	24 x 24 [610 x 610]	PDF

Note: Dimensions in inches [millimeters].

Heartland Series – Enclosure Accessories



AttaBox
A ROBROY ENCLOSURES™ BRAND



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Heartland Series – Enclosure Latch Kits

Part Number	Price	Description
<u>AHLKSS</u>	\$15.25	latch, replacement, quick-release, 304 stainless steel. Package of 2.
<u>AHLK</u>	\$11.00	latch, replacement, quick-release, polycarbonate. Package of 2.



[AHLKSS](#)



[AHLK](#)

Heartland Series – Enclosure Accessory Kit

Part Number	Price	Description
<u>AHAK</u>	\$14.00	mounting feet kit, polycarbonate. Includes (4) mounting feet and mounting hardware.



[AHAK](#)

Heartland Series – Enclosure Pole Mount Kits

Part Number	Price	For Pole Diameter	Fits Enclosure Width
<u>PM6-8</u>	\$72.00	3.00 - 12.00 [76 - 305]	6.00 - 8.00 [152 - 203]
<u>PM10-12</u>	\$78.00		10.00 - 12.00 [254 - 305]
<u>PM14-16</u>	\$84.00		14.00 - 16.00 [356 - 406]
<u>PM18-24</u>	\$98.00		18.00 - 24.00 [457 - 610]

Note: Dimensions in inches [millimeters].



[PM14-16](#)

Heartland Series – Enclosure Accessories

Part Number	Price	Description
<u>AHSNK</u>	\$23.00	slot nut kit, #10-32 UNF x 0.375in, Phillips pan head, zinc plated steel. Package of 2. Includes screw and galvanized steel slot nut.
<u>AHTSKSS</u>	\$11.00	thumb screw, replacement, #10-32 UNF x 0.375in, stainless steel. Package of 2. Nylon washer included.
<u>AHTSKAL</u>	\$8.00	thumb screw, replacement, #10-32 UNF x 0.375in, aluminum. Package of 2. Nylon washer included.
<u>RE2PKTBS</u>	Retired	trilobular self-tapping screw, replacement, #10-14 x 0.375in, Phillips pan head, aluminum. Package of 2.



[AHSNK](#)



[AHTSKSS](#)



[AHTSKAL](#)



Heartland Series – Enclosure Swing Panel Mounts

Part Number	Price	Description
<u>AHSPM</u>	\$32.50	AttaBox Heartland series swing panel bracket, package of 4. For use with Heartland series enclosures. Mounting screws included.



[AHSPM](#)

Heartland Series – Enclosure Accessories

Part Number	Price	Description
<u>REAH-V60</u>	\$16.25	vent, 60mm, polycarbonate. Maintains NEMA 3R rating.
<u>REAH-V80</u>	\$21.50	vent, 80mm, polycarbonate. Not UL rated, Enclosure is NEMA 1 when vent is installed
<u>REAVP12</u>	\$47.00	vent gland, 12mm, polycarbonate. Not UL rated, Enclosure is NEMA 1 when vent is installed



[REAH-V60](#)



[REAH-V80](#)



[REAVP12](#)