

BONDHUS® Wrenches

HexPro™ Pivot Head Wrenches


Bondhus HexPro™ Pivot Head Wrenches are a staple in any toolbox and allow for maximum leverage with minimum space. The pivoting head works from 90° to 270° and eliminates the need for constant removal and repositioning of the tool during use. Working in tight spaces against an obstruction is no problem for these wrenches.

Features

- Fits imperial/metric hex, and Torx screws
- Available in 25 sizes to cover most fastener heads
- Heat-treated high-quality industrial tool steel
- Long handles for extra reach
- Matte chrome finish to prevent corrosion




HEX•PRO™



Small, Strong Joints



Pivot Head



Forged Hinges



Sturdy Pouch

HexPro™ Pivot Head Wrench Sets						
Part Number	Number of Pieces	Part Image	Tip Type	Tip Size	Set Includes	Price
<u>BH00010</u>	6		External hex Metric	3mm 4mm 5mm 6mm 8mm 10mm	(6) external hex pivot head wrenches (3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) fold-up pouch	\$58.50
<u>BH00017</u>	8		External hex Imperial	1/8in 9/64in 5/32in 3/16in 7/32in 1/4in 5/16in 3/8in	(8) external hex pivot head wrenches (1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) fold-up pouch	\$70.50
<u>BH00015</u>	6		Torx	T25 T27 T30 T40 T45 T50	(6) torx pivot head wrenches (T25, T27, T30, T40, T45, T50), (1) fold-up pouch	\$66.00
<u>BH00019</u>	5		Torx	T15 T20 T25 T27 T30	(5) torx pivot head wrenches (T15, T20, T25, T27, T30), (1) fold-up pouch	\$54.00