

# Commander Series Polycarbonate Pushbutton Enclosures

NEMA 1, 3R, 4X, 6P, and 12 with Lift-off Cover



## Applications

AttaBox offers an all-polycarbonate product with blank covers or a choice of one- or two-hole pushbutton openings for both 22mm and 30mm hardware. These enclosures include the external flush wall design, unobstructed internal sidewalls, polycarbonate cover screws, and watertight seal.



[COPC432](#)



[COPC1PB](#)



[COPC2PB](#)

## Construction

- High impact-resistant polycarbonate, gray in color with gloss finish
- Poured-in-place seamless gasket for water-tight and dust-tight seal
- Mounting wells located under the cover/ outside the gasket area
- Removable cover with polycarbonate screws (provided). Torque cover screws to 16 -20 lb-in (1.8-2.2 N·m)
- Rounded edges help to prevent collection of dust and debris
- Available with 22mm or 30mm pushbutton holes, or blank cover

## Listings

- UL/cUL File # E64358
- NEMA Ratings 1, 3R, 4X, 6P, and 12
- [UL508A, UL50 and UL50e]
- IEC 60529 Ratings IP66, IP68
- Temperature Range -20°F to +240°F [-29°C to +115°C]
- Flammability Rating UL94-5VA
- Certifications cULus, IEC, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



### Polycarbonate Pushbutton Enclosures – Commander Series NEMA 1, 3R, 4X, 6P, and 12

| Part Number                      | Price   | # Holes | Pushbutton Size | Enclosure Size H x W x D           |
|----------------------------------|---------|---------|-----------------|------------------------------------|
| <u><a href="#">COPC432</a></u>   | \$59.00 | 0       | —               | 4.34 x 3.16 x 2.79 [110 x 80 x 71] |
| <u><a href="#">COPC533</a></u>   | \$61.00 | 0       | —               | 5.12 x 3.16 x 3.54 [130 x 80 x 90] |
| <u><a href="#">COPC1PB</a></u>   | \$64.00 | 1       | 30mm            | 4.34 x 3.16 x 2.79 [110 x 80 x 71] |
| <u><a href="#">COPC2PB</a></u>   | \$70.00 | 2       | 30mm            | 5.12 x 3.16 x 3.54 [130 x 80 x 90] |
| <u><a href="#">COPC1PB22</a></u> | \$64.00 | 1       | 22mm            | 4.34 x 3.16 x 2.79 [110 x 80 x 71] |
| <u><a href="#">COPC2PB22</a></u> | \$70.00 | 2       | 22mm            | 5.12 x 3.16 x 3.54 [130 x 80 x 90] |

Dimensions in inches [millimeters].

# Commander Series Polycarbonate Pushbutton Enclosures

NEMA 1, 3R, 4X, 6P, and 12



[YW-COPC1PB22](#)

## Applications

AttaBox offers an all-polycarbonate product with blank covers or a choice of one- or two-hole pushbutton openings for both 22mm and 30mm hardware. These enclosures include the external flush wall design, unobstructed internal sidewalls, cover screws, and watertight seal.

## Construction

- High impact-resistant polycarbonate, gloss finished black base with a yellow lid
- Poured-in-place seamless gasket for water-tight and dust-tight seal
- Mounting wells located under the cover/ outside the gasket area
- Removable cover with polycarbonate screws (provided). Torque cover screws to 16 -20 lb-in [1.8-2.2 N·m]
- Rounded edges help to prevent collection of dust and debris
- Available with 22mm or 30mm pushbutton holes, or blank cover

## Listings

- UL/cUL File # E319779
- NEMA Ratings 1, 3R, 4X, 6P, and 12 [UL508A, UL50 and UL50e]
- IEC 60529 Ratings IP68
- Temperature Range -20°F to +240°F [-29°C to +115°C]
- Flammability Rating UL94-5VA
- Certifications cULus, IEC, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated



### Polycarbonate Pushbutton Enclosures – Commander Series NEMA 1, 3R, 4X, 6P, 12



| Part Number                         | Price   | # Holes | Pushbutton Size (mm) | Enclosure Size H x W x D           | Drawing Links              |
|-------------------------------------|---------|---------|----------------------|------------------------------------|----------------------------|
| <u><a href="#">YW-COPC1PB22</a></u> | \$79.00 | 1       | 22                   | 4.34 x 3.16 x 2.79 [110 x 80 x 71] | <u><a href="#">PDF</a></u> |
| <u><a href="#">YW-COPC1PB</a></u>   | \$79.00 | 1       | 30                   | 4.34 x 3.16 x 2.79 [110 x 80 x 71] | <u><a href="#">PDF</a></u> |
| <u><a href="#">YW-COPC2PB22</a></u> | \$86.00 | 2       | 22                   | 5.12 x 3.16 x 3.54 [130 x 80 x 90] | <u><a href="#">PDF</a></u> |
| <u><a href="#">YW-COPC2PB</a></u>   | \$86.00 | 2       | 30                   | 5.12 x 3.16 x 3.54 [130 x 80 x 90] | <u><a href="#">PDF</a></u> |

Dimensions in inches [millimeters].

# Commander Series Polycarbonate Pushbutton Enclosures


NEMA 1, 3R, 4X, 6P, and 12 with Lift-off Cover

## Dimensions





1PB-22/2PB-22  
HOLE DETAIL

PB HOLE ARRANGEMENTS




SINGLE PB-22

DOUBLE PB-22



1PB/2PB  
HOLE DETAIL

PB HOLE ARRANGEMENTS



SINGLE PB

DOUBLE PB