

# **DINnectors** Accessories


## Steel DIN Rails Features

### 35mm wide

- Available in 1-meter lengths
- 7.5 mm-high rails primarily used to mount terminal blocks, relays, timers and small PLCs such as the BRX, CLICK, DirectLogic and Productivity series. 15mm-high rails for mounting larger and heavier components such as contactors and larger PLCs

### 15mm wide

- Available in 1-meter lengths
- DN-R15S1 exclusively for mounting mini terminal blocks such as the DN-M10-A



| Steel DIN Rails Specifications       |   |     |         |  |     |         |  |     |         |
|--------------------------------------|---|-----|---------|--|-----|---------|--|-----|---------|
|                                      | Part Number   | Qty | Price   | Part Number  | Qty | Price   | Part Number  | Qty | Price   |
| <b>DIN Rail</b>                      | <a href="#"><u>DN-R35S1</u></a>   | 10  | \$39.00 | <a href="#"><u>DN-R35HS1</u></a>   | 10  | \$68.00 | <a href="#"><u>DN-R15S1</u></a>  | 10  | \$36.00 |
|                                      | <a href="#"><u>DN-R35S1-2</u></a>   | 2   | \$11.00 | <a href="#"><u>DN-R35HS1-2</u></a>   | 2   | \$16.50 | <a href="#"><u>DN-R15S1-2</u></a>  | 2   | \$10.00 |
| <b>Description</b>                   | DINnectors DIN rail, slotted, 35mm, 7.5mm height, 1m length, plated steel. Package of 10. |     |         | DINnectors DIN rail, slotted, 35mm, 15mm height, 1m length, plated steel. Package of 10. |     |         | DINnectors DIN rail, slotted, 15mm, 5.5mm height, 1m length, plated steel. Package of 2. |     |         |
| <b>Plating</b>                       | Zinc-plated and chromated   |     |         |  |     |         |  |     |         |
| <b>International Standards</b>       | EN 60715, RoHs  |     |         |  |     |         |  |     |         |
| <b>Suggested Mounting Screw Type</b> | M6  |     |         | M6   |     |         | M4   |     |         |


## Aluminum DIN Rail Features

### 35mm wide

- Non-anodized finish
- Zinc plating and passivation (minimum thickness 6 microns)
- Lightweight, easy to cut and deburr
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in 1-meter lengths

### 35mm wide raised

- Non-anodized finish
- Zinc plating and passivation (minimum thickness 6 microns)
- Enables users to raise terminal blocks 2¼" above the back panel
- Terminal blocks only
- Available in 1-meter lengths
- Bushing or grommet recommended for wire access hole (example Heyco UB-875 not sold by ADC)




| Aluminum DIN Rails Specifications    |  |     |         |   |     |         |
|--------------------------------------|--|-----|---------|---|-----|---------|
|                                      | Part Number  | Qty | Price   | Part Number   | Qty | Price   |
| <b>DIN Rail</b>                      | <a href="#"><u>DN-R35SAL1</u></a>  | 10  | \$60.00 | <a href="#"><u>DN-R35SAL2-2</u></a>   | 2   | \$38.00 |
|                                      | <a href="#"><u>DN-R35SAL1-2</u></a>  | 2   | \$16.00 |   |     |         |
| <b>Description</b>                   | DINnectors DIN rail, slotted, 35mm, 10mm height, 1m length, aluminum. Package of 10. |     |         | DINnectors DIN rail, slotted, 2in raised 35mm, 7.5mm height, 1m length, aluminum. Package of 2. |     |         |
| <b>Plating</b>                       | Galvanic zinc plating, non-anodized finish   |     |         |   |     |         |
| <b>International Standards</b>       | DIN 50960, RoHs  |     |         |   |     |         |
| <b>Suggested Mounting Screw Type</b> | #10-32 or M5   |     |         |   |     |         |

# DINnectors<sup>®</sup> Accessories


## Dimensions

mm [inches]


**DN-R35S1**




**DN-R35HS1-2**






**DN-R15S1**



**DN-R35SAL1**  
**DN-R35SAL1-2**



**DN-R35SAL2-2**



# **DINnectors** Accessories


## DIN rail support brackets

- Angled support brackets raise and tilt mounting rails 30 degrees from mounting surface for easier wiring
- [DN-ASB1](#) plated steel support bracket
- [DN-ASB2-10](#) cold-rolled steel treated with galvanic zinc plating and passivation

## DIN rail mounting clips

- Snap small devices not made for mounting onto 35mm DIN rails
- Zinc plated steel

| DIN Rail Support Brackets and Mounting Clips |   |     |          |
|--|---|-----|----------|
| Part Number                                  | Description   | Qty | Price    |
| <a href="#">DN-ASB1</a>                      | 30° angled DIN rail support bracket (M6-1.0 screws not included)            | 50  | \$107.00 |
| <a href="#">DN-ASB2-10</a>                   | 30° angled DIN rail support bracket (M6-1.0 screws included)                | 10  | \$18.00  |
| <a href="#">DN-SSB25-10</a>                  | 1" (25mm) DIN rail support bracket (M6-1.0 screws included)                 | 10  | \$24.50  |
| <a href="#">DN-SSB50-10</a>                  | 2" (50mm) DIN rail support bracket (M6-1.0 screws included)                 | 10  | \$25.50  |
| <a href="#">DN-SSB70-10</a>                  | 2.75" (70mm) DIN rail support bracket (M6-1.0 screws included)              | 10  | \$32.00  |
| <a href="#">DN-SSB90-10</a>                  | 3.5" (90mm) DIN rail support bracket (M6-1.0 screws included)               | 10  | \$34.50  |
| <a href="#">DN-CLIP-FM4</a>                  | DIN rail mounting clip with M4 x 0.7 mm threaded hole (Screws not included) | 40  | \$66.00  |
| <a href="#">DN-CLIP-FM4-5</a>                |   | 5   | \$9.50   |
| <a href="#">DN-CLIP-FM5</a>                  | DIN rail mounting clip with M5 x 0.8 mm threaded hole (Screws not included) | 40  | \$66.00  |
| <a href="#">DN-CLIP-FM5-5</a>                |   | 5   | \$9.50   |




**DN-ASB1****DN-ASB2-10****DN-SSB25-10****DN-SSB50-10****DN-SSB70-10****DN-SSB90-10****DN-CLIP-FM4**  
**DN-CLIP-FM4-5****DN-CLIP-FM5**  
**DN-CLIP-FM5-5**

# DINnectors® Accessories

## DIN Rail Support Brackets and Mounting Clips



### Dimensions

mm [inches]



| DIN Rail Support Brackets |                      |                      |
|---------------------------|----------------------|----------------------|
| Part Number               | DIM A<br>mm [inches] | DIM B<br>mm [inches] |
| <b>DN-SSB25-10</b>        | 15.0 [0.59]          | 25.0 [0.98]          |
| <b>DN-SSB50-10</b>        | 40.0 [1.58]          | 50.0 [1.97]          |
| <b>DN-SSB70-10</b>        | 60.0 [2.36]          | 70.0 [2.76]          |
| <b>DN-SSB90-10</b>        | 80.0 [3.15]          | 90.0 [3.54]          |

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings



# DINnectors® Accessories

## Jumpers

Multi-pole jumper bars for DINnector terminal blocks




**DN-12JL14B-A**

| Multi-pole Jumper Bars        |     |          |            |        |     |                    |                         |                                    |                         |
|-------------------------------|-----|----------|------------|--------|-----|--------------------|-------------------------|------------------------------------|-------------------------|
| Part Number                   | Qty | Price    | # of Poles | Rating |     | Tightening Torque  | Insulation Color        | For Use With Terminal Block Series |                         |
|                               |     |          |            | (V)    | (A) |                    |                         |                                    |                         |
| <b>Screw-down Connection</b>  |     |          |            |        |     |                    |                         |                                    |                         |
| <a href="#">DN-2J6</a>        | 100 | \$76.00  | 2          | 600    | 65  | 0.5 Nm [4.4 Lb-In] | -                       | <a href="#">DN-T6</a>              |                         |
| <a href="#">DN-3J6</a>        | 100 | \$132.00 | 3          | 600    | 65  |                    | -                       |                                    |                         |
| <a href="#">DN-4J6</a>        | 100 | \$169.00 | 4          | 600    | 65  |                    | -                       |                                    |                         |
| <a href="#">DN-55J6</a>       | 1   | \$26.50  | 55         | 600    | 65  |                    | -                       |                                    |                         |
| <a href="#">DN-24J8</a>       | 5   | \$41.00  | 24         | 600    | 50  | 0.6 Nm [5.3 lb-in] | Green                   | <a href="#">DN-T8</a>              |                         |
| <b>Push-in Connection</b>     |     |          |            |        |     |                    |                         |                                    |                         |
| <a href="#">DN-2J2Y</a>       | 100 | \$43.00  | 2          | 600    | 25  | -                  | Orange                  | <a href="#">DN-T12-A</a>           |                         |
| <a href="#">DN-2J2YMN</a>     | 25  | \$13.00  | 2          | 600    | 25  |                    | Orange                  | <a href="#">DN-EMX</a>             |                         |
| <a href="#">DN-3J2Y</a>       | 100 | \$62.00  | 3          | 600    | 25  |                    | Orange                  | <a href="#">DN-Q12-A</a>           |                         |
| <a href="#">DN-3J2YMN</a>     | 25  | \$18.00  | 3          | 600    | 25  |                    | Orange                  | <a href="#">DN-QD12-A</a>          |                         |
| <a href="#">DN-24J2Y</a>      | 5   | \$28.00  | 24         | 600    | 25  |                    | Orange                  | <a href="#">DN-QEMX</a>            |                         |
| <a href="#">DN-24J2YMN</a>    | 5   | \$28.00  | 24         | 600    | 25  |                    | Orange                  | <a href="#">DN-QKBD12-A</a>        |                         |
| <a href="#">DN-2J4Y</a>       | 100 | \$46.00  | 2          | 600    | 25  |                    | Yellow                  | <a href="#">DN-T10-A</a>           |                         |
| <a href="#">DN-2J4YMN</a>     | 25  | \$14.50  | 2          | 600    | 25  |                    | Yellow                  |                                    |                         |
| <a href="#">DN-3J4Y</a>       | 100 | \$74.00  | 3          | 600    | 25  |                    | Yellow                  |                                    |                         |
| <a href="#">DN-3J4YMN</a>     | 25  | \$22.00  | 3          | 600    | 25  |                    | Yellow                  |                                    |                         |
| <a href="#">DN-24J4Y</a>      | 5   | \$29.50  | 24         | 600    | 25  |                    | Yellow                  |                                    |                         |
| <a href="#">DN-2JL14-A</a>    | 100 | \$67.00  | 2          | 300    | 20  |                    | -                       | Red                                | <a href="#">DN-TL-A</a> |
| <a href="#">DN-2JL14-AMN</a>  | 25  | \$15.00  | 2          | 300    | 20  | Red                |                         |                                    |                         |
| <a href="#">DN-2JL14B-A</a>   | 100 | \$67.00  | 2          | 300    | 20  | Blue               |                         |                                    |                         |
| <a href="#">DN-2JL14B-AMN</a> | 25  | \$15.00  | 2          | 300    | 20  | Blue               |                         |                                    |                         |
| <a href="#">DN-3JL14-A</a>    | 100 | \$99.00  | 3          | 300    | 20  | Red                |                         |                                    |                         |
| <a href="#">DN-3JL14-AMN</a>  | 25  | \$23.00  | 3          | 300    | 20  | Red                |                         |                                    |                         |
| <a href="#">DN-3JL14B-A</a>   | 100 | \$99.00  | 3          | 300    | 20  | Blue               |                         |                                    |                         |
| <a href="#">DN-3JL14B-AMN</a> | 25  | \$23.00  | 3          | 300    | 20  | Blue               |                         |                                    |                         |
| <a href="#">DN-12JL14-A</a>   | 10  | \$26.50  | 12         | 300    | 20  | Red                |                         |                                    |                         |
| <a href="#">DN-12JL14B-A</a>  | 10  | \$26.50  | 12         | 300    | 20  | Blue               |                         |                                    |                         |
| <a href="#">DN-12JFE</a>      | 10  | \$60.00  | 12         | 300    | 25  | Blue               |                         | <a href="#">DN-FE4</a>             |                         |
| <a href="#">DN-2J6Y</a>       | 100 | \$60.00  | 2          | 600    | 30  | Green              |                         | <a href="#">DN-Q8-A</a>            |                         |
| <a href="#">DN-2J6YMN</a>     | 25  | \$15.00  | 2          | 600    | 30  | Green              |                         |                                    |                         |
| <a href="#">DN-3J6Y</a>       | 100 | \$84.00  | 3          | 600    | 30  | Green              | <a href="#">DN-Q8-A</a> |                                    |                         |
| <a href="#">DN-3J6YMN</a>     | 25  | \$23.50  | 3          | 600    | 30  | Green              |                         |                                    |                         |
| <a href="#">DN-12J6Y</a>      | 10  | \$35.50  | 12         | 600    | 30  | Green              | <a href="#">DN-Q8-A</a> |                                    |                         |


## Dimensions

mm [inches]


### DN-24J8




### DN-xJ2Y / DN-xJ2YMN




### DN-xJ4Y / DN-xJ4YMN




### DN-xJL14 / DN-xJL14x-AMN, DN-xJ14x-A



### DN-12JFE



### DN-xJ6Y / DN-xJ6YMN



# DINnectors® Accessories

## Modifying a DN-24J8 jumper bar to the required number of poles

1) Place the insulating part into the jumper bar and insert screws, based on number of poles required.  
(For instance, in the following example, 5 poles are required). Click into place.

2) Using a cutting tool, cut the insulating part at the edge of the jumper bar (see below).

3) Hold the metal jumper bar and insulating jumper with two hands, placing fingers to the left and right of the pole you wish to cut, repeatedly flexing up and down (1 or 2 times should be sufficient) until the jumper bar and insulating jumper break in two.

4) Remove the small remaining piece of jumper (see below). This is important to ensure appropriate insulation distance in the case of contiguously applied jumpers in sequence. This step also facilitates the placement of a separator terminal if the bridge is positioned as the last terminal of a group.

5) The jumpers now are ready to be screwed onto DN-T8 series terminal blocks.

## Jumper Cutting Tools

Jumper cutting tools maintain protective covering.

| Jumper Cutting Tools              |  |     |          |
|-----------------------------------|--|-----|----------|
| Part Number                       | Description  | Qty | Price    |
| <a href="#"><u>DN-J2CUT</u></a>   | DINnector jumper cutting tool, for use with DN-2J2Y, DN-3J2Y and DN-24J2Y jumpers.   | 1   | \$79.00  |
| <a href="#"><u>DN-J4CUT</u></a>   | DINnector jumper cutting tool, for use with DN-2J4Y, DN-3J4Y and DN-24J4Y jumpers.   | 1   | \$79.00  |
| <a href="#"><u>DN-J6CUT</u></a>   | DINnector jumper cutting tool, for use with DN-12J6Y jumpers.  | 1   | \$118.00 |
| <a href="#"><u>DN-JL14CUT</u></a> | DINnector jumper cutting tool, for use with DN-12JL14-A and DN-12JL14B-A jumpers.  | 1   | \$112.00 |
| <a href="#"><u>DN-JXCUT</u></a>   | DINnector jumper cutting tool, for use with DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE and DN-JFEDIE dies.   | 1   | \$76.00  |
| <a href="#"><u>DN-JFECUT</u></a>  | DINnector jumper cutting tool, for use with DN-12JFE jumpers.  | 1   | \$92.00  |
| <a href="#"><u>DN-JKIT</u></a>    | DINnector cutting tool kit for DN series jumpers. Includes (1) DN-JXCUT cutting tool, (5) dies (DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE, and DN-JFEDIE).  | 1   | \$313.00 |
| <a href="#"><u>DN-TOOL2</u></a>   | DINnector tool kit, for use with DN series terminal blocks, includes (1) spring opening tool for DN-Q series screwless terminal blocks and (1) jumper removal tool for J2, J4, J6, and JL14 jumpers. | 1   | \$11.50  |



**DN-J2CUT**



**DN-J4CUT**



**DN-JKIT**



**DN-TOOL2**

| Replacement Dies                  |   |          |
|-----------------------------------|---|----------|
| Part Number                       | Description   | Price    |
| <a href="#"><u>DN-J2DIE</u></a>   | DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J2CUT or DN-JXCUT.   | \$118.00 |
| <a href="#"><u>DN-J4DIE</u></a>   | DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J4CUT or DN-JXCUT.   | \$118.00 |
| <a href="#"><u>DN-JFEDIE</u></a>  | DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JFECUT or DN-JXCUT.  | \$92.00  |
| <a href="#"><u>DN-J6DIE</u></a>   | DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J6CUT or DN-JXCUT.   | \$118.00 |
| <a href="#"><u>DN-JL14DIE</u></a> | DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JL14CUT or DN-JXCUT. | \$118.00 |




# DINnectors® Accessories

## Terminal Plugs



DN-xxPLUG / DN-xxPLUGMN



| Accessories – Terminal Plugs |   |          |                             |     |         |                 |                |
|------------------------------|---|----------|-----------------------------|-----|---------|-----------------|----------------|
| Plugs* Part Number           | Qty   | Price    | Plugs* Part Number          | Qty | Price   | Number of Poles | Length mm [in] |
| <a href="#">DN-2PLUG</a>     | 200   | \$115.00 | <a href="#">DN-2PLUGMN</a>  | 10  | \$7.25  | 2               | 10.2 [0.40]    |
| <a href="#">DN-3PLUG</a>     | 200   | \$177.00 | <a href="#">DN-3PLUGMN</a>  | 10  | \$11.50 | 3               | 15.2 [0.60]    |
| <a href="#">DN-4PLUG</a>     | 100   | \$118.00 | <a href="#">DN-4PLUGMN</a>  | 10  | \$14.50 | 4               | 20.3 [0.80]    |
| <a href="#">DN-5PLUG</a>     | 100   | \$136.00 | <a href="#">DN-5PLUGMN</a>  | 10  | \$18.00 | 5               | 25.4 [1.00]    |
| <a href="#">DN-6PLUG</a>     | 100   | \$176.00 | <a href="#">DN-6PLUGMN</a>  | 10  | \$18.00 | 6               | 30.5 [1.20]    |
| <a href="#">DN-7PLUG</a>     | 50  | \$92.00  | <a href="#">DN-7PLUGMN</a>  | 5   | \$14.50 | 7               | 35.6 [1.40]    |
| <a href="#">DN-8PLUG</a>     | 50  | \$117.00 | <a href="#">DN-8PLUGMN</a>  | 5   | \$14.50 | 8               | 40.6 [1.60]    |
| <a href="#">DN-9PLUG</a>     | 50  | \$128.00 | <a href="#">DN-9PLUGMN</a>  | 5   | \$15.00 | 9               | 45.7 [1.80]    |
| <a href="#">DN-10PLUG</a>    | 50  | \$136.00 | <a href="#">DN-10PLUGMN</a> | 5   | \$17.00 | 10              | 50.8 [2.00]    |
| <a href="#">DN-11PLUG</a>    | 50  | \$161.00 | <a href="#">DN-11PLUGMN</a> | 5   | \$19.50 | 11              | 55.9 [2.20]    |
| <a href="#">DN-12PLUG</a>    | 50  | \$176.00 | <a href="#">DN-12PLUGMN</a> | 5   | \$20.00 | 12              | 61.0 [2.40]    |
| Terminal Plugs Ratings       |   |          |                             |     |         |                 |                |
| <b>Voltage/Current</b>       | 300V, 12A   |          |                             |     |         |                 |                |
| <b>Wire Gauge</b>            | 14–22 AWG, CU only  |          |                             |     |         |                 |                |
| <b>Torque</b>                | Tightening Torque: 0.51 N·m [4.5 lb·in]   |          |                             |     |         |                 |                |
| <b>Usage Temperature</b>     | Ambient air temperature: -20 to 105°C [-4 to 221°F]<br>Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F] |          |                             |     |         |                 |                |
| <b>Agency Approvals</b>      | UL file #: E179129  |          |                             |     |         |                 |                |


Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

\* DN-xxPLUGs fit all DN-EMXxx & DN-QEMXxx plug-in terminal blocks

## Disconnect Blade




DN-DIS-BLADE  
DN-DIS-BMN







| Disconnect Blade             |   |     |         |
|------------------------------|---|-----|---------|
| Part Number                  | Description   | Qty | Price   |
| <a href="#">DN-DIS-BLADE</a> | Terminal block disconnect blade for DN-FE2, DN-FE4, DN-DIS2 and DN-DIS4 | 50  | \$36.00 |
| <a href="#">DN-DIS-BMN</a>   |   | 10  | \$9.75  |

## End Brackets



| End Brackets                 |  |          |
|------------------------------|--|----------|
| Part Number                  | Description  | Price    |
| <a href="#">DN-EB15</a>      | DINnecter snap-on end bracket, 7mm wide. Package of 100. For use with 15mm DIN rail.   | \$108.00 |
| <a href="#">DN-EB15MN</a>    | DINnecter snap-on end bracket, 7mm wide. Package of 20. For use with 15mm DIN rail.    | \$25.50  |
| <a href="#">DN-EB35</a>      | DINnecter screw-down end bracket, 9mm wide. Package of 50. For use with 35mm DIN rail. | \$67.00  |
| <a href="#">DN-EB35MN</a>    | DINnecter screw-down end bracket, 9mm wide. Package of 20. For use with 35mm DIN rail. | \$31.50  |
| <a href="#">DN-EB35-A</a>    | DINnecter screw-down end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail. | \$47.50  |
| <a href="#">DN-EB35-A-10</a> | DINnecter screw-down end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail. | \$12.00  |
| <a href="#">DN-QEB35</a>     | DINnecter snap-on end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.    | \$42.50  |
| <a href="#">DN-QEB35-10</a>  | DINnecter snap-on end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.    | \$11.50  |



For more information on accessories, see the "DINnectors Accessories" section of this section.

# **DINnectors** Accessories

## End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

| DINnectors End Covers        |   |         |
|------------------------------|---|---------|
| Part Number                  | Description   | Price   |
| <a href="#">DN-EC1210</a>    | DINnector terminal block end cover, gray. Package of 100. For use with DN-T12 or DN-T10 series terminal blocks.   | \$43.00 |
| <a href="#">DN-EC1210MN</a>  | DINnector terminal block end cover, gray. Package of 25. For use with DN-T12 or DN-T10 series terminal blocks.    | \$14.50 |
| <a href="#">DN-EC86</a>      | DINnector terminal block end cover, gray. Package of 100. For use with DN-T8 or DN-T6 series terminal blocks.     | \$47.00 |
| <a href="#">DN-EC86MN</a>    | DINnector terminal block end cover, gray. Package of 25. For use with DN-T8 or DN-T6 series terminal blocks.      | \$14.50 |
| <a href="#">DN-EC4</a>       | DINnector terminal block end cover, gray. Package of 50. For use with DN-T4 series terminal blocks.               | \$29.50 |
| <a href="#">DN-EC4MN</a>     | DINnector terminal block end cover, gray. Package of 10. For use with DN-T4 series terminal blocks.               | \$5.75  |
| <a href="#">DN-EC1/0</a>     | DINnector terminal block end cover, gray. Package of 50. For use with DN-T1/0 series terminal blocks.             | \$33.50 |
| <a href="#">DN-EC1/0MN</a>   | DINnector terminal block end cover, gray. Package of 10. For use with DN-T1/0 series terminal blocks.             | \$8.00  |
| <a href="#">DN-DEC10</a>     | DINnector terminal block end cover, gray. Package of 50. For use with DN-D10-A series terminal blocks.            | \$31.50 |
| <a href="#">DN-DEC10MN</a>   | DINnector terminal block end cover, gray. Package of 10. For use with DN-D10-A series terminal blocks.            | \$6.00  |
| <a href="#">DN-EC14</a>      | DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14 series terminal blocks.             | \$18.00 |
| <a href="#">DN-EC14S</a>     | DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14S series terminal blocks.            | \$15.00 |
| <a href="#">DN-ECM10</a>     | DINnector terminal block end cover, gray. Package of 100. For use with DN-M10-A series terminal blocks.           | \$43.00 |
| <a href="#">DN-ECM10MN</a>   | DINnector terminal block end cover, gray. Package of 25. For use with DN-M10-A series terminal blocks.            | \$14.50 |
| <a href="#">DN-ECKBD</a>     | DINnector terminal block end cover, gray. Package of 100. For use with DN-KBD12 series terminal blocks.           | \$43.00 |
| <a href="#">DN-ECKBDMN</a>   | DINnector terminal block end cover, gray. Package of 10. For use with DN-KBD12 series terminal blocks.            | \$6.00  |
| <a href="#">DN-EMXM1EC1</a>  | DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block leftside.    | \$15.00 |
| <a href="#">DN-EMXM1EC2</a>  | DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block rightside.   | \$15.00 |
| <a href="#">DN-EMXDVEC1</a>  | DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block leftside.    | \$15.00 |
| <a href="#">DN-EMXDVEC2</a>  | DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block rightside.   | \$15.00 |
| <a href="#">DN-FESEP</a>     | DINnector terminal block end cover, gray. Package of 50. For use with DN-FE and DN-DIS series terminal blocks.    | \$26.50 |
| <a href="#">DN-FESEP-10</a>  | DINnector terminal block end cover, gray. Package of 10. For use with DN-FE and DN-DIS series terminal blocks.    | \$5.25  |
| <a href="#">DN-QEC12</a>     | DINnector terminal block end cover, gray. Package of 50. For use with DN-Q12-A or DN-QG12 series terminal blocks. | \$21.50 |
| <a href="#">DN-QEC12MN</a>   | DINnector terminal block end cover, gray. Package of 10. For use with DN-Q12-A or DN-QG12 series terminal blocks. | \$5.25  |
| <a href="#">DN-QEC10</a>     | DINnector terminal block end cover, gray. Package of 50. For use with DN-Q10-A or DN-QG10 series terminal blocks. | \$21.50 |
| <a href="#">DN-QEC10MN</a>   | DINnector terminal block end cover, gray. Package of 10. For use with DN-Q10-A or DN-QG10 series terminal blocks. | \$5.25  |
| <a href="#">DN-QEC8</a>      | DINnector terminal block end cover, gray. Package of 50. For use with DN-Q8-A or DN-QG8 series terminal blocks.   | \$25.50 |
| <a href="#">DN-QEC8MN</a>    | DINnector terminal block end cover, gray. Package of 10. For use with DN-Q8-A or DN-QG8 series terminal blocks.   | \$5.75  |
| <a href="#">DN-QEC12-1-2</a> | DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-1-2-A series terminal blocks.        | \$15.00 |
| <a href="#">DN-QEC12-2-2</a> | DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-2-2-A series terminal blocks.        | \$16.50 |
| <a href="#">DN-QDEC12</a>    | DINnector terminal block end cover, gray. Package of 25. For use with DN-QD12 series terminal blocks.             | \$16.50 |

## Spacers

Spacers are used to put more space between adjacent blocks.

| DINnectors Spacers           |  |     |         |
|------------------------------|--|-----|---------|
| Part Number                  | Description  | Qty | Price   |
| <a href="#">DN-S1210</a>     | Spacer for DN-T12-A and DN-T10-A series terminal blocks                | 100 | \$51.00 |
| <a href="#">DN-S1210MN</a>   |  | 25  | \$16.00 |
| <a href="#">DN-S86</a>       | Spacer for DN-T8 and DN-T6 series terminal blocks                      | 100 | \$61.00 |
| <a href="#">DN-S86MN</a>     |  | 25  | \$14.00 |
| <a href="#">DN-EMXM1SPA1</a> | Spacer for DN-EMXM1 and DN-QEMXM1 single-level plug-in terminal blocks | 25  | \$13.00 |
| <a href="#">DN-EMXDVSPA1</a> | Spacer for DN-EMXDV and DN-QEMXDV double-level plug-in terminal blocks | 25  | \$14.50 |
| <a href="#">DN-FESPA</a>     | Spacer for DN-FE sockets and DN-DIS disconnects                        | 50  | \$26.50 |
| <a href="#">DN-FESPA-10</a>  |  | 10  | \$5.25  |

## Top Covers








| DINnectors Top Covers     |  |                |     |         |
|---------------------------|--|----------------|-----|---------|
| Part Number               | Description                                  | For Use With   | Qty | Price   |
| <a href="#">DN-C12</a>    | Top cover, clear, printed electrical symbol. | DN-T12-A       | 100 | \$62.00 |
| <a href="#">DN-C12MN</a>  |  |                | 25  | \$14.00 |
| <a href="#">DN-C10</a>    | Top cover, clear, printed electrical symbol. | DN-T10-A       | 100 | \$62.00 |
| <a href="#">DN-C10MN</a>  |  |                | 25  | \$14.00 |
| <a href="#">DN-C86</a>    | Top cover, clear, printed electrical symbol. | DN-T8<br>DN-T6 | 100 | \$62.00 |
| <a href="#">DN-C86MN</a>  |  |                | 25  | \$14.00 |
| <a href="#">DN-DC10</a>   | Top cover, clear, printed electrical symbol. | DN-D10         | 100 | \$60.00 |
| <a href="#">DN-DC10MN</a> |  |                | 25  | \$14.00 |
| <a href="#">DN-MC10</a>   | Top cover, clear, printed electrical symbol. | DN-M10         | 100 | \$64.00 |
| <a href="#">DN-MC10MN</a> |  |                | 25  | \$14.00 |



# DINnectors<sup>®</sup> Accessories









| Part Number                  |                              | Length<br>mm[in]      | Height<br>mm [in] | Thickness<br>mm [in] |
|------------------------------|------------------------------|-----------------------|-------------------|----------------------|
| <a href="#">DN-EC1210</a>    | <a href="#">DN-EC1210MN</a>  | 44 [1.73]             | 35 [1.38]         | 1.5 [0.06]           |
| <a href="#">DN-S1210</a>     | <a href="#">DN-S1210MN</a>   | 55 [2.17]             | 44 [1.73]         |                      |
| <a href="#">DN-EC86</a>      | <a href="#">DN-EC86MN</a>    | 50 [1.97]             | 43 [1.69]         |                      |
| <a href="#">DN-S86</a>       | <a href="#">DN-S86MN</a>     | 55 [2.17]             | 49 [1.93]         |                      |
| <a href="#">DN-EC4</a>       | <a href="#">DN-EC4MN</a>     | 56 [2.21]             | 48 [1.89]         |                      |
| <a href="#">DN-EC1/0</a>     | <a href="#">DN-EC1/0MN</a>   | 62 [2.44]             | 60 [2.36]         |                      |
| <a href="#">DN-DEC10</a>     | <a href="#">DN-DEC10MN</a>   | 72 [2.80]             | 49 [1.93]         |                      |
| <a href="#">DN-EC14</a>      | -                            | 78 [3.08]             | 55 [2.17]         |                      |
| <a href="#">DN-EC14S</a>     | -                            | 55 [2.17]             | 50 [1.97]         |                      |
| <a href="#">DN-ECM10</a>     | <a href="#">DN-ECM10MN</a>   | 32 [1.26]             | 27 [1.06]         |                      |
| <a href="#">DN-ECKBD</a>     | <a href="#">DN-ECKBDMN</a>   | 52 [2.05]             | 34.5 [1.36]       |                      |
| <a href="#">DN-EMXM1EC1</a>  | <a href="#">DN-EMXM1EC2</a>  | as shown on next page |                   |                      |
| <a href="#">DN-EMXDVEC1</a>  | <a href="#">DN-EMXDVEC2</a>  |                       |                   |                      |
| <a href="#">DN-EMXDVSPA1</a> | <a href="#">DN-EMXM1SPA1</a> |                       |                   |                      |
| <a href="#">DN-FESPA</a>     | <a href="#">DN-FESPA-10</a>  |                       |                   |                      |
| <a href="#">DN-FESEP</a>     | <a href="#">DN-FESEP-10</a>  |                       |                   |                      |
| <a href="#">DN-QEC12</a>     | <a href="#">DN-QEC12MN</a>   | 50 [1.97]             | 23 [0.9]          | 1.5 [0.06]           |
| <a href="#">DN-QEC10</a>     | <a href="#">DN-QEC10MN</a>   | 57.4 [2.26]           | 33.6 [1.32]       |                      |
| <a href="#">DN-QEC8</a>      | <a href="#">DN-QEC8MN</a>    | 63 [2.48]             | 38.5 [1.52]       |                      |
| <a href="#">DN-QEC12-1-2</a> | -                            | 68.5 [2.70]           | 28.5 [1.12]       |                      |
| <a href="#">DN-QEC12-2-2</a> | -                            | 87.5 [3.44]           | 28.5 [1.12]       |                      |
| <a href="#">DN-QDEC12</a>    | -                            | 98 [3.86]             | 37 [1.46]         |                      |

**DN-EC1210 (MN), DN-EC86 (MN), DN-EC4 (MN), DN-EC1/0 (MN), DN-ECKBD (MN), DN-S1210 (MN), DN-S86 (MN)**



# **DINnectors** Accessories

## Dimensional Drawings




**DINnectors® Accessories**

## Marking Tags Cross Reference Charts - Screw-type

| <b>DINector Marking Tags Cross Reference - Screw-type</b> |             |              |              |               |                 |
|---|-------------|--------------|--------------|---------------|-----------------|
| <i>Block Type</i>   | <i>DN-L</i> | <i>DN-LA</i> | <i>DN-LT</i> | <i>DN-LAT</i> | <i>DN-EMLBL</i> |
| <i>DN-T12</i>   | -           | X            | X            | -             | -               |
| <i>DN-T10</i>   | X           | -            | X            | -             | -               |
| <i>DN-T8</i>  | X           | -            | X            | -             | -               |
| <i>DN-T6</i>  | X           | -            | X            | -             | -               |
| <i>DN-T4</i>  | X           | -            | X            | -             | -               |
| <i>DN-T1/0</i>  | X           | -            | X            | -             | -               |
| <i>DN-T3/0</i>  | X           | -            | X            | -             | -               |
| <i>DN-D10</i>   | X           | -            | X            | -             | -               |
| <i>DN-D10X</i>  | X           | -            | X            | -             | -               |
| <i>DN-D10LED</i>  | X           | -            | X            | -             | -               |
| <i>DN-D10DR</i>   | X           | -            | X            | -             | -               |
| <i>DN-TL14</i>  | -           | -            | -            | X             | -               |
| <i>DN-THERM</i>   | X           | -            | X            | -             | -               |
| <i>DN-EMXM1</i>   | -           | X            | X            | -             | X               |
| <i>DN-EMXDV</i>   | -           | X            | X            | -             | X               |
| <i>DN-M10</i>   | -           | -            | X            | -             | -               |
| <i>DN-MG10</i>  | -           | -            | X            | -             | -               |
| <i>DN-G10</i>   | X           | -            | X            | -             | -               |
| <i>DN-G8</i>  | X           | -            | X            | -             | -               |
| <i>DN-G6</i>  | X           | -            | X            | -             | -               |
| <i>DN-G4</i>  | X           | -            | X            | -             | -               |
| <i>DN-G1/0</i>  | X           | -            | X            | -             | -               |
| <i>DN-F6</i>  | X           | -            | X            | -             | -               |
| <i>DN-F10</i>   | X           | -            | X            | -             | -               |
| <i>DN-DIS2</i>  | -           | X            | X            | -             | -               |
| <i>DN-DIS4</i>  | X           | -            | X            | -             | -               |
| <i>DN-FE2</i>   | -           | X            | X            | -             | -               |
| <i>DN-FE4</i>   | X           | -            | X            | -             | -               |
| <i>DN-DIS10</i>   | X           | -            | X            | -             | -               |
| <i>DN-KBD12</i>   | -           | X            | X            | -             | -               |

Continued on next page


**DINnectors** Accessories


## Marking Tags Cross Reference Charts - Screwless

| <b>DINector Marking Tags Cross Reference - Screwless</b> |              |              |              |                 |
|--|--------------|--------------|--------------|-----------------|
| <i>Block Type</i>  | <i>DN-QL</i> | <i>DN-LA</i> | <i>DN-LT</i> | <i>DN-EMLBL</i> |
| <i>DN-Q12</i>  | X            | -            | -            | -               |
| <i>DN-Q10</i>  | X            | -            | -            | -               |
| <i>DN-Q8</i>   | X            | -            | -            | -               |
| <i>DN-QD12</i>   | X            | -            | -            | -               |
| <i>DN-Q12-1-2</i>  | X            | -            | -            | -               |
| <i>DN-Q12-1-2L</i>                                       | X            | -            | -            | -               |
| <i>DN-Q12-1-2D</i>                                       | X            | -            | -            | -               |
| <i>DN-QKBD</i>   | X            | -            | -            | -               |
| <i>DN-Q12-2-2</i>  | X            | -            | -            | -               |
| <i>DN-Q12-2-2L</i>                                       | X            | -            | -            | -               |
| <i>DN-Q12-2-2D</i>                                       | X            | -            | -            | -               |
| <i>DN-QEMXM1</i>   | -            | X            | X            | X               |
| <i>DN-QEMXDV</i>   | -            | X            | X            | X               |
| <i>DN-QG12</i>   | X            | -            | -            | -               |
| <i>DN-QG10</i>   | X            | -            | -            | -               |
| <i>DN-QG8</i>  | X            | -            | -            | -               |
| <i>DN-QG12-1-2</i>                                       | X            | -            | -            | -               |
| <i>DN-QG12-2-2</i>                                       | X            | -            | -            | -               |

## Marking Tags

| Marking Tags DN-L Series |                                       |     |         |
|--------------------------|---------------------------------------|-----|---------|
| Part Number              | Marking Sequence                      | Qty | Price   |
| <a href="#">DN-L50</a>   | 1-50                                  | 500 | \$56.00 |
| <a href="#">DN-L100</a>  | 51-100                                | 500 | \$56.00 |
| <a href="#">DN-L150</a>  | 101-150                               | 500 | \$56.00 |
| <a href="#">DN-L200</a>  | 151-200                               | 500 | \$56.00 |
| <a href="#">DN-L250</a>  | 201-250                               | 500 | \$56.00 |
| <a href="#">DN-L300</a>  | 251-300                               | 500 | \$56.00 |
| <a href="#">DN-L350</a>  | 301-350                               | 500 | \$56.00 |
| <a href="#">DN-L400</a>  | 351-400                               | 500 | \$56.00 |
| <a href="#">DN-L450</a>  | 401-450                               | 500 | \$56.00 |
| <a href="#">DN-LB</a>    | Blank                                 | 500 | \$38.00 |
| <a href="#">DN-LS</a>    | L1, L2, L3, L, N, GND, +, -, COM,COM* | 500 | \$56.00 |


**Dimensions**



- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500.
- The DN-L tags fit all DINnectors 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

| Marking Tags DN-LA Series |                                       |     |         |
|---------------------------|---------------------------------------|-----|---------|
| Part Number               | Marking Sequence                      | Qty | Price   |
| <a href="#">DN-LA100</a>  | 1-100                                 | 500 | \$56.00 |
| <a href="#">DN-LA200</a>  | 101-200                               | 500 | \$56.00 |
| <a href="#">DN-LA300</a>  | 201-300                               | 500 | \$56.00 |
| <a href="#">DN-LA400</a>  | 301-400                               | 500 | \$56.00 |
| <a href="#">DN-LAB</a>    | Blank Tags                            | 500 | \$56.00 |
| <a href="#">DN-LAS</a>    | L1, L2, L3, L, N, GND, +, -, COM,COM* | 500 | \$56.00 |


**Dimensions**



- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

| Marking Tags DN-LAT Series  |                                  |     |         |
|-----------------------------|----------------------------------|-----|---------|
| Part Number                 | Marking Sequence                 | Qty | Price   |
| <a href="#">DN-LAT100-A</a> | 1-100                            | 500 | \$49.00 |
| <a href="#">DN-LAT200-A</a> | 101-200                          | 500 | \$49.00 |
| <a href="#">DN-LAT300-A</a> | 201-300                          | 500 | \$49.00 |
| <a href="#">DN-LAT400-A</a> | 301-400                          | 500 | \$49.00 |
| <a href="#">DN-LAT500-A</a> | 401-500                          | 500 | \$49.00 |
| <a href="#">DN-LAT600-A</a> | 501-600                          | 500 | \$49.00 |
| <a href="#">DN-LATB-A</a>   | Blank Tags                       | 500 | \$35.50 |
| <a href="#">DN-LATS-A</a>   | L1, L2, L3, L, N, +, -, COM,COM* | 500 | \$49.00 |


**Dimensions**



- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

| Marking Tags DN-QL Series |                                  |     |         |
|---------------------------|----------------------------------|-----|---------|
| Part Number               | Marking Sequence                 | Qty | Price   |
| <a href="#">DN-QL100</a>  | 1-100                            | 500 | \$42.50 |
| <a href="#">DN-QL200</a>  | 101-200                          | 500 | \$42.50 |
| <a href="#">DN-QL300</a>  | 201-300                          | 500 | \$42.50 |
| <a href="#">DN-QL400</a>  | 301-400                          | 500 | \$42.50 |
| <a href="#">DN-QL500</a>  | 401-500                          | 500 | \$42.50 |
| <a href="#">DN-QLB</a>    | Blank Tags                       | 500 | \$36.00 |
| <a href="#">DN-QLS</a>    | L1, L2, L3, L, N, +, -, COM,COM* | 500 | \$49.00 |

**Dimensions**




- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.



# **DINnectors** Accessories


## Marking Tags continued

| Marking Tags DN-LT Series |                  |     |         |
|---------------------------|------------------|-----|---------|
| Part Number               | Marking Sequence | Qty | Price   |
| <a href="#">DN-LT15</a>   | 1-5              | 100 | \$10.00 |
| <a href="#">DN-LT60</a>   | 6-0              | 100 | \$10.00 |
| <a href="#">DN-LT1</a>    | 1                | 100 | \$10.00 |
| <a href="#">DN-LT2</a>    | 2                | 100 | \$10.00 |
| <a href="#">DN-LT3</a>    | 3                | 100 | \$10.00 |
| <a href="#">DN-LT4</a>    | 4                | 100 | \$10.00 |
| <a href="#">DN-LT5</a>    | 5                | 100 | \$10.00 |
| <a href="#">DN-LT6</a>    | 6                | 100 | \$10.00 |
| <a href="#">DN-LT7</a>    | 7                | 100 | \$10.00 |
| <a href="#">DN-LT8</a>    | 8                | 100 | \$10.00 |
| <a href="#">DN-LT9</a>    | 9                | 100 | \$10.00 |
| <a href="#">DN-LT0</a>    | 0                | 100 | \$10.00 |
| <a href="#">DN-LTBLNK</a> | Unprinted        | 100 | \$10.00 |
| <a href="#">DN-LTA</a>    | A                | 100 | \$10.00 |
| <a href="#">DN-LTB</a>    | B                | 100 | \$10.00 |
| <a href="#">DN-LTC</a>    | C                | 100 | \$10.00 |
| <a href="#">DN-LTD</a>    | D                | 100 | \$10.00 |
| <a href="#">DN-LTE</a>    | E                | 100 | \$10.00 |
| <a href="#">DN-LTF</a>    | F                | 100 | \$10.00 |
| <a href="#">DN-LTG</a>    | G                | 100 | \$10.00 |
| <a href="#">DN-LTH</a>    | H                | 100 | \$10.00 |
| <a href="#">DN-LTI</a>    | I                | 100 | \$10.00 |
| <a href="#">DN-LTJ</a>    | J                | 100 | \$10.00 |
| <a href="#">DN-LTK</a>    | K                | 100 | \$10.00 |
| <a href="#">DN-LTL</a>    | L                | 100 | \$10.00 |
| <a href="#">DN-LTM</a>    | M                | 100 | \$10.00 |
| <a href="#">DN-LTN</a>    | N                | 100 | \$10.00 |
| -                         | -                | -   | -       |
| <a href="#">DN-LTP</a>    | P                | 100 | \$10.00 |
| <a href="#">DN-LTQ</a>    | Q                | 100 | \$10.00 |
| <a href="#">DN-LTR</a>    | R                | 100 | \$10.00 |
| <a href="#">DN-LTS</a>    | S                | 100 | \$10.00 |
| <a href="#">DN-LTT</a>    | T                | 100 | \$10.00 |
| <a href="#">DN-LTU</a>    | U                | 100 | \$10.00 |
| <a href="#">DN-LTV</a>    | V                | 100 | \$10.00 |
| <a href="#">DN-LTW</a>    | W                | 100 | \$10.00 |
| <a href="#">DN-LTX</a>    | X                | 100 | \$10.00 |
| <a href="#">DN-LTY</a>    | Y                | 100 | \$10.00 |
| <a href="#">DN-LTZ</a>    | Z                | 100 | \$10.00 |
| <a href="#">DN-LTGND</a>  | ⊕                | 100 | \$10.00 |
| <a href="#">DN-LTPOS</a>  | +                | 100 | \$10.00 |
| <a href="#">DN-LTNEG</a>  | -                | 100 | \$10.00 |
| <a href="#">DN-LTAC</a>   | ~                | 100 | \$10.00 |
| <a href="#">DN-LTDC</a>   | =                | 100 | \$10.00 |




- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DINnectors support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

**DN-MTA** marking tag adapter



**DN-MTA** dimensions




| Part Number            | Description                                    | Qty | Price   |
|------------------------|--|-----|---------|
| <a href="#">DN-MTA</a> | Marking tag adapter holds up to six DN-LT tags | 50  | \$14.50 |

Note: [DN-MTA](#) adapter does not fit [DN-T12-A](#) terminal blocks.

# DINnectors® Accessories

## Terminal Marking Accessories



**DN-EMLBL1**



**DN-EMLBL2**



**DN-EMLBL3**

| Part Number      | Description            | For Use With  | Qty | Price   |
|------------------|------------------------|---|-----|---------|
| <b>DN-EMLBL1</b> | Blank labels           | DN-EMPEG1 pin protectors for<br>DN-xEMxx plug-in terminal<br>blocks | 100 | \$9.25  |
| <b>DN-EMLBL2</b> | Labels printed 1 – 12  |   | 100 | \$13.00 |
| <b>DN-EMLBL3</b> | Labels printed 13 – 24 |   | 100 | \$13.00 |

## Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

| Part Number  | Description   | Qty | Price  |
|--------------|---|-----|--------|
| <b>DN-MP</b> | Staedtler-Mars marking pen, for use with blank marking tags. Permanent Ink, fine tip. | 1   | \$4.50 |



**Marking pen**

## Wire Marking Accessories



**DN-WMTAG1 wire tags & DN-WM-x wire tag holders**

| Part Number      | Description  | For Use With                 | Qty | Price   |
|------------------|--|------------------------------|-----|---------|
| <b>DN-WMTAG1</b> | Wire tag – blank   | all DN-WM-x wire tag holders | 525 | \$60.00 |
| <b>DN-WM-1</b>   | Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire | <b>DN-WMTAG1</b>             | 200 | \$12.50 |
| <b>DN-WM-2</b>   | Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16–11 AWG wire |                              | 200 | \$12.50 |
| <b>DN-WM-3</b>   | Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire  |                              | 100 | \$8.25  |
| <b>DN-WM-4</b>   | Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire      |                              | 100 | \$7.75  |