

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid



Features

- Ideally suited for mounting printed circuit boards or DIN rail-mounted components.
- Gasketed lid with tongue and groove construction provides protection against oil, dust, and water.
- All hardware is designed to avoid corrosion caused by harsh environments over time.
- Lid screws are self-captivating (lid holes are threaded with the first installation of lid screws).
- Internal features are maximized for mounting options and vary with size:
 - Internal DIN rail mounting tabs molded into most models, except sizes "C" and "D".
 - Threaded (M3) integral brass inserts and/or standoffs (#6 self tapping screws) for P.C. board or subpanel mounting in all except size ("B").
 - Vertical P.C. card guides (for 0.59in [15 mm] thick P.C. boards) are molded in all except size ("B").
- Foot Kits available for sizes 4.72 x 3.54in [120 x 90 mm] 1554FT) and 11.77 x 9.45in [299 x 240 mm] (1554FT-XY)

Construction

- UV-stabilized Polycarbonate for indoor use. (Gray polycarb carries a UL94-5VA rating, while clear and smoked lids carry a UL94V-0 rating.)
- Replaceable gasket is one piece made from high temperature, UL-listed silicone.
 - Sold in pairs
- Light gray finish.
- Lids available as shown or with clear (CL) or smoke clear (SL).

Listings

- Meets NEMA Type 4, 4X, 6, 6P, 12, and 13 ratings which meet and exceed IP ratings up to and including IP68. (Except 1554V size which is 4 and 4X only)
- cUL and UL508A (File # E65324)



NEMA Type 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid

Part Number	Price	Enclosure Size HxWxD	Lid Depth	Lid Color	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1554B2GY	\$11.00	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	Opaque	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1554B2GYCL	\$12.00	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	Clear	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1554B2GYSL	\$12.00	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	Smoke	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1554E2GY	\$17.00	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	Opaque	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554E2GYCL	\$20.75	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	Clear	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554E2GYSL	\$20.75	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	Smoke	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554EE2GY	\$19.75	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	Opaque	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554EE2GYCL	\$21.50	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	Clear	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554EE2GYSL	\$21.50	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	Smoke	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554L2GY	\$19.50	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	Opaque	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554L2GYCL	\$21.50	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	Clear	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554L2GYSL	\$21.50	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	Smoke	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554LA2GY	\$22.00	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	Opaque	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554LA2GYCL	\$27.50	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	Clear	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554LA2GYSL	\$27.50	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	Smoke	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554C2GY	\$15.50	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	Opaque	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554C2GYCL	\$16.75	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	Clear	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554C2GYSL	\$16.75	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	Smoke	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554D2GY	\$16.75	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	Opaque	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554D2GYCL	\$20.25	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	Clear	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554D2GYSL	\$20.25	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	Smoke	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid



Continued from previous page

NEMA Type 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid									
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Lid Color	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1554F2GY	\$19.25	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	Opaque	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554F2GYCL	\$21.00	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	Clear	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554F2GYSL	\$21.00	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	Smoke	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554G2GY	\$22.50	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	Opaque	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554G2GYCL	\$23.50	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	Clear	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554G2GYSL	\$23.50	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	Smoke	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554N2GY	\$21.50	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	Opaque	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554N2GYCL	\$26.50	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	Clear	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554N2GYSL	\$26.50	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	Smoke	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554P2GY	\$27.50	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	Opaque	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554P2GYCL	\$29.00	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	Clear	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554P2GYSL	\$29.00	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	Smoke	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554Q2GY	\$23.50	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	Opaque	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554Q2GYCL	\$28.50	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	Clear	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554Q2GYSL	\$28.50	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	Smoke	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554QA2GY	\$35.50	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	Opaque	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554QA2GYCL	\$37.00	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	Clear	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554QA2GYSL	\$37.00	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	Smoke	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554JL2GY	\$21.50	6.30 x 3.54 x 1.81 [160 x 90 x 46]	15 [0.59]	Opaque	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554JL2GYCL	\$23.50	6.30 x 3.54 x 1.81 [160 x 90 x 46]	15 [0.59]	Clear	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554J2GY	\$23.50	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	Opaque	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554J2GYCL	\$25.00	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	Clear	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554J2GYSL	\$25.00	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	Smoke	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554K2GY	\$25.00	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	Opaque	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554K2GYCL	\$29.00	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	Clear	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554K2GYSL	\$29.00	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	Smoke	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554R2GY	\$35.50	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	Opaque	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554R2GYCL	\$37.00	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	Clear	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554R2GYSL	\$37.00	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	Smoke	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554S2GY	\$32.50	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	Opaque	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554S2GYSL	\$40.00	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	Smoke	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554S2GYCL	\$40.00	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	Clear	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554HL2GY	\$25.00	7.09 x 4.72 x 1.81 [180 x 120 x 46]	15 [0.59]	Opaque	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554HL2GYCL	\$27.00	7.09 x 4.72 x 1.81 [180 x 120 x 46]	15 [0.59]	Clear	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554H2GY	\$27.00	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	Opaque	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554H2GYCL	\$29.00	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	Clear	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554H2GYSL	\$29.00	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	Smoke	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554T2GY	\$35.50	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	Opaque	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554T2GYCL	\$37.00	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	Clear	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554T2GYSL	\$37.00	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	Smoke	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554W2GY	\$32.50	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	Opaque	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554W2GYCL	\$34.50	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	Clear	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid



Table continued from previous page

NEMA Type 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Flat Lid									
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Lid Color	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1554W2GYSL	\$34.50	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	Smoke	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554WA2GY	\$35.00	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	Opaque	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554WA2GYCL	\$41.50	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	Clear	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554WA2GYSL	\$41.50	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	Smoke	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554U2GY	\$32.00	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	Opaque	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1554U2GYCL	\$37.50	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	Clear	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1554U2GYSL	\$37.50	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	Smoke	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1554VAL2GY	\$39.50	9.45 x 6.30 x 2.36 [240 x 160 x 60]	22 [0.87]	Opaque	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VAL2GYCL	\$41.50	9.45 x 6.30 x 2.36 [240 x 160 x 60]	22 [0.87]	Clear	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VA2GY	\$45.50	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	Opaque	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VA2GYCL	\$47.50	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	Clear	PDF	1554VAPL	\$9.00	1554VGASKET	\$4.50
1554VA2GYSL	\$47.50	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	Smoke	PDF	1554VAPL	\$9.00	1554VGASKET	\$4.50
1554VB2GY	\$45.50	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	Opaque	PDF	1554VAPL	\$9.00	1554VGASKET	\$4.50
1554VB2GYCL	\$47.50	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	Clear	PDF	1554VAPL	\$9.00	1554VGASKET	\$4.50
1554VB2GYSL	\$47.50	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	Smoke	PDF	1554VAPL	\$9.00	1554VGASKET	\$4.50
1554X2GY	\$57.00	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	Opaque	PDF	1554XPL	\$11.25	1554VGASKET	\$4.50
1554X2GYCL	\$59.00	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	Clear	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554X2GYSL	\$59.00	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	Smoke	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554XA2GY	\$63.00	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	Opaque	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554XA2GYCL	\$68.00	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	Clear	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554XA2GYSL	\$68.00	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	Smoke	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554Y2GY	\$64.00	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	Opaque	PDF	1554YPL	\$12.75	1554YGASKET	\$9.75
1554Y2GYCL	\$71.00	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	Clear	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1554Y2GYSL	\$71.00	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	Smoke	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1554YA2GY	\$70.00	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	Opaque	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1554YA2GYCL	\$75.00	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	Clear	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1554YA2GYSL	\$75.00	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	Smoke	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75

Note: Dimensions in inches [millimeters].

NEMA Type 4 and 4X Polycarbonate Miniature Cases with Flat Lid



NEMA Type 4 and 4X Polycarbonate Miniature Cases with Flat Lid									
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Lid Color	Drawing Link	Subpanel	Price	Replacement Gaskets*	Price
1554V2GY	\$45.50	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	Opaque	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554V2GYCL	\$47.50	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	Clear	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554V2GYSL	\$47.50	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	Smoke	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00

Note: Dimensions in inches [millimeters].

* Replacement gaskets are sold in pairs.

IP66 ABS Plastic Miniature Cases with Flat Lid



Features

- Ideally suited for mounting printed circuit boards or DIN rail-mounted components.
- Gasketed lid with tongue and groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws. All hardware is designed to avoid corrosion caused by harsh environments over time.
- Lid screws are self-captivating (lid holes are threaded with the first installation of lid screws).
- Internal DIN rail mounting tabs molded into most models, except sizes C and D.
- Threaded (M3) integral brass inserts and/or standoffs (#6 self tapping screws) for P.C. board or subpanel mounting except size ("B").
- Vertical P.C. card guides (for 0.59in [15 mm] thick P.C. boards) are molded except size ("B").
- Foot Kits available for sizes 4.72 x 3.54in [120 x 90 mm] (1554FT) and 11.77 x 9.45in [299 x 240 mm] (1554FT-XY)

Construction

- Molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Replaceable gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs
- Light gray finish.

Listings

- IP66



IP66 ABS Plastic Flat Lid Miniature Cases with Flat Lid								
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Gasket	Price
1554BGY	\$9.75	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1554EEGY	\$15.00	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554EGY	\$12.25	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1554LAGY	\$19.00	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554LGY	\$15.00	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1554CGY	\$11.00	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554DGY	\$12.00	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1554FGY	\$15.00	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554GGY	\$15.25	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1554NGY	\$18.75	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554PGY	\$19.75	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1554QAGY	\$27.00	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554QGY	\$19.50	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1554JLGY	\$18.00	6.30 x 3.54 x 1.81 [160 x 90 x 46]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554JGY	\$18.00	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554KGY	\$19.75	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1554RGY	\$27.00	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554SGY	\$29.00	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554HLGY	\$20.25	7.09 x 4.72 x 1.81 [180 x 120 x 46]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554HGY	\$20.50	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1554TGY	\$27.00	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1554WAGY	\$31.50	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1554WGY	\$25.50	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75

Note: Dimensions in inches [millimeters].

Table continued on next page

IP66 ABS Plastic Miniature Cases with Flat Lid



Table continued from previous page

IP66 ABS Plastic Flat Lid Miniature Cases with Flat Lid								
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Gasket	Price
1554UGY	\$29.50	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1554VALGY	\$35.00	9.45 x 6.30 x 2.36 [240 x 160 x 60]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VAGY	\$37.00	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VBGY	\$37.00	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1554VGY	\$37.00	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	PDF	1554VPL	\$12.00	1554VGASKET	\$4.50
1554XAGY	\$38.50	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554XGY	\$37.50	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1554YAGY	\$41.00	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1554YGY	\$38.50	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
Note: Dimensions in inches [millimeters].								