

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards or DIN rail-mounted components.
- "Styled" lid version has three main advantages: Smooth recessed surface on lid for a membrane keypad/label, standoffs molded in the interior of lid (except for size "B"), (#6 self-tapping screws,) and a more modern look.
- Gasketed lid with two piece tongue and groove construction provides protection against oil, dust, and water.
- UV stabilized for outdoor use.
- Single piece gasket made from high temperature, UL listed silicone (not preinstalled).
 - Sold in pairs
- All hardware is stainless steel to avoid corrosion.
- M4 lid screws are self-captivating (lid holes are threaded with the first installation of lid screws).
- Internal DIN rail mounting tabs molded into most models, except sizes C and D.
- Threaded (M3) integral brass inserts and/or standoffs (#6 self tapping screws) for P.C. board or subpanel mounting except size ("B").
- Vertical P.C. card guides (for 0.59in [15 mm] thick P.C. boards) are molded except size ("B").



Construction

- Polycarbonate
- Finish is light gray (RAL7035).

Listings

- UL 508A Type 4, 4X, 6 and 6P [UL File E63524]
- UL94-5VA
- IP68
- Complies with
 - NEMA T4, 4X, 6 , 6P, 12 and 13
 - IEC 60529, IP68



NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Styled Lid

Part Number	Price	Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1555B2GY	\$11.00	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1555E2GY	\$17.00	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1555EE2GY	\$19.50	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1555L2GY	\$19.25	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555LA2GY	\$22.00	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555C2GY	\$15.50	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1555D2GY	\$16.50	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1555F2GY	\$19.25	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1555G2GY	\$22.50	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1555N2GY	\$21.50	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1555P2GY	\$27.50	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1555Q2GY	\$23.00	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555QA2GY	\$35.00	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555JL2GY	\$23.00	6.30 x 3.54 x 1.81 [160 x 90 x 46]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555J2GY	\$23.00	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555K2GY	\$25.00	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555R2GY	\$35.00	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1555S2GY	\$32.00	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1555HL2GY	\$27.00	7.09 x 4.72 x 1.81 [180 x 120 x 46]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Styled Lid



Table continued from previous page

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Styled Lid								
Part Number	Price	Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1555H2GY	\$27.00	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1555T2GY	\$35.00	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1555U2GY	\$32.00	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1555VA2GY	\$45.00	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555V2GY	\$45.00	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	PDF	1554VPL	\$12.00	1554VGASKET	\$4.50
1555VB2GY	\$45.00	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555W2GY	\$32.50	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555WA2GY	\$35.00	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555VAL2GY	\$43.00	9.45 x 6.30 x 2.36 [240 x 160 x 60]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555X2GY	\$56.00	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1555XA2GY	\$63.00	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1555Y2GY	\$63.00	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1555YA2GY	\$69.00	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
Note: Dimensions in inches [millimeters].								

IP66 ABS Plastic Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards or DIN rail-mounted components.
- "Styled" lid version has three main advantages: Smooth recessed surface on lid for a membrane keypad or label, standoffs molded in the interior of the lid (except for size "B"). Designed for #6 self-tapping screws, and a more modern "styled" look vs. our traditional flat lid.
- Gasketed lid with tongue and groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel captive, self-tapping machine screws.
 - Lid holes are threaded with the first installation of lid screws.
- All hardware is designed to avoid corrosion caused by harsh environments over time.
- Internal DIN rail mounting tabs molded into most models, except sizes C and D.
- Threaded (M3) integral brass inserts and/or standoffs (#6 self-tapping screws) for P.C. board or subpanel mounting in all except size ("B").
- Vertical P.C. card guides (for 0.59in [15 mm] thick P.C. boards) are molded in all except size ("B").
- Foot Kits available for sizes 4.72 x 3.54in [120 x 90 mm] [1554FT](#)) and 11.77 x 9.45in [299 x 240 mm] ([1554FT-XY](#)).

Construction

- Molded from general purpose material.
- Replaceable gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs.
 - Finish is light gray (RAL7035).

Listings

- IEC 60529, IP66



IP66 ABS Plastic Miniature Cases with Styled Lid



IP66 ABS Plastic Miniature Cases with Styled Lid								
Part Number	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1555BGY	\$9.75	2.56 x 2.56 x 1.61 [65 x 65 x 41]	15 [0.59]	PDF	1554BPL	\$5.75	1554BGASKET	\$2.25
1555EEGY	\$14.75	3.54 x 3.54 x 3.58 [90 x 90 x 91]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1555EGY	\$12.00	3.54 x 3.54 x 2.40 [90 x 90 x 61]	15 [0.59]	PDF	1554EPL	\$7.25	1554EGASKET	\$3.00
1555LAGY	\$18.75	4.13 x 4.13 x 3.54 [105 x 105 x 90]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555LGY	\$14.75	4.13 x 4.13 x 2.36 [105 x 105 x 60]	15 [0.59]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555CGY	\$10.75	4.72 x 2.56 x 1.61 [120 x 65 x 41]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1555DGY	\$12.00	4.72 x 2.56 x 2.40 [120 x 65 x 61]	15 [0.59]	PDF	1554CPL	\$6.75	1554CGASKET	\$2.00
1555FGY	\$14.75	4.72 x 3.54 x 2.40 [120 x 90 x 61]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1555GGY	\$15.00	4.72 x 3.54 x 3.19 [120 x 90 x 81]	15 [0.59]	PDF	1554FPL	\$7.25	1554FGASKET	\$2.00
1555NGY	\$18.25	4.72 x 4.72 x 2.40 [120 x 120 x 61]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1555PGY	\$19.50	4.72 x 4.72 x 3.15 [120 x 120 x 80]	15 [0.59]	PDF	1554NPL	\$7.75	1554NGASKET	\$3.75
1555QAGY	\$26.50	5.51 x 5.51 x 3.54 [140 x 140 x 90]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555QGY	\$19.00	5.51 x 5.51 x 2.36 [140 x 140 x 60]	15 [0.59]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555JLGY	\$17.75	6.30 x 3.54 x 1.81 [160 x 90 x 46]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555JGY	\$17.75	6.30 x 3.54 x 2.40 [160 x 90 x 61]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555KGY	\$19.50	6.30 x 3.54 x 3.58 [160 x 90 x 91]	15 [0.59]	PDF	1554JPL	\$8.00	1554JGASKET	\$2.75
1555RGY	\$26.50	6.30 x 6.30 x 2.40 [160 x 160 x 61]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1555SGY	\$28.50	6.30 x 6.30 x 3.58 [160 x 160 x 91]	15 [0.59]	PDF	1554RPL	\$10.00	1554RGASKET	\$4.25
1555HLGY	\$19.75	7.09 x 4.72 x 1.81 [180 x 120 x 46]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1555HGY	\$20.25	7.09 x 4.72 x 2.40 [180 x 120 x 61]	15 [0.59]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1555TGY	\$26.50	7.09 x 4.72 x 3.58 [180 x 120 x 91]	16 [0.63]	PDF	1554HPL	\$8.75	1554HGASKET	\$5.00
1555UGY	\$29.00	7.87 x 4.72 x 3.58 [200 x 120 x 91]	15 [0.59]	PDF	1554UPL	\$9.25	1554UGASKET	\$5.25
1555VAGY	\$36.00	9.45 x 6.30 x 3.54 [240 x 160 x 90]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555VGY	\$36.00	9.45 x 6.30 x 3.58 [240 x 160 x 91]	20 [0.79]	PDF	1554VPL	\$12.00	1554VGASKET	\$4.50
1555VBGY	\$36.00	9.45 x 6.30 x 4.72 [240 x 160 x 120]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555WGY	\$25.00	7.09 x 7.09 x 2.36 [180 x 180 x 60]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555WAGY	\$31.00	7.09 x 7.09 x 3.54 [180 x 180 x 90]	15 [0.59]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555VALGY	\$34.00	9.45 x 6.30 x 2.36 [240 x 160 x 60]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555XAGY	\$38.00	11.77 x 7.87 x 4.72 [299 x 200 x 120]	50 [1.97]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1555XGY	\$37.00	11.77 x 7.87 x 3.54 [299 x 200 x 90]	20 [0.79]	PDF	1554XPL	\$11.25	1554XGASKET	\$9.75
1555YGY	\$38.00	11.77 x 9.45 x 3.74 [299 x 240 x 95]	25 [0.98]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75
1555YAGY	\$40.50	11.77 x 9.45 x 4.72 [299 x 240 x 120]	50 [1.97]	PDF	1554YPL	\$12.75	1554YGASKET	\$10.75

Note: Dimensions in inches [millimeters].

NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Mounting Flange and Styled Lid



Features

- Designed for harsh industrial environments or outdoor applications (security, outdoor wireless, controls, etc.).
- Designed for wall-mounting. Interior is secure as lid screws are behind the lid. Can be made more secure if wall-mounted with security screws (tamper-resistant screws).
- Standoffs molded in the interior of the lid and enclosure - designed for #4 x 0.25in [6.35mm] self-tapping screws (part number 1555TS100)
- Gasketed lid with two-piece tongue and groove construction provides protection against oil, dust, and water.
- UV stabilized for outdoor use.
- Gasket is one piece made from high temperature, UL listed silicone (not pre-installed).
 - Sold in pairs
- Lid is secured with included M4 stainless steel machine screws. All hardware is stainless steel to avoid corrosion.
- Lid screws are self-captivating (lid holes are threaded with the first installation of lid screws).
- Internal features are maximized for mounting options and vary with size:
 - Internal DIN rail mounting tabs molded into most models, except 1555CF22 and 1555CF42.
 - Standoffs (#6 self-tapping screws) for P.C. board or subpanel.

Construction

- Polycarbonate (material carries a UL flammability rating of UL94 5VA @ 3mm) — Recommended for outdoor use.
- Satin texture finish with smooth recessed surface on lid for a membrane keypad or label.
- Finish is RAL 7035 Light Gray

Listings

- UL94-5VA
- UL 508A [UL File E65324]
- Complies with
 - NEMA 4, 4X, 6, 6P, 12, and 13
 - IEC 60529, IP68



NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Mounting Flange and Styled Lid



NEMA 4, 4X, 6, 6P, 12, and 13 Polycarbonate Miniature Cases with Mounting Flange and Styled Lid								
Part Number	Price	Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1555B2F22GY	\$14.50	2.56 x 2.56 x 1.69 [65 x 65 x 43]	28 [1.10]	PDF	1555BFPL	\$5.25	1554BGASKET	\$2.25
1555E2F17GY	\$17.00	3.54 x 3.54 x 1.50 [90 x 90 x 38]	23 [0.91]	PDF	1555EFPL	\$7.75	1554EGASKET	\$3.00
1555E2F42GY	\$18.00	3.54 x 3.54 x 2.48 [90 x 90 x 63]	48 [1.89]	PDF	1555EFPL	\$7.75	1554EGASKET	\$3.00
1555L2F17GY	\$15.75	4.13 x 4.13 x 1.46 [105 x 105 x 37]	22 [0.87]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555L1F17GY	\$13.25	4.13 x 4.13 x 1.46 [105 x 105 x 37]	22 [0.87]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555L2F42GY	\$16.50	4.13 x 4.13 x 2.44 [105 x 105 x 62]	47 [1.85]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555LF42GY	\$14.00	4.13 x 4.13 x 2.44 [105 x 105 x 62]	47 [1.85]	PDF	1554LPL	\$6.75	1554LGASKET	\$5.00
1555C2F22GY	\$16.50	4.72 x 2.60 x 1.69 [120 x 66 x 43]	27 [1.06]	PDF	1555CFPL	\$6.75	1554CGASKET	\$2.00
1555C2F42GY	\$17.25	4.72 x 2.60 x 2.48 [120 x 66 x 63]	47 [1.85]	PDF	1555CFPL	\$6.75	1554CGASKET	\$2.00
1555F2F17GY	\$17.50	4.72 x 3.58 x 1.50 [120 x 91 x 38]	22 [0.87]	PDF	1555FFPL	\$7.00	1554FGASKET	\$2.00
1555F2F42GY	\$18.50	4.72 x 3.58 x 2.48 [120 x 91 x 63]	47 [1.85]	PDF	1555FFPL	\$7.00	1554FGASKET	\$2.00
1555N2F17GY	\$21.00	4.76 x 4.72 x 1.50 [121 x 120 x 38]	22 [0.87]	PDF	1555NFPL	\$5.50	1554NGASKET	\$3.75
1555N2F42GY	\$22.50	4.76 x 4.72 x 2.48 [121 x 120 x 63]	47 [1.85]	PDF	1555NFPL	\$5.50	1554NGASKET	\$3.75
1555Q2F17GY	\$17.75	5.51 x 5.51 x 1.46 [140 x 140 x 37]	22 [0.87]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555QF17GY	\$15.25	5.51 x 5.51 x 1.46 [140 x 140 x 37]	22 [0.87]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555Q2F42GY	\$18.75	5.51 x 5.51 x 2.44 [140 x 140 x 62]	47 [1.85]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555QF42GY	\$16.25	5.51 x 5.51 x 2.44 [140 x 140 x 62]	47 [1.85]	PDF	1554QPL	\$9.00	1554QGASKET	\$6.00
1555J2F17GY	\$19.00	6.30 x 3.58 x 1.50 [160 x 91 x 38]	22 [0.87]	PDF	1555JFPL	\$7.75	1554JGASKET	\$2.75
1555J2F42GY	\$20.50	6.30 x 3.58 x 2.48 [160 x 91 x 63]	47 [1.85]	PDF	1555JFPL	\$7.75	1554JGASKET	\$2.75
1555R2F42GY	\$24.50	6.30 x 6.30 x 2.48 [160 x 160 x 63]	48 [1.89]	PDF	1555RFPL	\$9.75	1554RGASKET	\$4.25
1555R2F17GY	\$23.50	6.34 x 6.30 x 1.50 [161 x 160 x 38]	23 [0.91]	PDF	1555RFPL	\$9.75	1554RGASKET	\$4.25
1555H2F17GY	\$24.50	7.09 x 4.76 x 1.50 [180 x 121 x 38]	22 [0.87]	PDF	1555HFPL	\$8.00	1554HGASKET	\$5.00
1555WF17GY	\$19.00	7.09 x 7.09 x 1.57 [180 x 180 x 40]	22 [0.87]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555W2F17GY	\$22.00	7.09 x 7.09 x 1.57 [180 x 180 x 40]	22 [0.87]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555H2F42GY	\$26.00	7.09 x 4.76 x 2.44 [180 x 121 x 62]	47 [1.85]	PDF	1555HFPL	\$8.00	1554HGASKET	\$5.00
1555W2F42GY	\$23.00	7.09 x 7.09 x 2.56 [180 x 180 x 65]	47 [1.85]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555WF42GY	\$20.00	7.09 x 7.09 x 2.56 [180 x 180 x 65]	47 [1.85]	PDF	1554WPL	\$11.00	1554WGASKET	\$9.75
1555VA2F17GY	\$24.00	9.45 x 6.30 x 1.46 [240 x 160 x 37]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555VAF17GY	\$21.00	9.45 x 6.30 x 1.46 [240 x 160 x 37]	22 [0.87]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555VA2F42GY	\$25.50	9.45 x 6.30 x 2.44 [240 x 160 x 62]	47 [1.85]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00
1555VAF42GY	\$22.50	9.45 x 6.30 x 2.44 [240 x 160 x 62]	47 [1.85]	PDF	1554VAPL	\$9.00	1554VAGASKET	\$7.00

Note: Dimensions in inches [millimeters].

IP66 ABS Plastic Miniature Cases with Mounting Flange and Styled Lid



Features

- Designed for harsh industrial environments or outdoor applications (security, outdoor wireless, controls, etc.).
- Designed for wall-mounting. Interior is secure as lid screws are behind the lid. Can be made more secure if wall-mounted with security screws (tamper-resistant screws).
- Standoffs molded in the interior of the lid and enclosure - designed for #4 x 0.25in [6.35mm] self-tapping screws (part number 1555TS100)
- Gasketed lid with two piece tongue and groove construction provides protection against oil, dust, and water.
- UV stabilized for outdoor use.
- Gasket is one piece made from high temperature, UL listed silicone (not pre-installed).
 - Sold in pairs
- Lid is secured with included M4 stainless steel machine screws.
 - Lid screws are self-captivating (lid holes are threaded with the first installation of lid screws).
- All hardware is stainless steel to avoid corrosion.
- Internal features are maximized for mounting options and vary with size:
- Internal DIN rail mounting tabs molded into most models, except 1555CF22 and 1555CF42.
 - Standoffs (#6 self-tapping screws) for P.C. board or subpanel



Construction

- Polycarbonate (material carries a UL flammability rating of UL94 5VA @ 3mm) — recommended for outdoor use.
- Satin texture finish with smooth recessed surface on lid for a membrane keypad or label.
- Finish is light gray (RAL7035)

Listings

- Complies with
 - IEC 60529, IP66



IP66 ABS Plastic Miniature Cases with Mounting Flange and Styled Lid

Part Number	Price	Size HxWxD	Lid Depth	Drawing Link	Subpanel	Price	Replacement Gaskets	Price
1555BF22GY	\$12.75	2.56 x 2.56 x 1.69 [65 x 65 x 43]	28 [1.10]	PDF	1555BFPL	\$5.25	1554BGASKET	\$2.25
1555EF17GY	\$14.75	3.54 x 3.54 x 1.50 [90 x 90 x 38]	23 [0.91]	PDF	1555EFPL	\$7.75	1554EGASKET	\$3.00
1555EF42GY	\$15.75	3.54 x 3.54 x 2.48 [90 x 90 x 63]	48 [1.89]	PDF	1555EFPL	\$7.75	1554EGASKET	\$3.00
1555CF22GY	\$14.50	4.72 x 2.60 x 1.69 [120 x 66 x 43]	27 [1.06]	PDF	1555CFPL	\$6.75	1554CGASKET	\$2.00
1555CF42GY	\$14.75	4.72 x 2.60 x 2.48 [120 x 66 x 63]	47 [1.85]	PDF	1555CFPL	\$6.75	1554CGASKET	\$2.00
1555FF17GY	\$15.00	4.72 x 3.58 x 1.50 [120 x 91 x 38]	22 [0.87]	PDF	1555FFPL	\$7.00	1554FGASKET	\$2.00
1555FF42GY	\$15.50	4.72 x 3.58 x 2.48 [120 x 91 x 63]	47 [1.85]	PDF	1555FFPL	\$7.00	1554FGASKET	\$2.00
1555NF17GY	\$15.75	4.76 x 4.72 x 1.50 [121 x 120 x 38]	22 [0.87]	PDF	1555NFPL	\$5.50	1554NGASKET	\$3.75
1555NF42GY	\$16.50	4.76 x 4.72 x 2.48 [121 x 120 x 63]	47 [1.85]	PDF	1555NFPL	\$5.50	1554NGASKET	\$3.75
1555JF17GY	\$16.25	6.30 x 3.58 x 1.50 [160 x 91 x 38]	22 [0.87]	PDF	1555JFPL	\$7.75	1554JGASKET	\$2.75
1555JF42GY	\$17.00	6.30 x 3.58 x 2.48 [160 x 91 x 63]	47 [1.85]	PDF	1555JFPL	\$7.75	1554JGASKET	\$2.75
1555RF17GY	\$19.75	6.34 x 6.30 x 1.50 [161 x 160 x 38]	23 [0.91]	PDF	1555RFPL	\$9.75	1554RGASKET	\$4.25
1555RF42GY	\$20.50	6.30 x 6.30 x 2.48 [160 x 160 x 63]	48 [1.89]	PDF	1555RFPL	\$9.75	1554RGASKET	\$4.25
1555HF17GY	\$17.75	7.09 x 4.76 x 1.50 [180 x 121 x 38]	22 [0.87]	PDF	1555HFPL	\$8.00	1554HGASKET	\$5.00
1555HF42GY	\$18.25	7.09 x 4.76 x 2.44 [180 x 121 x 62]	47 [1.85]	PDF	1555HFPL	\$8.00	1554HGASKET	\$5.00

Note: Dimensions in inches [millimeters].