

NEMA 12 and 13 22 mm Pushbutton Wall-Mount



Applications

- Designed to accept 22 mm [0.87in] miniature oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see table).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door, and a grounding stud is provided on the enclosure.

Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray or RAL7035 light gray powder coating.

Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
 - NEMA Type 12 and 13
 - IEC 60529, IP54
- All appropriate components are required to maintain these standards.





NEMA 12 and 13 22 mm [0.87in] Pushbutton Wall-Mount							
ANSI 61	RAL7035	Price	Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged
MPB1	MPB1LG	\$81.00	3.56 x 3.06 x 3.66 [90 x 78 x 93]	PDF	1	16	No
MPB2	MPB2LG	\$93.00	5.44 x 3.06 x 3.67 [138 x 78 x 93]	PDF	2	14	
MPB3	MPB3LG	\$102.00	7.31 x 3.06 x 3.67 [186 x 78 x 93]	PDF	3		
MPB4	MPB4LG	\$113.00	9.19 x 3.06 x 3.67 [233 x 78 x 93]	PDF	4		
MPB6	MPB6LG	\$144.00	8.81 x 5.31 x 4.47 [224 x 135 x 114]	PDF	6		Yes
MPB9	MPB9LG	\$158.00	8.81 x 6.81 x 4.47 [224 x 173 x 114]	PDF	9		
MPB12	MPB12LG	\$176.00	10.69 x 6.81 x 4.47 [272 x 173 x 114]	PDF	12		
Note: Dimensions in inches [millimeters].							


NEMA 12 and 13 22 mm Pushbutton Wall-Mount




Dimensions




1




2




3




4



6



9



12