


# NEMA 12 Double-Door Wall-Mount



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides some protection from falling dirt, dust, oil, and water.

## Construction

- Enclosures are formed 14-gauge steel with 12-gauge steel subpanels. Exceptions are 42 x 60 in [1067 x 1524 mm] and 48 x 48 in [1219 x 1219 mm] which are formed 12-gauge steel with 10-gauge steel subpanels.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Body stiffeners are provided in enclosures 30 in [762 mm] high or more for extra rigidity.
- 14-gauge welded mounting brackets
- Gasketed overlapping doors eliminate the need for a center post.
- Continuously hinged doors may be removed by pulling the hinge pin.
- Doors are secured with a 3-point latch and operated with a key locking automotive type handle.
- Latch rods are equipped with rollers for easier door closing.
- Oil-resistant gaskets are permanently secured.
- Collar studs are provided for mounting subpanels.
- A grounding stud is provided in the enclosure, and a bonding stud is provided on the door.
- A literature pocket is provided for the inside of the door.

## Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating on the inside and outside.
- Removable subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 12 [UL File E65324]
- CSA Type 12 [CSA File LR21001]
- Complies with
  - NEMA Type 12
  - IEC 60529, IP54



## NEMA 12 Double-Door Wall-Mount

| Part Number              | Price      | Enclosure Size HxWxD                      | Optional Subpanels      |                         |                         |                            |                            | Drawing Link        |
|--------------------------|------------|-------------------------------------------|-------------------------|-------------------------|-------------------------|----------------------------|----------------------------|---------------------|
|                          |            |                                           | Painted (included)      | Aluminum                | Galvanized              | Stainless                  | Dimensions                 |                     |
| <a href="#">1422P8</a>   | \$1,062.00 | 24.00 x 42.00 x 9.21 [610 x 1067 x 234]   | <a href="#">18P3921</a> | —                       | <a href="#">18G3921</a> | —                          | 39.00 x 21.00 [991 x 533]  | <a href="#">PDF</a> |
| <a href="#">1422P10</a>  | \$1,274.00 | 24.00 x 42.00 x 11.21 [610 x 1067 x 285]  | <a href="#">18P3921</a> | —                       | <a href="#">18G3921</a> | —                          | 39.00 x 21.00 [991 x 533]  | <a href="#">PDF</a> |
| <a href="#">1422PW8</a>  | \$1,161.00 | 24.00 x 48.00 x 9.21 [610 x 1219 x 234]   | <a href="#">18P4521</a> | —                       | <a href="#">18G4521</a> | —                          | 45.00 x 21.00 [1143 x 533] | <a href="#">PDF</a> |
| <a href="#">1422R10</a>  | \$1,281.00 | 30.00 x 42.00 x 11.21 [762 x 1067 x 285]  | <a href="#">18P3927</a> | —                       | <a href="#">18G3927</a> | <a href="#">18P3927S16</a> | 39.00 x 27.00 [991 x 686]  | <a href="#">PDF</a> |
| <a href="#">1422RW10</a> | \$1,401.00 | 30.00 x 48.00 x 11.21 [762 x 1219 x 285]  | <a href="#">18P4527</a> | —                       | <a href="#">18G4527</a> | —                          | 45.00 x 27.00 [1143 x 686] | <a href="#">PDF</a> |
| <a href="#">1422RX10</a> | \$1,678.00 | 30.00 x 60.00 x 11.21 [762 x 1524 x 285]  | —                       | —                       | —                       | —                          | —                          | <a href="#">PDF</a> |
| <a href="#">1422UV12</a> | \$1,537.00 | 36.00 x 42.00 x 13.21 [914 x 1067 x 336]  | <a href="#">18P3933</a> | —                       | <a href="#">18G3933</a> | <a href="#">18P3933S16</a> | 39.00 x 33.00 [991 x 838]  | <a href="#">PDF</a> |
| <a href="#">1422UW12</a> | \$1,642.00 | 36.00 x 48.00 x 13.21 [914 x 1219 x 336]  | <a href="#">18P4533</a> | <a href="#">18A4533</a> | <a href="#">18G4533</a> | <a href="#">18P4533S16</a> | 45.00 x 33.00 [1143 x 838] | <a href="#">PDF</a> |
| <a href="#">1422UX12</a> | \$1,928.00 | 36.00 x 60.00 x 13.21 [914 x 1524 x 336]  | <a href="#">18P5733</a> | <a href="#">18A5733</a> | <a href="#">18G5733</a> | <a href="#">18P5733S16</a> | 57.00 x 33.00 [1448 x 838] | <a href="#">PDF</a> |
| <a href="#">1422VV12</a> | \$1,699.00 | 42.00 x 42.00 x 13.21 [1067 x 1067 x 336] | —                       | —                       | —                       | —                          | —                          | <a href="#">PDF</a> |
| <a href="#">1422VW12</a> | \$1,869.00 | 42.00 x 48.00 x 13.21 [1067 x 1219 x 336] | —                       | —                       | —                       | —                          | —                          | <a href="#">PDF</a> |
| <a href="#">1422VX12</a> | \$2,169.00 | 42.13 x 60.06 x 13.85 [1070 x 1526 x 352] | —                       | —                       | —                       | —                          | —                          | <a href="#">PDF</a> |
| <a href="#">1422WW12</a> | \$2,027.00 | 48.13 x 48.06 x 13.85 [1223 x 1221 x 352] | —                       | —                       | —                       | —                          | —                          | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# NEMA 12 Double-Door Wall-Mount



## Dimensions

