


# NEMA 4 and 12 Lift-Off Cover Wall-Mount



## Applications

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes, or terminal wiring enclosures.
- Provides some protection from falling dirt, dust, oil, and water.

## Construction

- Body formed from 16-gauge or 14-gauge steel. Covers are formed from 14-gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- 14-gauge welded mounting brackets
- Lift-off cover is secured with stainless steel clamps and stainless steel screws and retained with a stainless steel chain when open.
- Seamless poured-in-place gasket.
- Internal threaded weld studs are provided for mounting subpanels.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray recoatable powder coating.

## Listings

- UL 508A Type 3R, 4, 12, and 13 [UL File E65324]
- CSA Type 3R, 4, 12, and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4, 12, and 13
  - IEC 60529, IP66



## NEMA 4 and 12 Lift-Off Cover Wall-Mount

| Part Number                | Price    | Enclosure Size HxWxD                    | Subpanels               |                         |                         |                           | Size HxW                  | Drawing Link        |
|----------------------------|----------|-----------------------------------------|-------------------------|-------------------------|-------------------------|---------------------------|---------------------------|---------------------|
|                            |          |                                         | Painted                 | Aluminum                | Galvanized              | Stainless                 |                           |                     |
| <a href="#">HJ443LP</a>    | \$56.00  | 4.31 x 4.31 x 3.20 [109 x 109 x 81]     | —                       | —                       | —                       | —                         | —                         | <a href="#">PDF</a> |
| <a href="#">HJ444LP</a>    | \$59.00  | 4.31 x 4.31 x 4.20 [109 x 109 x 107]    | —                       | —                       | —                       | —                         | —                         | <a href="#">PDF</a> |
| <a href="#">HJ643LP</a>    | \$63.00  | 6.31 x 4.31 x 3.20 [160 x 109 x 81]     | <a href="#">14R0503</a> | <a href="#">14A0503</a> | <a href="#">14G0503</a> | <a href="#">14R0503SS</a> | 4.88 x 2.88 [124 x 73]    | <a href="#">PDF</a> |
| <a href="#">HJ644LP</a>    | \$68.00  | 6.31 x 4.31 x 4.20 [160 x 109 x 107]    | <a href="#">14R0503</a> | <a href="#">14A0503</a> | <a href="#">14G0503</a> | <a href="#">14R0503SS</a> | 4.88 x 2.88 [124 x 73]    | <a href="#">PDF</a> |
| <a href="#">HJ664LP</a>    | \$73.00  | 6.31 x 6.31 x 4.20 [160 x 160 x 107]    | <a href="#">14R0505</a> | <a href="#">14A0505</a> | <a href="#">14G0505</a> | <a href="#">14R0505SS</a> | 4.88 x 4.88 [124 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ863LP</a>    | \$77.00  | 8.31 x 6.31 x 3.70 [211 x 160 x 94]     | <a href="#">14R0705</a> | <a href="#">14A0705</a> | <a href="#">14G0705</a> | <a href="#">14R0705SS</a> | 6.75 x 4.88 [171 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ1084LP</a>   | \$98.00  | 10.31 x 8.31 x 4.20 [262 x 211 x 107]   | <a href="#">14R0907</a> | <a href="#">14A0907</a> | <a href="#">14G0907</a> | <a href="#">14R0907SS</a> | 8.75 x 6.88 [222 x 175]   | <a href="#">PDF</a> |
| <a href="#">HJ12105LP</a>  | \$126.00 | 12.31 x 10.31 x 5.20 [313 x 262 x 132]  | <a href="#">14R1109</a> | <a href="#">14A1109</a> | <a href="#">14G1109</a> | <a href="#">14R1109SS</a> | 10.75 x 8.88 [273 x 226]  | <a href="#">PDF</a> |
| <a href="#">HJ14126LP</a>  | \$164.00 | 14.31 x 12.31 x 6.20 [363 x 313 x 157]  | <a href="#">14R1311</a> | <a href="#">14A1311</a> | <a href="#">14G1311</a> | <a href="#">14R1311SS</a> | 12.75 x 10.88 [324 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ16146LP</a>  | \$191.00 | 16.31 x 14.31 x 6.20 [414 x 363 x 157]  | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |
| <a href="#">HJ14128LP</a>  | \$194.00 | 14.31 x 12.31 x 8.20 [363 x 313 x 208]  | <a href="#">14R1311</a> | <a href="#">14A1311</a> | <a href="#">14G1311</a> | <a href="#">14R1311SS</a> | 12.75 x 10.88 [324 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ161410LP</a> | \$233.00 | 16.31 x 14.31 x 10.20 [414 x 363 x 259] | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# NEMA 4 and 12 Lift-Off Cover Wall-Mount



## Dimensions

