

# NEMA 4 and 12 Single-Door Wall-Mount



## Applications

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes, or terminal wiring enclosures.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in outdoor applications for full weather protection.

## Construction

- Body formed from 16-gauge or 14-gauge steel. Covers are formed from 14-gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- 14-gauge welded mounting brackets
- Continuous hinged cover is secured with stainless steel clamps and screws.
- Stainless steel continuous hinge on door may be removed by pulling the stainless steel hinge pin.
- Seamless poured-in-place gasket.
- Internal threaded weld studs are provided for mounting subpanels.
- A bonding stud is provided on the door, and a grounding stud is provided in the enclosure.

## Finish


- Cover and enclosure are phosphatized and finished in smooth ANSI 61 gray recoatable powder coating.
- Removable subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 3R, 4, 12, and 13 [UL File E65324]
- CSA Type 3R, 4, 12, and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4, 12, and 13
  - IEC 60529, IP66 IEC 60529, IP66



## Dimensions



# NEMA 4 and 12 Single-Door Wall-Mount



| NEMA 4 and 12 Single-Door Wall-Mount |          |                                         |                         |                         |                         |                           |                           |                     |
|--------------------------------------|----------|-----------------------------------------|-------------------------|-------------------------|-------------------------|---------------------------|---------------------------|---------------------|
| Part Number                          | Price    | Enclosure Size HxWxD                    | Subpanels               |                         |                         |                           |                           | Drawing Link        |
|                                      |          |                                         | Painted                 | Aluminum                | Galvanized              | Stainless                 | Size HxW                  |                     |
| <a href="#">HJ443HLP</a>             | \$55.00  | 4.31 x 4.31 x 3.20 [109 x 109 x 81]     | —                       | —                       | —                       | —                         | —                         | <a href="#">PDF</a> |
| <a href="#">HJ444HLP</a>             | \$57.00  | 4.31 x 4.31 x 4.20 [109 x 109 x 107]    | —                       | —                       | —                       | —                         | —                         | <a href="#">PDF</a> |
| <a href="#">HJ643HLP</a>             | \$63.00  | 6.31 x 4.31 x 3.20 [160 x 109 x 81]     | <a href="#">14R0503</a> | <a href="#">14A0503</a> | <a href="#">14G0503</a> | <a href="#">14R0503SS</a> | 4.88 x 2.88 [124 x 73]    | <a href="#">PDF</a> |
| <a href="#">HJ644HLP</a>             | \$67.00  | 6.31 x 4.31 x 4.20 [160 x 109 x 107]    | <a href="#">14R0503</a> | <a href="#">14A0503</a> | <a href="#">14G0503</a> | <a href="#">14R0503SS</a> | 4.88 x 2.88 [124 x 73]    | <a href="#">PDF</a> |
| <a href="#">HJ664HLP</a>             | \$71.00  | 6.31 x 6.31 x 4.20 [160 x 160 x 107]    | <a href="#">14R0505</a> | <a href="#">14A0505</a> | <a href="#">14G0505</a> | <a href="#">14R0505SS</a> | 4.88 x 4.88 [124 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ683HLP</a>             | \$76.00  | 6.31 x 8.31 x 3.70 [160 x 211 x 94]     | <a href="#">14R0705</a> | <a href="#">14A0705</a> | <a href="#">14G0705</a> | <a href="#">14R0705SS</a> | 6.75 x 4.88 [171 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ863HLP</a>             | \$76.00  | 8.31 x 6.31 x 3.70 [211 x 160 x 94]     | <a href="#">14R0705</a> | <a href="#">14A0705</a> | <a href="#">14G0705</a> | <a href="#">14R0705SS</a> | 6.75 x 4.88 [171 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ884HLP</a>             | \$87.00  | 8.31 x 8.31 x 4.20 [211 x 211 x 107]    | <a href="#">14R0707</a> | <a href="#">14A0707</a> | <a href="#">14G0707</a> | <a href="#">14R0707SS</a> | 6.75 x 6.88 [171 x 175]   | <a href="#">PDF</a> |
| <a href="#">HJ866HLP</a>             | \$91.00  | 8.31 x 6.31 x 6.20 [211 x 160 x 157]    | <a href="#">14R0705</a> | <a href="#">14A0705</a> | <a href="#">14G0705</a> | <a href="#">14R0705SS</a> | 6.75 x 4.88 [171 x 124]   | <a href="#">PDF</a> |
| <a href="#">HJ1084HLP</a>            | \$96.00  | 10.31 x 8.31 x 4.20 [262 x 211 x 107]   | <a href="#">14R0907</a> | <a href="#">14A0907</a> | <a href="#">14G0907</a> | <a href="#">14R0907SS</a> | 8.75 x 6.88 [222 x 175]   | <a href="#">PDF</a> |
| <a href="#">HJ1264HLP</a>            | \$96.00  | 12.31 x 6.31 x 4.20 [313 x 160 x 107]   | <a href="#">14R1105</a> | <a href="#">14A1105</a> | <a href="#">14G1105</a> | —                         | 10.75 x 4.88 [273 x 124]  | <a href="#">PDF</a> |
| <a href="#">HJ8104HLP</a>            | \$95.00  | 8.31 x 10.31 x 4.20 [211 x 262 x 107]   | <a href="#">14R0907</a> | <a href="#">14A0907</a> | <a href="#">14G0907</a> | <a href="#">14R0907SS</a> | 8.75 x 6.88 [222 x 175]   | <a href="#">PDF</a> |
| <a href="#">HJ1086HLP</a>            | \$110.00 | 10.31 x 8.31 x 6.20 [262 x 211 x 157]   | <a href="#">14R0907</a> | <a href="#">14A0907</a> | <a href="#">14G0907</a> | <a href="#">14R0907SS</a> | 8.75 x 6.88 [222 x 175]   | <a href="#">PDF</a> |
| <a href="#">HJ10106HLP</a>           | \$119.00 | 10.31 x 10.31 x 6.20 [262 x 262 x 157]  | <a href="#">14R0909</a> | <a href="#">14A0909</a> | <a href="#">14G0909</a> | <a href="#">14R0909SS</a> | 8.75 x 8.88 [222 x 226]   | <a href="#">PDF</a> |
| <a href="#">HJ10125HLP</a>           | \$122.00 | 10.31 x 12.31 x 5.20 [262 x 313 x 132]  | <a href="#">14R1109</a> | <a href="#">14A1109</a> | <a href="#">14G1109</a> | <a href="#">14R1109SS</a> | 10.75 x 8.88 [273 x 226]  | <a href="#">PDF</a> |
| <a href="#">HJ12105HLP</a>           | \$123.00 | 12.31 x 10.31 x 5.20 [313 x 262 x 132]  | <a href="#">14R1109</a> | <a href="#">14A1109</a> | <a href="#">14G1109</a> | <a href="#">14R1109SS</a> | 10.75 x 8.88 [273 x 226]  | <a href="#">PDF</a> |
| <a href="#">HJ1486HLP</a>            | \$131.00 | 14.31 x 8.31 x 6.20 [363 x 211 x 157]   | <a href="#">14R1307</a> | <a href="#">14A1307</a> | <a href="#">14G1307</a> | —                         | 12.75 x 6.88 [324 x 175]  | <a href="#">PDF</a> |
| <a href="#">HJ12126HLP</a>           | \$143.00 | 12.31 x 12.31 x 6.20 [313 x 313 x 157]  | <a href="#">14R1111</a> | <a href="#">14A1111</a> | <a href="#">14G1111</a> | <a href="#">14R1111SS</a> | 10.75 x 10.88 [273 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ12108HLP</a>           | \$150.00 | 12.31 x 10.31 x 8.20 [313 x 262 x 208]  | <a href="#">14R1109</a> | <a href="#">14A1109</a> | <a href="#">14G1109</a> | <a href="#">14R1109SS</a> | 10.75 x 8.88 [273 x 226]  | <a href="#">PDF</a> |
| <a href="#">HJ12146HLP</a>           | \$153.00 | 12.31 x 14.31 x 6.20 [313 x 363 x 157]  | <a href="#">14R1311</a> | <a href="#">14A1311</a> | <a href="#">14G1311</a> | <a href="#">14R1311SS</a> | 12.75 x 10.88 [324 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ14126HLP</a>           | \$154.00 | 14.31 x 12.31 x 6.20 [363 x 313 x 157]  | <a href="#">14R1311</a> | <a href="#">14A1311</a> | <a href="#">14G1311</a> | <a href="#">14R1311SS</a> | 12.75 x 10.88 [324 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ16106HLP</a>           | \$156.00 | 16.31 x 10.31 x 6.20 [414 x 262 x 157]  | <a href="#">14R1509</a> | <a href="#">14A1509</a> | <a href="#">14G1509</a> | —                         | 14.75 x 8.88 [375 x 226]  | <a href="#">PDF</a> |
| <a href="#">HJ14128HLP</a>           | \$176.00 | 14.31 x 12.31 x 8.20 [363 x 313 x 208]  | <a href="#">14R1311</a> | <a href="#">14A1311</a> | <a href="#">14G1311</a> | <a href="#">14R1311SS</a> | 12.75 x 10.88 [324 x 276] | <a href="#">PDF</a> |
| <a href="#">HJ14166HLP</a>           | \$180.00 | 14.31 x 16.31 x 6.20 [363 x 414 x 157]  | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |
| <a href="#">HJ16146HLP</a>           | \$182.00 | 16.31 x 14.31 x 6.20 [414 x 363 x 157]  | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |
| <a href="#">HJ16148HLP</a>           | \$201.00 | 16.31 x 14.31 x 8.20 [414 x 363 x 208]  | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |
| <a href="#">HJ161410HLP</a>          | \$227.00 | 16.31 x 14.31 x 10.20 [414 x 363 x 259] | <a href="#">14R1513</a> | <a href="#">14A1513</a> | <a href="#">14G1513</a> | <a href="#">14R1513SS</a> | 14.75 x 12.88 [375 x 327] | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].