




# Potable Water Push-to-Connect Fittings

HydroMode push-to-connect bulkhead union fitting with acetel body and synthetic rubber o-ring. For use with polyethylene and other flexible tubing. Five fittings per package.




**HydroMode™ Bulkhead Union**

*Inch Sizes - dimensions in millimeters (mm) unless otherwise noted*

| Part No.                  | Price   | Size (inch)         | ØD (inch) | T         | L    | A    | B    | H1   | H2   | Package Weight (lbs) | Qty. per pack |
|---------------------------|---------|---------------------|-----------|-----------|------|------|------|------|------|----------------------|---------------|
| <a href="#">UB532-P</a>   | \$13.50 | 5/32 in. x 5/32 in. | 5/32      | M15*1.5P  | 31.4 | 7.2  | 14.7 | 17.0 | 18.0 | 0.1                  | 5             |
| <a href="#">UB14-P</a>    | \$14.00 | 1/4 in. x 1/4 in.   | 1/4       | M17*1.5P  | 34.2 | 7.9  | 16.9 | 19.0 | 21.0 | 0.1                  | 5             |
| <a href="#">UB516-P</a>   | \$14.00 | 5/16 in. x 5/16 in. | 1/4       | M24*1.75P | 47.9 | 11.1 | 16.9 | 24.0 | 28.5 | 0.2                  | 5             |
| <a href="#">UB38-14-P</a> | \$14.00 | 3/8 in. x 1/4 in.   | 5/16      | M20*1.75P | 38.5 | 9.4  | 17.5 | 21.0 | 25.5 | 0.2                  | 5             |
| <a href="#">UB38-P</a>    | \$16.00 | 3/8 in. x 3/8 in.   | 3/8       | M24*1.75P | 42.4 | 10.8 | 20.2 | 24.0 | 28.5 | 0.2                  | 5             |
| <a href="#">UB12-P</a>    | \$17.00 | 1/2 in. x 1/2 in.   | 1/2       | M27*2.0P  | 51.8 | 16.4 | 25.1 | 27.0 | 31.0 | 0.3                  | 5             |

HydroMode push-to-connect union check valve fitting with acetel body and synthetic rubber o-ring. For use with polyethylene and other flexible tubing. Five fittings per package.



**HydroMode™ Union Check Valve**

*Inch Sizes - dimensions in millimeters (mm) unless otherwise noted*


| Part No.                 | Price   | Size (inch)         | ØD (inch) | ØP   | L    | B    | Package Weight (lbs) | Qty. per pack |
|--------------------------|---------|---------------------|-----------|------|------|------|----------------------|---------------|
| <a href="#">CVU14-P</a>  | \$20.00 | 1/4 in. x 1/4 in.   | 1/4       | 15.5 | 45.5 | 16.1 | 0.1                  | 2             |
| <a href="#">CVU516-P</a> | \$20.00 | 5/16 in. x 5/16 in. | 5/16      | 17.6 | 48.6 | 17.5 | 0.1                  | 2             |
| <a href="#">CVU38-P</a>  | \$20.00 | 3/8 in. x 3/8 in.   | 3/8       | 20.0 | 57.8 | 19.4 | 0.1                  | 2             |
| <a href="#">CVU12-P</a>  | \$20.00 | 1/2 in. x 1/2 in.   | 1/2       | 23.6 | 67.9 | 24.1 | 0.1                  | 2             |

# HydroMode™ Potable Water Push-to-Connect Fittings

HydroMode push-to-connect fittings are designed to work with potable water and beverages. Installing or removing flexible tubing is quick and easy. All fittings are made of NSF approved materials with NSF-51® and NSF-61® certifications. The body and collet of the fittings are made from polyoxymethylene (POM) also known as acetal, while the o-rings are made from ethylene propylene diene monomer (EPDM) which is a type of synthetic rubber.

## Features

- Designed for potable water and beverages
- NSF-51 and NSF-61 certified
- Easy tubing installation and removal
- Optional retaining clips prevent accidental tube removal
- Fittings rated for up to 145psi at 70°C (158°F)



*Push-to-Connect Fitting  
Cut-away Diagram*