

## iX7NH System Non-Brake Motor Power Cables

| Part Number                      | Price    | Flex Rated | Length        | Gauge | Drawing             | Compatible Motors                                   |
|----------------------------------|----------|------------|---------------|-------|---------------------|-----------------------------------------------------|
| <a href="#">APCS-PN03LSX-AD</a>  | \$48.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | FBL/FCL series motors                               |
| <a href="#">APCS-PN05LSX-AD</a>  | \$53.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN10LSX-AD</a>  | \$65.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN20LSX-AD</a>  | \$94.00  |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF03LSX-AD</a>  | \$55.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF05LSX-AD</a>  | \$65.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF10LSX-AD</a>  | \$93.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF20LSX-AD</a>  | \$146.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN03HSX1-AD</a> | \$48.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE15A series motors without brake               |
| <a href="#">APCS-PN05HSX1-AD</a> | \$55.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN10HSX1-AD</a> | \$72.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN20HSX1-AD</a> | \$108.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF03HSX1-AD</a> | \$56.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF05HSX1-AD</a> | \$68.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF10HSX1-AD</a> | \$100.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF20HSX1-AD</a> | \$158.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN03HSX-AD</a>  | \$44.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE16D and APM-FE22D series motors without brake |
| <a href="#">APCS-PN05HSX-AD</a>  | \$53.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN10HSX-AD</a>  | \$74.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN20HSX-AD</a>  | \$116.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF03HSX-AD</a>  | \$57.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF05HSX-AD</a>  | \$74.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF10HSX-AD</a>  | \$116.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF20HSX-AD</a>  | \$200.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN03ISX-AD</a>  | \$49.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FF35D motors without brake                      |
| <a href="#">APCS-PN05ISX-AD</a>  | \$57.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN10ISX-AD</a>  | \$79.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PN20ISX-AD</a>  | \$120.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF03ISX-AD</a>  | \$63.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF05ISX-AD</a>  | \$80.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF10ISX-AD</a>  | \$124.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                     |
| <a href="#">APCS-PF20ISX-AD</a>  | \$213.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                     |

NOTE: These parts available for sale to North American locations only



APCS-PxxLSX series power cable



APCS-PxxHSX1 series power cable



APCS-PxxHSX series power cable



# iX7NH Series Accessories

## Accessories, continued

### iX7NH System Brake Motor Power Cables

| Part Number                                                                                                                                                                                                                                                       | Price    | Flex Rated | Length        | Gauge | Drawing             | Compatible Motors                                 |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------------|---------------|-------|---------------------|---------------------------------------------------|
| Note: For FBL/FCL 100W–1kW motors with brake, use the power cables on the previous page AND separate brake cable APCS-BxxxQS-AD from page tSRV-82. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below). |          |            |               |       |                     |                                                   |
| <a href="#">APCS-PN03NBX1-AD</a>                                                                                                                                                                                                                                  | \$58.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE15A series motors with brakes               |
| <a href="#">APCS-PN05NBX1-AD</a>                                                                                                                                                                                                                                  | \$68.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN10NBX1-AD</a>                                                                                                                                                                                                                                  | \$94.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN20NBX1-AD</a>                                                                                                                                                                                                                                  | \$144.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF03NBX1-AD</a>                                                                                                                                                                                                                                  | \$72.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF05NBX1-AD</a>                                                                                                                                                                                                                                  | \$91.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF10NBX1-AD</a>                                                                                                                                                                                                                                  | \$139.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF20NBX1-AD</a>                                                                                                                                                                                                                                  | \$237.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN03NBX-AD</a>                                                                                                                                                                                                                                   | \$51.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FE16D and APM-FE22D series motors with brakes |
| <a href="#">APCS-PN05NBX-AD</a>                                                                                                                                                                                                                                   | \$61.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN10NBX-AD</a>                                                                                                                                                                                                                                   | \$86.00  |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN20NBX-AD</a>                                                                                                                                                                                                                                   | \$137.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF03NBX-AD</a>                                                                                                                                                                                                                                   | \$67.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF05NBX-AD</a>                                                                                                                                                                                                                                   | \$89.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF10NBX-AD</a>                                                                                                                                                                                                                                   | \$137.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF20NBX-AD</a>                                                                                                                                                                                                                                   | \$243.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN03PBX-AD</a>                                                                                                                                                                                                                                   | \$70.00  | Y          | 3m [9.8 ft]   |       | <a href="#">PDF</a> | APM-FF35D series motors with brakes               |
| <a href="#">APCS-PN05PBX-AD</a>                                                                                                                                                                                                                                   | \$82.00  |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN10PBX-AD</a>                                                                                                                                                                                                                                   | \$117.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PN20PBX-AD</a>                                                                                                                                                                                                                                   | \$184.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF03PBX-AD</a>                                                                                                                                                                                                                                   | \$89.00  | N          | 3m [9.8 ft]   |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF05PBX-AD</a>                                                                                                                                                                                                                                   | \$117.00 |            | 5m [16.4 ft]  |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF10PBX-AD</a>                                                                                                                                                                                                                                   | \$182.00 |            | 10m [32.8 ft] |       | <a href="#">PDF</a> |                                                   |
| <a href="#">APCS-PF20PBX-AD</a>                                                                                                                                                                                                                                   | \$315.00 |            | 20m [65.6 ft] |       | <a href="#">PDF</a> |                                                   |



**APCS-PxxNBX1 series power cable**



**APCS-PxxNBX series power cable**



**APCS-PxxPBX series power cable**