









# 5mm x 20mm Fuse Holder Terminal Blocks

**KN-F10****Dimensions: mm [in]****KN-F10LxxDC****KN-F10LxxAC**

- Screw connection terminal
- UL E179129  
(For copper wire only.  
One conductor in  
terminal only.)
- CE (EN 60947-7-3)
- Fuse series: GMA, GMC,  
S500, S506



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

## Ordering Information

| Color | Part Number               | Qty | Price    | Part Number                     | Qty | Price   | Part Number                     | Qty | Price   |
|-------|---------------------------|-----|----------|---------------------------------|-----|---------|---------------------------------|-----|---------|
| Gray  | <a href="#">KN-F10</a>    | 50  | \$146.00 | <a href="#">KN-F10L24DC</a>     | 25  | \$89.00 | <a href="#">KN-F10L24AC</a>     | 25  | \$89.00 |
|       | <a href="#">KN-F10-10</a> | 10  | \$33.00  | <a href="#">KN-F10L24DC-10</a>  | 10  | \$39.00 | <a href="#">KN-F10L24AC-10</a>  | 10  | \$39.00 |
|       | —                         | —   | —        | <a href="#">KN-F10L110DC</a>    | 25  | \$89.00 | <a href="#">KN-F10L110AC</a>    | 25  | \$89.00 |
|       | —                         | —   | —        | <a href="#">KN-F10L110DC-10</a> | 10  | \$39.00 | <a href="#">KN-F10L110AC-10</a> | 10  | \$39.00 |
|       | —                         | —   | —        | <a href="#">KN-F10L220DC</a>    | 25  | \$89.00 | <a href="#">KN-F10L220AC</a>    | 25  | \$89.00 |
|       | —                         | —   | —        | <a href="#">KN-F10L220DC-10</a> | 10  | \$39.00 | <a href="#">KN-F10L220AC-10</a> | 10  | \$39.00 |

## Technical Specifications

| Technical Specifications |                                                                                                                            |       |          |                                                                                                                  |      |          |                                                                                                                     |       |          |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------|-------|----------|------------------------------------------------------------------------------------------------------------------|------|----------|---------------------------------------------------------------------------------------------------------------------|-------|----------|
| Model                    | KN-F10                                                                                                                     |       |          | KN-F10LxxDC                                                                                                      |      |          | KN-F10LxxAC                                                                                                         |       |          |
| Width                    | 8mm [0.31 in]                                                                                                              |       |          | 8mm [0.31 in]                                                                                                    |      |          | 8mm [0.31 in]                                                                                                       |       |          |
| Stripping Length         | 12mm [0.47 in]                                                                                                             |       |          | 12mm [0.47 in]                                                                                                   |      |          | 12mm [0.47 in]                                                                                                      |       |          |
| Tightening Torque        | 0.8 N·m [7.1 lb·in]                                                                                                        |       |          | 0.8 N·m [7.1 lb·in]                                                                                              |      |          | 0.8 N·m [7.1 lb·in]                                                                                                 |       |          |
| Density                  | 125/m [38 pcs/ft]                                                                                                          |       |          | 125/m [38 pcs/ft]                                                                                                |      |          | 125/m [38 pcs/ft]                                                                                                   |       |          |
| UL/CSA Approval          | 300V                                                                                                                       | 6.3A  | 26-8 AWG | 300V                                                                                                             | 6.3A | 26-8 AWG | 300V                                                                                                                | 6.3A  | 26-8 AWG |
| CE Conformity            | 500V                                                                                                                       | 6.3 A | 6mm²     | 24/110VDC                                                                                                        | 6.3A | 6mm²     | 24/110VAC                                                                                                           | 6.3 A | 6mm²     |
| LED Voltage              | —                                                                                                                          |       |          | 2 Volts                                                                                                          |      |          | —                                                                                                                   |       |          |
| Resistor Value           | —                                                                                                                          |       |          | 10kΩ (KN-F10L24DC), 2mA, 9-36VDC<br>56kΩ (KN-F10L110DC), 2mA, 60-150VDC<br>220kΩ (KN-F10L220DC), 1mA, 100-250VDC |      |          | 4.7kΩ (KN-F10L24AC), 2.5 mA, 9-36VAC<br>33kΩ (KN-F10L110AC), 2mA, 60-150VAC<br>56kΩ (KN-F10L220AC), 2mA, 100-250VAC |       |          |
| Operating Temperature    | Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C] |       |          |                                                                                                                  |      |          |                                                                                                                     |       |          |
| SCCR Rating              | 10kA per Table SB4.1, 2009, UL 508A. Maximum short circuit current rating for unmarked components.                         |       |          |                                                                                                                  |      |          |                                                                                                                     |       |          |
| Material                 | Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel                                              |       |          |                                                                                                                  |      |          |                                                                                                                     |       |          |
| Mounting                 | 35mm DIN rail                                                                                                              |       |          |                                                                                                                  |      |          |                                                                                                                     |       |          |

## Accessories

|                   |                                |        |         |                                |        |         |                                |        |         |
|-------------------|--------------------------------|--------|---------|--------------------------------|--------|---------|--------------------------------|--------|---------|
| End Covers / Gray | <a href="#">KN-ECF10</a>       | 25/pkg | \$16.00 | <a href="#">KN-ECF10</a>       | 25/pkg | \$16.00 | <a href="#">KN-ECF10</a>       | 25/pkg | \$16.00 |
| Marking Tags      | KN-L5 Series<br>KN-L6P5 Series |        |         | KN-L5 Series<br>KN-L6P5 Series |        |         | KN-L5 Series<br>KN-L6P5 Series |        |         |



# KONNECT-IT Accessories

## Multi-Pole Jumper Bars

Multi-pole jumper bars provide terminal block connection flexibility. Screw-down connection jumpers feature all-metal construction and can be installed quickly just by tightening the screws. Screwless comb-style jumpers are also available. See next page for the larger J1/O jumper installation instructions.

KN-10J12



KN-2JM12



KN-2JCC8



### Multi-Pole Jumper Bars Ordering Information

| Type                  | Part Number                | Price   | Qty | Number of Poles | Rating     | Tightening Torque               | Dimensions - mm [in] |              |                | Fig. | Works With                                                            |
|-----------------------|----------------------------|---------|-----|-----------------|------------|---------------------------------|----------------------|--------------|----------------|------|-----------------------------------------------------------------------|
|                       |                            |         |     |                 |            |                                 | Height               | Length       | Width          |      |                                                                       |
| Screw-down connection | <a href="#">KN-2J12</a>    | \$13.00 | 25  | 2               | 750V 24A   | 0.4–0.6 Nm<br>[3.5–5.3 lb-in]   | 15.8<br>[0.62]       | 10.1 [0.40]  | 4.4<br>[0.17]  | 1    | KN-T12xx<br>KN-D12xx<br>KN-D12X<br>KN-D12DR1<br>KN-D12LEDxx           |
|                       | <a href="#">KN-3J12</a>    | \$16.00 | 20  | 3               |            |                                 |                      | 15.3 [0.60]  |                |      |                                                                       |
|                       | <a href="#">KN-4J12</a>    | \$20.00 | 15  | 4               |            |                                 |                      | 20.4 [0.80]  |                |      |                                                                       |
|                       | <a href="#">KN-10J12</a>   | \$13.00 | 5   | 10              |            |                                 |                      | 51.1 [2.01]  |                |      |                                                                       |
|                       | <a href="#">KN-2J10</a>    | \$19.00 | 25  | 2               | 750V 32A   | 0.6–0.8 Nm<br>[5.3–7.1 lb-in]   | 15.5<br>[0.61]       | 10.8 [0.43]  | 6.0<br>[0.24]  | 1    | KN-T10xx<br>KN-D10xx<br>KN-D10X<br>KN-D10DR1<br>KN-D10LEDxx           |
|                       | <a href="#">KN-3J10</a>    | \$23.00 | 20  | 3               |            |                                 |                      | 17.0 [0.67]  |                |      |                                                                       |
|                       | <a href="#">KN-4J10</a>    | \$23.00 | 15  | 4               |            |                                 |                      | 23.0 [0.91]  |                |      |                                                                       |
|                       | <a href="#">KN-10J10</a>   | \$16.00 | 5   | 10              |            |                                 |                      | 59.0 [2.32]  |                |      |                                                                       |
|                       | <a href="#">KN-2J8</a>     | \$20.00 | 25  | 2               | 630V 41A   | 0.6–0.8 Nm<br>[5.3–7.1 lb-in]   | 15.5<br>[0.61]       | 14.3 [0.56]  | 6.0<br>[0.24]  | 1    | KN-T8xx                                                               |
|                       | <a href="#">KN-3J8</a>     | \$24.00 | 20  | 3               |            |                                 |                      | 22.3 [0.88]  |                |      |                                                                       |
|                       | <a href="#">KN-4J8</a>     | \$24.00 | 15  | 4               |            |                                 |                      | 30.3 [1.19]  |                |      |                                                                       |
|                       | <a href="#">KN-10J8</a>    | \$19.00 | 5   | 10              |            |                                 |                      | 78.3 [3.08]  |                |      |                                                                       |
|                       | <a href="#">KN-2J6</a>     | \$25.00 | 25  | 2               | 630V 57A   | 0.6–0.8 Nm<br>[5.3–7.1 lb-in]   | 15.5<br>[0.61]       | 18.0 [0.71]  | 6.0<br>[0.24]  | 1    | KN-T6xx                                                               |
|                       | <a href="#">KN-3J6</a>     | \$26.00 | 20  | 3               |            |                                 |                      | 28.0 [1.10]  |                |      |                                                                       |
|                       | <a href="#">KN-4J6</a>     | \$26.00 | 15  | 4               |            |                                 |                      | 38.0 [1.50]  |                |      |                                                                       |
|                       | <a href="#">KN-10J6</a>    | \$20.00 | 5   | 10              |            |                                 |                      | 98.0 [3.86]  |                |      |                                                                       |
|                       | <a href="#">KN-2J4</a>     | \$39.00 | 25  | 2               | 750V 76A   | 0.6–0.8 Nm<br>[5.3–7.1 lb-in]   | 23.0<br>[0.91]       | 21.0 [0.83]  | 6.0<br>[0.24]  | 1    | KN-T4xx                                                               |
|                       | <a href="#">KN-3J4</a>     | \$41.00 | 20  | 3               |            |                                 |                      | 33.0 [1.30]  |                |      |                                                                       |
|                       | <a href="#">KN-4J4</a>     | \$41.00 | 15  | 4               |            |                                 |                      | 45.0 [1.77]  |                |      |                                                                       |
|                       | <a href="#">KN-10J4</a>    | \$32.00 | 5   | 10              |            |                                 |                      | 117.0 [4.61] |                |      |                                                                       |
|                       | <a href="#">KN-2J2</a>     | \$40.00 | 25  | 2               | 750V 125A  | 1.2–1.4 Nm<br>[10.6–12.4 lb-in] | 21.0<br>[0.83]       | 29.0 [1.14]  | 8.0<br>[0.31]  | 1    | KN-T2xx                                                               |
|                       | <a href="#">KN-3J2</a>     | \$43.00 | 20  | 3               |            |                                 |                      | 45.0 [1.77]  |                |      |                                                                       |
|                       | <a href="#">KN-4J2</a>     | \$43.00 | 15  | 4               |            |                                 |                      | 61.0 [2.40]  |                |      |                                                                       |
|                       | <a href="#">KN-10J2</a>    | \$32.00 | 5   | 10              |            |                                 |                      | 157.0 [6.18] |                |      |                                                                       |
|                       | <a href="#">KN-2J1/O</a>   | \$12.00 | 5   | 2               | 1000V 150A | 2.5–3.5 Nm<br>[22.1–31.0 lb-in] | 22.3<br>[0.88]       | 36.0 [1.42]  | 12.0<br>[0.47] | 2    | KN-T1/Oxx                                                             |
|                       | <a href="#">KN-3J1/O</a>   | \$20.00 | 5   | 3               |            |                                 |                      | 56.0 [2.20]  |                |      |                                                                       |
|                       | <a href="#">KN-4J1/O</a>   | \$26.00 | 5   | 4               |            |                                 |                      | 76.0 [2.99]  |                |      |                                                                       |
|                       | <a href="#">KN-2JTL12</a>  | \$20.00 | 25  | 2               | 440V 24A   | 0.4–0.6 Nm<br>[3.5–5.3 lb-in]   | 15.5<br>[0.61]       | 11.0 [0.43]  | 4.4<br>[0.17]  | 1    | KN-DG12<br>KN-TG12<br>KN-TL14<br>KN-TL14S<br>KN-TL14SLN<br>KN-TL14SLP |
|                       | <a href="#">KN-3JTL12</a>  | \$25.00 | 20  | 3               |            |                                 |                      | 17.0 [0.67]  |                |      |                                                                       |
|                       | <a href="#">KN-4JTL12</a>  | \$24.00 | 15  | 4               |            |                                 |                      | 23.0 [0.91]  |                |      |                                                                       |
|                       | <a href="#">KN-10JTL12</a> | \$20.00 | 5   | 10              |            |                                 |                      | 59.0 [2.32]  |                |      |                                                                       |
| Push-in Connection    | <a href="#">KN-2JM10</a>   | \$12.00 | 25  | 2               | 750V 32A   | –                               | 23.2<br>[0.91]       | 9.5 [0.37]   | 2.7<br>[0.11]  | 3    | KN-M10xx<br>KN-KBD10                                                  |
|                       | <a href="#">KN-3JM10</a>   | \$15.00 | 20  | 3               |            |                                 |                      | 15.5 [0.61]  |                |      |                                                                       |
|                       | <a href="#">KN-4JM10</a>   | \$17.00 | 15  | 4               |            |                                 |                      | 21.5 [0.85]  |                |      |                                                                       |
|                       | <a href="#">KN-10JM10</a>  | \$16.00 | 5   | 10              |            |                                 |                      | 57.5 [2.26]  |                |      |                                                                       |
|                       | <a href="#">KN-2JM12</a>   | \$12.00 | 25  | 2               | 750V 24A   | –                               | 21.7<br>[0.85]       | 8.0 [0.31]   | 2.3<br>[0.09]  | 3    | KN-M12xx<br>KN-T12SP4                                                 |
|                       | <a href="#">KN-3JM12</a>   | \$13.00 | 20  | 3               |            |                                 |                      | 13.0 [0.51]  |                |      |                                                                       |
|                       | <a href="#">KN-4JM12</a>   | \$13.00 | 15  | 4               |            |                                 |                      | 18.0 [0.71]  |                |      |                                                                       |
|                       | <a href="#">KN-10JM12</a>  | \$15.00 | 5   | 10              |            |                                 |                      | 48.0 [1.89]  |                |      |                                                                       |
| Screwless Comb-style  | <a href="#">KN-2JCC12</a>  | \$17.00 | 25  | 2               | 750V 24A   | –                               | 23.7<br>[0.93]       | 8.0 [0.31]   | 2.8<br>[0.11]  | 4    | KN-T12xx                                                              |
|                       | <a href="#">KN-2JCC10</a>  | \$34.00 | 25  |                 | 750V 32A   | –                               | 24.7<br>[0.97]       | 9.5 [0.37]   |                |      | KN-T10xx                                                              |
|                       | <a href="#">KN-2JCC8</a>   | \$36.00 | 25  |                 | 630V 41A   | –                               | 25.6<br>[1.01]       | 13.5 [0.53]  |                |      | KN-T8xx                                                               |
|                       | <a href="#">KN-2JCC6</a>   | \$40.00 | 25  |                 | 630V 57A   | –                               | 26.7<br>[1.05]       | 16.0 [0.63]  |                |      | KN-T6xx                                                               |

Figure 1




Figure 2




Figure 3





Figure 4



Please visit our website  
[www.AutomationDirect.com](http://www.AutomationDirect.com)  
 for complete engineering drawings.

Screwless Comb-Style jumpers are designed to be connected under the conductor clamp.



# KONNECT-IT® Accessories

## End Brackets

End brackets prevent terminal blocks and other DIN rail mount components and devices from moving laterally on the rail. They are constructed from polyamide 66 and available in configurations for 35mm and 15mm DIN rails.

Dimensions mm [in]



### End Brackets Ordering Information

|                   |                  |         |         |                  |         |         |                  |         |         |                  |        |         |
|-------------------|------------------|---------|---------|------------------|---------|---------|------------------|---------|---------|------------------|--------|---------|
| Gray End Brackets | <b>KN-EB3</b>    | 100/pkg | \$53.00 | <b>KN-EB4</b>    | 100/pkg | \$55.00 | <b>KN-EB5</b>    | 100/pkg | \$80.00 | <b>KN-EB7</b>    | 50/pkg | \$55.00 |
|                   | <b>KN-EB3-10</b> | 10/pkg  | \$7.00  | <b>KN-EB4-10</b> | 10/pkg  | \$5.00  | <b>KN-EB5-10</b> | 10/pkg  | \$9.00  | <b>KN-EB7-10</b> | 10/pkg | \$11.00 |

### Technical Specifications

|                      |                                                               |                       |                       |                        |
|----------------------|---------------------------------------------------------------|-----------------------|-----------------------|------------------------|
| <b>Description</b>   | Screw-type end bracket                                        | Screwless end bracket | Screwless end bracket | Screw-type end bracket |
| <b>Bracket Width</b> | 8 mm [0.31 in]                                                | 8 mm [0.31 in]        | 8 mm [0.31 in]        | 10 mm [0.39 in]        |
| <b>Mounting</b>      | 35mm DIN rail                                                 | 35mm DIN rail         | 15mm DIN rail         | 35mm DIN rail          |
| <b>Material</b>      | Housing: Polyamide 66 / Clamping Connector: Zinc Plated Steel |                       |                       |                        |


### End Bracket Accessories

|                     |                                |   |   |                   |        |         |   |   |   |                   |        |         |
|---------------------|--------------------------------|---|---|-------------------|--------|---------|---|---|---|-------------------|--------|---------|
| Label Holder        | —                              | — | — | <b>KN-MA-1</b>    | 25/pkg | \$23.50 | — | — | — | <b>KN-MA-2</b>    | 50/pkg | \$59.00 |
|                     | —                              | — | — | <b>KN-MA-1-10</b> | 10/pkg | \$10.50 | — | — | — | <b>KN-MA-2-10</b> | 10/pkg | \$14.00 |
| <b>Marking Tags</b> | KN-L5 Series or KN-L6P5 Series |   |   |                   |        |         |   |   |   |                   |        |         |

## End Covers

End covers are used to cover the open side of sectional DIN rail mount terminal blocks. They should be used at the end of an assembly of identical terminal blocks or whenever there is a change in the physical size of the terminal block.

Material: Polyamide 66



### End Covers Ordering Information

| Part Number          | Color  | Dimensions<br>H x L x W<br>mm [in] | Works<br>With                      | Qty | Price   | Part Number        | Color           | Dimensions<br>H x L x W<br>mm [in] | Works<br>With      | Qty | Price   |
|----------------------|--------|------------------------------------|------------------------------------|-----|---------|--------------------|-----------------|------------------------------------|--------------------|-----|---------|
| <b>KN-ECT6GRY</b>    | Gray   | 34.0x42.7x1.3<br>[1.34x1.68x0.05]  | KN-T12<br>KN-T10<br>KN-T8<br>KN-T6 | 100 | \$29.00 | <b>KN-ECDORG</b>   | Orange          | 48.2x63.2x1.3<br>[1.90x2.49x0.05]  | KN-D10<br>KN-D12   | 10  | \$7.00  |
| <b>KN-ECT6GRY-25</b> | Gray   |                                    |                                    | 25  | \$6.50  | <b>KN-ECDRED</b>   | Red             |                                    |                    |     | \$7.00  |
| <b>KN-ECT6BLU</b>    | Blue   |                                    |                                    |     | \$3.50  | <b>KN-ECDYEL</b>   | Yellow          |                                    |                    |     | \$7.00  |
| <b>KN-ECT6BLK</b>    | Black  |                                    |                                    |     | \$3.50  | <b>KN-ECTL</b>     | Gray            | 54.7x87.1x1.3<br>[2.15x3.43x0.05]  | KN-TL14            | 10  | \$4.00  |
| <b>KN-ECT6BRN</b>    | Brown  |                                    |                                    |     | \$3.50  | <b>KN-ECTLS</b>    | Gray            | 54.7x72.8x1.2<br>[2.15x2.87x0.05]  | KN-TL14S           | 10  | \$5.00  |
| <b>KN-ECT6GRN</b>    | Green  |                                    |                                    | 10  | \$3.50  | <b>KN-ECDG12</b>   | Gray            | 48.0x71.4x1.2<br>[1.89x2.81x0.05]  | KN-DG12            | 10  | \$5.00  |
| <b>KN-ECT6ORG</b>    | Orange |                                    |                                    |     | \$3.50  | <b>KN-ECTG12</b>   | Gray            | 62.5x87.5x1.2<br>[2.46x3.44x0.05]  | KN-TG12            | 10  | \$5.00  |
| <b>KN-ECT6RED</b>    | Red    |                                    |                                    |     | \$3.50  | <b>KN-ECMGY</b>    | Gray            | 28.1x27.0x3.0<br>[1.11x1.06x0.12]  | KN-M12<br>KN-M10   | 100 | \$61.00 |
| <b>KN-ECT6WHT</b>    | White  |                                    |                                    |     | \$3.50  | <b>KN-ECMGY-10</b> | Gray            |                                    |                    | 10  | \$6.50  |
| <b>KN-ECT6YEL</b>    | Yellow |                                    |                                    |     | \$3.50  | <b>KN-ECMBLU</b>   | Blue            |                                    |                    |     | \$6.50  |
| <b>KN-ECT4GRY</b>    | Gray   | 45.7x52.8x1.2<br>[1.80x2.08x0.05]  | KN-T4                              | 25  | \$14.00 | <b>KN-ECMGRN</b>   | Green<br>Yellow | 28.1x27.0x3.0<br>[1.11x1.06x0.12]  | KN-MG12<br>KN-MG10 | 10  | \$6.50  |
| <b>KN-ECT4BLU</b>    | Blue   |                                    |                                    | 10  | \$6.00  | <b>KN-ECG12SP4</b> | Green<br>Yellow | 39.7x57.1x1.2<br>[1.56x2.25x0.05]  | KN-G12SP4          | 10  | \$5.00  |
| <b>KN-ECDGRY</b>     | Gray   | 48.2x63.2x1.3<br>[1.90x2.49x0.05]  | KN-D10<br>KN-D12                   | 25  | \$15.00 | <b>KN-ECT12SP4</b> | Gray            | 39.7x57.1x1.2<br>[1.56x2.25x0.05]  | KN-T12SP4          | 25  | \$13.00 |
| <b>KN-ECDBLU</b>     | Blue   |                                    |                                    | 10  | \$7.00  | <b>KN-ECF10</b>    | Gray            | 27.3x59.6x1.2<br>[1.07x2.35x0.05]  | KN-F10             | 25  | \$16.00 |
| <b>KN-ECDBLK</b>     | Black  |                                    |                                    |     | \$7.00  | <b>KN-ECKBD</b>    | Gray            | 37.1x53.5x1.2<br>[1.46x2.11x0.05]  | KN-KDB10           | 10  | \$6.50  |
| <b>KN-ECDGRN</b>     | Green  |                                    |                                    |     | \$7.00  |                    |                 |                                    |                    |     |         |



# KONNECT-IT® Accessories

## Separators

Separators are used to segment banks of terminal blocks. Allows you to maintain a single row of terminal blocks, but have separate power source clusters.

| Separators Ordering Information |        |                                    |                      |             |            |     |         |  |
|---------------------------------|--------|------------------------------------|----------------------|-------------|------------|-----|---------|--|
| Part Number                     | Color  | Works With                         | Dimensions - mm [in] |             |            | Qty | Price   |  |
|                                 |        |                                    | Height               | Length      | Thickness  |     |         |  |
| <a href="#">KN-ST1GRY</a>       | Gray   | KN-T12<br>KN-T10<br>KN-T8<br>KN-T6 | 39.0 [1.54]          | 42.5 [1.67] | 1.2 [0.05] | 25  | \$12.50 |  |
| <a href="#">KN-ST1BLU</a>       | Blue   |                                    |                      |             |            | 10  | \$4.75  |  |
| <a href="#">KN-ST1BLK</a>       | Black  |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1BRN</a>       | Brown  |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1GRN</a>       | Green  |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1ORG</a>       | Orange |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1RED</a>       | Red    |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1WHT</a>       | White  |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST1YEL</a>       | Yellow |                                    |                      |             |            |     | \$4.75  |  |
| <a href="#">KN-ST2GRY</a>       | Gray   | KN-T4                              | 52.5 [2.07]          | 50.5 [1.99] | 1.5 [0.06] | 25  | \$16.00 |  |
| <a href="#">KN-ST2BLU</a>       | Blue   |                                    |                      |             |            | 10  | \$16.00 |  |
| <a href="#">KN-ST3GRY</a>       | Gray   | KN-T2                              | 62.6 [2.46]          | 53.1 [2.09] | 1.5 [0.06] |     | \$8.00  |  |
| <a href="#">KN-ST3BLU</a>       | Blue   |                                    |                      |             |            |     | \$8.00  |  |

**KN-ST1GRY**



## Top Covers and Label Holders

| Top Covers and Label Holders Ordering Information |                                                                                                                                                        |                                    |                      |                |                |     |         |
|---------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|----------------------|----------------|----------------|-----|---------|
| Part Number                                       | Description                                                                                                                                            | Works With                         | Dimensions - mm [in] |                |                | Qty | Price   |
|                                                   |                                                                                                                                                        |                                    | Height               | Length         | Width          |     |         |
| <a href="#">KN-TC-1</a>                           | Top cover for Konnect-It terminal block, blank, white                                                                                                  | KN-T12<br>KN-T10<br>KN-T8<br>KN-T6 | 6.8<br>[0.27]        | 29.0<br>[1.14] | 5.8<br>[0.23]  | 25  | \$9.75  |
| <a href="#">KN-TC-1S</a>                          | Top cover for Konnect-It terminal block, printed electric symbol, white                                                                                |                                    |                      |                |                | 25  | \$14.00 |
| <a href="#">KN-TC-2</a>                           | Top cover for Konnect-It terminal block, blank, white                                                                                                  | KN-T4<br>KN-T2                     | 7.3<br>[0.29]        | 35.8<br>[1.41] | 9.0<br>[0.35]  | 25  | \$25.00 |
| <a href="#">KN-TC-2S</a>                          | Top cover for Konnect-It terminal block, printed electric symbol, white                                                                                |                                    |                      |                |                | 25  | \$25.00 |
| <a href="#">KN-MA-1</a>                           | Label holder for terminal block group. Label media not included.<br>Adhesive label: Apply on top.<br>Max label dimensions: 7 x 44 mm (0.28 x 1.73 in). | KN-EB4                             | 46.2<br>[1.82]       | 46.0<br>[1.81] | 11.4<br>[0.45] | 25  | \$23.50 |
| <a href="#">KN-MA-1-10</a>                        |                                                                                                                                                        |                                    |                      |                |                | 10  | \$10.50 |
| <a href="#">KN-MA-2</a>                           | Label holder for terminal block group. Label media not included.<br>Adhesive label: Apply on top.<br>Max label dimensions: 7 x 44 mm (0.28 x 1.73 in). | KN-EB7                             | 37.5<br>[1.48]       | 46.2<br>[1.82] | 9.5<br>[0.37]  | 50  | \$59.00 |
| <a href="#">KN-MA-2-10</a>                        |                                                                                                                                                        |                                    |                      |                |                | 10  | \$14.00 |
| <a href="#">KN-MA-3</a>                           | Top mounting marking tag adapter for terminal block.<br>Holds up to (4) L5x5 tags                                                                      | KN-T4<br>KN-T2                     | 9.3<br>[0.36]        | 36.0<br>[1.42] | 9.0<br>[0.35]  | 25  | \$15.50 |
| <a href="#">KN-MA-4</a>                           | Top mounting marking tag adapter for terminal block.<br>Holds up to (4) L5x5 tags                                                                      | KN-T12<br>KN-T10<br>KN-T8<br>KN-T6 | 9.0<br>[0.35]        | 29.0<br>[1.14] | 5.7<br>[0.22]  | 25  | \$14.00 |
| <a href="#">KN-MA-5</a>                           | Label holder for terminal block group. Label media included.<br>Max label dimensions: 10 x 38mm (0.39 x 1.50 in).<br>Thickness 0.30 mm (0.01 in)       | Attaches to any 35mm DIN rail      | 46.4<br>[1.83]       | 44.5<br>[1.75] | 10.0<br>[0.39] | 50  | \$48.00 |
| <a href="#">KN-MA-5-25</a>                        |                                                                                                                                                        |                                    |                      |                |                | 25  | \$29.50 |

**KN-MA-1**



**KN-MA-2**



**KN-MA-5**



**KN-TC-1 / KN-TC-2**



**KN-TC-1S / KN-TC-2S**



**KN-MA-3**



**KN-MA-4**







# KONNECT-IT Accessories

## Marking Tags 5 x 5mm

Use with any KONNECT-IT series terminal blocks.



### 5 x 5mm Marking Tags Ordering Information

| 250 Pieces per Package                   |         |         |                                      |         |         | 500 Pieces per Package               |         |         |                                  |         |         |
|------------------------------------------|---------|---------|--------------------------------------|---------|---------|--------------------------------------|---------|---------|----------------------------------|---------|---------|
| Part Number                              | Imprint | Price   | Part Number                          | Imprint | Price   | Part Number                          | Imprint | Price   | Part Number                      | Imprint | Price   |
| <a href="#"><u>KN-L5-BLANK-250</u></a>   | Blank   | \$13.00 | <a href="#"><u>KN-L5-A-250</u></a>   | A       | \$13.00 | <a href="#"><u>KN-L5-BLANK</u></a>   | Blank   | \$20.00 | <a href="#"><u>KN-L5-A</u></a>   | A       | \$24.00 |
| <a href="#"><u>KN-L5-0-250</u></a>       | 0       | \$13.00 | <a href="#"><u>KN-L5-B-250</u></a>   | B       | \$13.00 | <a href="#"><u>KN-L5-0</u></a>       | 0       | \$24.00 | <a href="#"><u>KN-L5-B</u></a>   | B       | \$24.00 |
| <a href="#"><u>KN-L5-1-250</u></a>       | 1       | \$13.00 | <a href="#"><u>KN-L5-C-250</u></a>   | C       | \$13.00 | <a href="#"><u>KN-L5-1</u></a>       | 1       | \$24.00 | <a href="#"><u>KN-L5-C</u></a>   | C       | \$24.00 |
| <a href="#"><u>KN-L5-2-250</u></a>       | 2       | \$13.00 | <a href="#"><u>KN-L5-D-250</u></a>   | D       | \$13.00 | <a href="#"><u>KN-L5-2</u></a>       | 2       | \$24.00 | <a href="#"><u>KN-L5-D</u></a>   | D       | \$24.00 |
| <a href="#"><u>KN-L5-3-250</u></a>       | 3       | \$13.00 | <a href="#"><u>KN-L5-E-250</u></a>   | E       | \$13.00 | <a href="#"><u>KN-L5-3</u></a>       | 3       | \$24.00 | <a href="#"><u>KN-L5-E</u></a>   | E       | \$24.00 |
| <a href="#"><u>KN-L5-4-250</u></a>       | 4       | \$13.00 | <a href="#"><u>KN-L5-F-250</u></a>   | F       | \$13.00 | <a href="#"><u>KN-L5-4</u></a>       | 4       | \$24.00 | <a href="#"><u>KN-L5-F</u></a>   | F       | \$24.00 |
| <a href="#"><u>KN-L5-5-250</u></a>       | 5       | \$13.00 | <a href="#"><u>KN-L5-G-250</u></a>   | G       | \$13.00 | <a href="#"><u>KN-L5-5</u></a>       | 5       | \$24.00 | <a href="#"><u>KN-L5-G</u></a>   | G       | \$24.00 |
| <a href="#"><u>KN-L5-6-250</u></a>       | 6       | \$13.00 | <a href="#"><u>KN-L5-H-250</u></a>   | H       | \$13.00 | <a href="#"><u>KN-L5-6</u></a>       | 6       | \$24.00 | <a href="#"><u>KN-L5-H</u></a>   | H       | \$24.00 |
| <a href="#"><u>KN-L5-7-250</u></a>       | 7       | \$13.00 | <a href="#"><u>KN-L5-I-250</u></a>   | I       | \$13.00 | <a href="#"><u>KN-L5-7</u></a>       | 7       | \$24.00 | <a href="#"><u>KN-L5-I</u></a>   | I       | \$24.00 |
| <a href="#"><u>KN-L5-8-250</u></a>       | 8       | \$13.00 | <a href="#"><u>KN-L5-J-250</u></a>   | J       | \$13.00 | <a href="#"><u>KN-L5-8</u></a>       | 8       | \$24.00 | <a href="#"><u>KN-L5-J</u></a>   | J       | \$25.00 |
| <a href="#"><u>KN-L5-9-250</u></a>       | 9       | \$13.00 | <a href="#"><u>KN-L5-K-250</u></a>   | K       | \$13.00 | <a href="#"><u>KN-L5-9</u></a>       | 9       | \$24.00 | <a href="#"><u>KN-L5-K</u></a>   | K       | \$25.00 |
| <a href="#"><u>KN-L5-10-250</u></a>      | 10      | \$13.00 | <a href="#"><u>KN-L5-L-250</u></a>   | L       | \$12.50 | <a href="#"><u>KN-L5-10</u></a>      | 10      | \$24.00 | <a href="#"><u>KN-L5-L</u></a>   | L       | \$24.00 |
| <a href="#"><u>KN-L5-1-10-250</u></a>    | 1-10    | \$13.00 | <a href="#"><u>KN-L5-M-250</u></a>   | M       | \$13.00 | <a href="#"><u>KN-L5-1-10</u></a>    | 1-10    | \$24.00 | <a href="#"><u>KN-L5-M</u></a>   | M       | \$25.00 |
| <a href="#"><u>KN-L5-11-20-250</u></a>   | 11-20   | \$13.00 | <a href="#"><u>KN-L5-N-250</u></a>   | N       | \$12.50 | <a href="#"><u>KN-L5-11-20</u></a>   | 11-20   | \$24.00 | <a href="#"><u>KN-L5-N</u></a>   | N       | \$24.00 |
| <a href="#"><u>KN-L5-21-30-250</u></a>   | 21-30   | \$13.00 | <a href="#"><u>KN-L5-O-250</u></a>   | O       | \$12.50 | <a href="#"><u>KN-L5-21-30</u></a>   | 21-30   | \$24.00 | <a href="#"><u>KN-L5-O</u></a>   | O       | \$24.00 |
| <a href="#"><u>KN-L5-31-40-250</u></a>   | 31-40   | \$13.00 | <a href="#"><u>KN-L5-P-250</u></a>   | P       | \$13.00 | <a href="#"><u>KN-L5-31-40</u></a>   | 31-40   | \$24.00 | <a href="#"><u>KN-L5-P</u></a>   | P       | \$25.00 |
| <a href="#"><u>KN-L5-41-50-250</u></a>   | 41-50   | \$13.00 | <a href="#"><u>KN-L5-Q-250</u></a>   | Q       | \$13.00 | <a href="#"><u>KN-L5-41-50</u></a>   | 41-50   | \$24.00 | <a href="#"><u>KN-L5-Q</u></a>   | Q       | \$25.00 |
| <a href="#"><u>KN-L5-1-50-250</u></a>    | 1-50    | \$13.00 | <a href="#"><u>KN-L5-R-250</u></a>   | R       | \$12.50 | <a href="#"><u>KN-L5-1-50</u></a>    | 1-50    | \$24.00 | <a href="#"><u>KN-L5-R</u></a>   | R       | \$24.00 |
| <a href="#"><u>KN-L5-51-100-250</u></a>  | 51-100  | \$13.00 | <a href="#"><u>KN-L5-S-250</u></a>   | S       | \$12.50 | <a href="#"><u>KN-L5-51-100</u></a>  | 51-100  | \$24.00 | <a href="#"><u>KN-L5-S</u></a>   | S       | \$24.00 |
| <a href="#"><u>KN-L5-101-150-250</u></a> | 101-150 | \$13.00 | <a href="#"><u>KN-L5-T-250</u></a>   | T       | \$12.50 | <a href="#"><u>KN-L5-101-150</u></a> | 101-150 | \$24.00 | <a href="#"><u>KN-L5-T</u></a>   | T       | \$24.00 |
| <a href="#"><u>KN-L5-151-200-250</u></a> | 151-200 | \$13.00 | <a href="#"><u>KN-L5-U-250</u></a>   | U       | \$13.00 | <a href="#"><u>KN-L5-151-200</u></a> | 151-200 | \$24.00 | <a href="#"><u>KN-L5-U</u></a>   | U       | \$25.00 |
| <a href="#"><u>KN-L5-201-250-250</u></a> | 201-250 | \$13.00 | <a href="#"><u>KN-L5-V-250</u></a>   | V       | \$12.50 | <a href="#"><u>KN-L5-201-250</u></a> | 201-250 | \$24.00 | <a href="#"><u>KN-L5-V</u></a>   | V       | \$24.00 |
| <a href="#"><u>KN-L5-251-300-250</u></a> | 251-300 | \$13.00 | <a href="#"><u>KN-L5-W-250</u></a>   | W       | \$13.00 | <a href="#"><u>KN-L5-251-300</u></a> | 251-300 | \$24.00 | <a href="#"><u>KN-L5-W</u></a>   | W       | \$25.00 |
| <a href="#"><u>KN-L5-301-350-250</u></a> | 301-350 | \$13.00 | <a href="#"><u>KN-L5-X-250</u></a>   | X       | \$12.50 | <a href="#"><u>KN-L5-301-350</u></a> | 301-350 | \$24.00 | <a href="#"><u>KN-L5-X</u></a>   | X       | \$24.00 |
| <a href="#"><u>KN-L5-351-400-250</u></a> | 351-400 | \$13.00 | <a href="#"><u>KN-L5-Y-250</u></a>   | Y       | \$12.50 | <a href="#"><u>KN-L5-351-400</u></a> | 351-400 | \$24.00 | <a href="#"><u>KN-L5-Y</u></a>   | Y       | \$24.00 |
| <a href="#"><u>KN-L5-401-450-250</u></a> | 401-450 | \$13.00 | <a href="#"><u>KN-L5-Z-250</u></a>   | Z       | \$13.00 | <a href="#"><u>KN-L5-401-450</u></a> | 401-450 | \$24.00 | <a href="#"><u>KN-L5-Z</u></a>   | Z       | \$25.00 |
| <a href="#"><u>KN-L5-451-500-250</u></a> | 451-500 | \$13.00 | <a href="#"><u>KN-L5-POS-250</u></a> | +       | \$12.50 | <a href="#"><u>KN-L5-451-500</u></a> | 451-500 | \$24.00 | <a href="#"><u>KN-L5-POS</u></a> | +       | \$24.00 |
| <a href="#"><u>KN-L5-L1-250</u></a>      | L1      | \$12.50 | <a href="#"><u>KN-L5-NEG-250</u></a> | -       | \$12.50 | <a href="#"><u>KN-L5-L1</u></a>      | L1      | \$24.00 | <a href="#"><u>KN-L5-NEG</u></a> | -       | \$24.00 |
| <a href="#"><u>KN-L5-L2-250</u></a>      | L2      | \$12.50 | <a href="#"><u>KN-L5-GND-250</u></a> | GND     | \$13.00 | <a href="#"><u>KN-L5-L2</u></a>      | L2      | \$24.00 | <a href="#"><u>KN-L5-GND</u></a> | GND     | \$24.00 |
| <a href="#"><u>KN-L5-L3-250</u></a>      | L3      | \$12.50 |                                      |         |         | <a href="#"><u>KN-L5-L3</u></a>      | L3      | \$24.00 |                                  |         |         |



# KONNECT-IT Accessories


## Marking Tags 6 x 11.5 mm

Use with Konnect-It series terminal blocks  
6.5mm or wider.



## Marking Tags 5 x 10mm, 6 x 10mm, 10 x 10mm

Use with Konnect-It series terminal blocks  
5 x 10mm, 6 x 10mm, and 10 x 10mm.



| Marking Tags 6 x 11.5mm                   |                 |     |         |
|-------------------------------------------|-----------------|-----|---------|
| Part Number                               | Description     | Qty | Price   |
| <a href="#"><u>KN-L6P5-BLNK</u></a>       | Blank           | 500 | Retired |
| <a href="#"><u>KN-L6P5-BLNK-250</u></a>   | Blank           | 250 | Retired |
| <a href="#"><u>KN-L6P5-BLNK-300</u></a>   | Blank           | 300 | \$15.00 |
| <a href="#"><u>KN-L6P5-1-10</u></a>       | Numbered 1-10   | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-1-10-250</u></a>   | Numbered 1-10   | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-1-10-300</u></a>   | Numbered 1-10   | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-11-20</u></a>      | Numbered 11-20  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-11-20-250</u></a>  | Numbered 11-20  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-11-20-300</u></a>  | Numbered 11-20  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-21-30</u></a>      | Numbered 21-30  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-21-30-250</u></a>  | Numbered 21-30  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-21-30-300</u></a>  | Numbered 21-30  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-31-40</u></a>      | Numbered 31-40  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-31-40-250</u></a>  | Numbered 31-40  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-31-40-300</u></a>  | Numbered 31-40  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-41-50</u></a>      | Numbered 41-50  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-41-50-250</u></a>  | Numbered 41-50  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-41-50-300</u></a>  | Numbered 41-50  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-51-60</u></a>      | Numbered 51-60  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-51-60-250</u></a>  | Numbered 51-60  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-51-60-300</u></a>  | Numbered 51-60  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-61-70</u></a>      | Numbered 61-70  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-61-70-250</u></a>  | Numbered 61-70  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-61-70-300</u></a>  | Numbered 61-70  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-71-80</u></a>      | Numbered 71-80  | 500 | \$57.00 |
| <a href="#"><u>KN-L6P5-71-80-250</u></a>  | Numbered 71-80  | 250 | \$31.50 |
| <a href="#"><u>KN-L6P5-71-80-300</u></a>  | Numbered 71-80  | 300 | \$34.00 |
| <a href="#"><u>KN-L6P5-81-90</u></a>      | Numbered 81-90  | 500 | \$58.00 |
| <a href="#"><u>KN-L6P5-81-90-250</u></a>  | Numbered 81-90  | 250 | \$32.00 |
| <a href="#"><u>KN-L6P5-91-100</u></a>     | Numbered 91-100 | 500 | \$58.00 |
| <a href="#"><u>KN-L6P5-91-100-250</u></a> | Numbered 91-100 | 250 | \$32.00 |

| Marking Tags                            |                                                                                    |     |         |
|-----------------------------------------|------------------------------------------------------------------------------------|-----|---------|
| Part Number*                            | Description                                                                        | Qty | Price   |
| <a href="#"><u>KN-L5X-BLNK</u></a>      | Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series         | 440 | \$21.50 |
| <a href="#"><u>KN-L5X-BLNK-220</u></a>  | Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series         | 220 | \$11.50 |
| <a href="#"><u>KN-L6X-BLNK</u></a>      | Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider   | 360 | \$18.50 |
| <a href="#"><u>KN-L6X-BLNK-180</u></a>  | Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider   | 180 | \$9.75  |
| <a href="#"><u>KN-L10X-BLNK</u></a>     | Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider | 200 | \$29.00 |
| <a href="#"><u>KN-L10X-BLNK-100</u></a> | Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider | 100 | \$16.00 |

\*Does not fit any KN-T1/0xx or [KN-G1/0](#) series block