KONNECT-IT TERMINAL BLOCKS Ground Terminal Blocks



- Screw connection terminal
- PE screw connection DIN Rail
- UL E179129 (For copper wire only. One conductor in terminal only.)
- CE (EN 60947-7-1/ EN 60947-7-2)
- VDE (IEC 60947-7-1)

Dimensions: mm [in]

KN-G10



KN-G8



KN-G4



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
Green Yellow	KN-G10	50	$154.00	KN-G8	25	$97.00	KN-G4	50	$378.00
	KN-G10-10	10	$33.00	KN-G8-10	10	$40.00	KN-G4-10	10	$74.00

Technical Specifications

Model	KN-G10			KN-G8			KN-G4		
Width	6mm [0.24 in]			10mm [0.39 in]			12mm [0.47 in]		
Stripping Length	10mm [0.39 in]			12mm [0.47 in]			12mm [0.47 in]		
Tightening Torque	0.5 N·m [4.4 lb·in]			1.2 N·m [10.6 lb·in]			1.2 N·m [10.6 lb·in]		
Density	166/m [50 pcs/ft]			100/m [30 pcs/ft]			83/m [25 pcs/ft]		
UL/CSA Approval	—	—	26-10 AWG	—	—	16-8 AWG	—	—	12-4 AWG
VDE Approval	—	—	4mm²	—	—	10mm²	—	—	16mm²
CE Conformity	—	—	4mm²	—	—	10mm²	—	—	16mm²
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]								
SCCR Rating	100kA per Table SB4.1, 2009, UL 508A. Maximum short circuit current rating for unmarked components.								
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel								
Mounting	35mm DIN rail								

Accessories

Marking Tags	KN-L5 Series	KN-L5 Series KN-L6 Series	KN-L5 Series KN-L6 Series

KONNECT-IT TERMINAL BLOCKS Ground Terminal Blocks



- Spring clamp terminal
- UL E179129
  (For copper wire only. One conductor in terminal only.)
- CE (EN 60947-7-1/ EN 60947-7-2)
- VDE (IEC 60947-7-1)

Dimensions: mm [in]

KN-G2



KN-G1/0



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price
Green Yellow	KN-G2	40	$332.00	KN-G1/0	10	$96.00
	KN-G2-10	10	$80.00	KN-G1/0-5	5	$51.00

Technical Specifications

Model	KN-G2			KN-G1/0		
Width	16mm [0.63 in]			20mm [0.79 in]		
Stripping Length	18mm [0.71 in]			20mm [0.79 in]		
Tightening Torque	2.5 N·m [22.1 lb·in]			6 N·m [22.1 lb·in]		
Density	62/m [19 pcs/ft]			50/m [15 pcs/ft]		
UL/CSA Approval	—	—	12-2 AWG	—	—	6-1/0 AWG
VDE Approval	—	—	35mm²	—	—	50mm²
CE Conformity	—	—	35mm²	—	—	50mm²
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C] Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]					
SCCR Rating	100kA per Table SB4.1, 2009, UL 508A. Maximum short circuit current rating for unmarked components.					
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel					
Mounting	35mm DIN rail					

Accessories

Marking Tags	KN-L5 Series KN-L6P5 Series	No tags available

KONNECT-IT TERMINAL BLOCKS

Ground Terminal Blocks



- Screw connection terminal
- PE snap-on connection
- UL E179129
  (For copper wire only. One conductor in terminal only.)
- CE (EN 60947-7-1/ EN 60947-7-2)
- VDE (IEC 60947-7-2)

Dimensions: mm [in]

KN-G12SP



KN-G12SP4



KN-G10SP



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
Green Yellow	KN-G12SP	50	$123.00	KN-G12SP4	25	$97.00	KN-G10SP	50	$138.00
	KN-G12SP-10	10	$27.00	KN-G12SP4-10	10	$41.00	KN-G10SP-10	10	$31.00

Technical Specifications

Model	KN-G12SP			KN-G12SP4			KN-G10SP		
Width	5.75 mm [0.23 in]			5mm [0.20 in]			6mm [0.24 in]		
Stripping Length	10mm [0.39 in]			10mm [0.39 in]			10mm [0.39 in]		
Tightening Torque	0.4 N·m [3.5 lb·in]			0.5 N·m [4.4 lb·in]			0.5 N·m [4.4 lb·in]		
Density	53 pcs/ft [173/m]			200/m [60 pcs/ft]			161/m [49 pcs/ft]		
UL/CSA Approval	—	—	26-12 AWG	—	—	26-12 AWG	—	—	26-10 AWG
VDE Approval	—	—	2.5 mm²	—	—	2.5 mm²	—	—	4mm²
CE Conformity	—	—	2.5 mm²	—	—	2.5 mm²	—	—	4mm²
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]								
SCCR Rating	100kA per Table SB4.1, 2009, UL 508A. Maximum short circuit current rating for unmarked components.								
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel								
Mounting	35mm DIN rail								

Accessories

End Covers	Yellow/Green	—	—	—	KN-ECG12SP4	10/pkg	$5.00	—	—	—
Marking Tags		KN-L5 Series			KN-L5 Series			KN-L5 Series		

KONNECT-IT® Accessories

Multi-Pole Jumper Bars

Multi-pole jumper bars provide terminal block connection flexibility. Screw-down connection jumpers feature all-metal construction and can be installed quickly just by tightening the screws. Screwless comb-style jumpers are also available. See next page for the larger J1/0 jumper installation instructions.

KN-10J12

KN-2JM12

KN-2JCC8

Multi-Pole Jumper Bars Ordering Information

Type	Part Number	Price	Qty	Number of Poles	Rating		Tightening Torque	Dimensions - mm [in]			Fig.	Works With
								Height	Length	Width		
Screw-down connection	KN-2J12	$13.00	25	2	750V	24A	0.4– 0.6 Nm [3.5–5.3 lb-in]	15.8 [0.62]	10.1 [0.40]	4.4 [0.17]	1	KN-T12xx KN-D12xx KN-D12X KN-D12DR1 KN-D12LEDxx
	KN-3J12	$16.00	20	3					15.3 [0.60]			
	KN-4J12	$20.00	15	4					20.4 [0.80]			
	KN-10J12	$13.00	5	10					51.1 [2.01]			
	KN-2J10	$19.00	25	2	750V	32A	0.6– 0.8 Nm [5.3–7.1 Lb-In]	15.5 [0.61]	10.8 [0.43]	6.0 [0.24]	1	KN-T10xx KN-D10xx KN-D10X KN-D10DR1 KN-D10LEDxx
	KN-3J10	$23.00	20	3					17.0 [0.67]			
	KN-4J10	$23.00	15	4					23.0 [0.91]			
	KN-10J10	$16.00	5	10					59.0 [2.32]			
	KN-2J8	$20.00	25	2	630V	41A	0.6– 0.8 Nm [5.3–7.1 lb-In]	15.5 [0.61]	14.3 [0.56]	6.0 [0.24]	1	KN-T8xx
	KN-3J8	$24.00	20	3					22.3 [0.88]			
	KN-4J8	$24.00	15	4					30.3 [1.19]			
	KN-10J8	$19.00	5	10					78.3 [3.08]			
	KN-2J6	$25.00	25	2	630V	57A	0.6– 0.8 Nm [5.3–7.1 lb-In]	15.5 [0.61]	18.0 [0.71]	6.0 [0.24]	1	KN-T6xx
	KN-3J6	$26.00	20	3					28.0 [1.10]			
	KN-4J6	$26.00	15	4					38.0 [1.50]			
	KN-10J6	$20.00	5	10					98.0 [3.86]			
	KN-2J4	$39.00	25	2	750V	76A	0.6– 0.8 Nm [5.3–7.1 lb-In]	23.0 [0.91]	21.0 [0.83]	6.0 [0.24]	1	KN-T4xx
	KN-3J4	$41.00	20	3					33.0 [1.30]			
	KN-4J4	$41.00	15	4					45.0 [1.77]			
	KN-10J4	$32.00	5	10					117.0 [4.61]			
	KN-2J2	$40.00	25	2	750V	125A	1.2–1.4 Nm [10.6–12.4 lb-In]	21.0 [0.83]	29.0 [1.14]	8.0 [0.31]	1	KN-T2xx
	KN-3J2	$43.00	20	3					45.0 [1.77]			
	KN-4J2	$43.00	15	4					61.0 [2.40]			
	KN-10J2	$32.00	5	10					157.0 [6.18]			
	KN-2J1/0	$12.00	5	2	1000V	150A	2.5–3.5 Nm [22.1–31.0 lb-In]	22.3 [0.88]	36.0 [1.42]	12.0 [0.47]	2	KN-T1/0xx
	KN-3J1/0	$20.00	5	3					56.0 [2.20]			
	KN-4J1/0	$26.00	5	4					76.0 [2.99]			
	KN-2JTL12	$20.00	25	2	440V	24A	0.4–0.6 Nm [3.5 - 5.3 lb-In]	15.5 [0.61]	11.0 [0.43]	4.4 [0.17]	1	KN-DG12 KN-TG12 KN-TL14 KN-TL14S KN-TL14SLN KN-TL14SLP
	KN-3JTL12	$25.00	20	3					17.0 [0.67]			
	KN-4JTL12	$24.00	15	4					23.0 [0.91]			
	KN-10JTL12	$20.00	5	10					59.0 [2.32]			
Push-in Connection	KN-2JM10	$12.00	25	2	750V	32A	–	23.2 [0.91]	9.5 [0.37]	2.7 [0.11]	3	KN-M10xx KN-KBD10
	KN-3JM10	$15.00	20	3					15.5 [0.61]			
	KN-4JM10	$17.00	15	4					21.5 [0.85]			
	KN-10JM10	$16.00	5	10					57.5 [2.26]			
	KN-2JM12	$12.00	25	2	750V	24A	–	21.7 [0.85]	8.0 [0.31]	2.3 [0.09]	3	KN-M12xx KN-T12SP4
	KN-3JM12	$13.00	20	3					13.0 [0.51]			
	KN-4JM12	$13.00	15	4					18.0 [0.71]			
	KN-10JM12	$15.00	5	10					48.0 [1.89]			
Screwless Comb-style	KN-2JCC12	$17.00	25	2	750V	24A	–	23.7 [0.93]	8.0 [0.31]	2.8 [0.11]	4	KN-T12xx
	KN-2JCC10	$34.00	25		750V	32A	–	24.7 [0.97]	9.5 [0.37]			KN-T10xx
	KN-2JCC8	$36.00	25		630V	41A	–	25.6 [1.01]	13.5 [0.53]			KN-T8xx
	KN-2JCC6	$40.00	25		630V	57A	–	26.7 [1.05]	16.0 [0.63]	3.9 [0.15]		KN-T6xx

Figure 1



Figure 2



Figure 3



Figure 4



Please visit our website www.AutomationDirect.com for complete engineering drawings.

Screwless Comb-Style jumpers are designed to be connected under the conductor clamp.

KONNECT-IT® Accessories

End Brackets

End brackets prevent terminal blocks and other DIN rail mount components and devices from moving laterally on the rail. They are constructed from polyamide 66 and available in configurations for 35mm and 15mm DIN rails.

Dimensions mm [in]

KN-EB3

KN-EB4



KN-EB5



KN-EB7



End Brackets Ordering Information												
Gray End Brackets	***KN-EB3***	100/pkg	$53.00	***KN-EB4***	100/pkg	$55.00	***KN-EB5***	100/pkg	$80.00	***KN-EB7***	50/pkg	$55.00
	KN-EB3-10	10/pkg	$7.00	***KN-EB4-10***	10/pkg	$5.00	***KN-EB5-10***	10/pkg	$9.00	***KN-EB7-10***	10/pkg	$11.00
Technical Specifications												
Description	Screw-type end bracket			Screwless end bracket			Screwless end bracket			Screw-type end bracket		
Bracket Width	8 mm [0.31 in]			8 mm [0.31 in]			8 mm [0.31 in]			10 mm [0.39 in]		
Mounting	35mm DIN rail			35mm DIN rail			15mm DIN rail			35mm DIN rail		
Material	Housing: Polyamide 66 / Clamping Connector: Zinc Plated Steel											
End Bracket Accessories												
Label Holder	—	—	—	***KN-MA-1***	25/pkg	$23.50	—	—	—	***KN-MA-2***	50/pkg	$59.00
	—	—	—	***KN-MA-1-10***	10/pkg	$10.50	—	—	—	***KN-MA-2-10***	10/pkg	$14.00
Marking Tags	KN-L5 Series or KN-L6P5 Series											

End Covers

End covers are used to cover the open side of sectional DIN rail mount terminal blocks. They should be used at the end of an assembly of identical terminal blocks or whenever there is a change in the physical size of the terminal block.
Material: Polyamide 66

End Covers Ordering Information											
Part Number	***Color***	***Dimensions H x L x W mm [in]***	***Works With***	***Qty***	***Price***	***Part Number***	***Color***	***Dimensions H x L x W mm [in]***	***Works With***	***Qty***	***Price***
KN-ECT6GRY	Gray	34.0x42.7x1.3 [1.34x1.68x0.05]	KN-T12 KN-T10 KN-T8 KN-T6	100	$29.00	***KN-ECDORG***	Orange	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	10	$7.00
KN-ECT6GRY-25	Gray			25	$6.50	***KN-ECDRED***	Red				$7.00
KN-ECT6BLU	Blue			10	$3.50	***KN-ECDYEL***	Yellow				$7.00
KN-ECT6BLK	Black				$3.50	***KN-ECTL***	Gray	54.7x87.1x1.3 [2.15x3.43x0.05]	KN-TL14	10	$4.00
KN-ECT6BRN	Brown				$3.50	***KN-ECTLS***	Grayy	54.7x72.8x1.2 [2.15x2.87x0.05]	KN-TL14S	10	$5.00
KN-ECT6GRN	Green				$3.50	***KN-ECDG12***	Gray	48.0x71.4x1.2 [1.89x2.81x0.05]	KN-DG12	10	$5.00
KN-ECT6ORG	Orange				$3.50	***KN-ECTG12***	Gray	62.5x87.5x1.2 [2.46x3.44x0.05]	KN-TG12	10	$5.00
KN-ECT6RED	Red				$3.50	***KN-ECMGRY***	Gray	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-M12 KN-M10	100	$61.00
KN-ECT6WHT	White				$3.50	***KN-ECMGRY-10***	Gray			10	$6.50
KN-ECT6YEL	Yellow				$3.50	***KN-ECMBLU***	Blue				$6.50
KN-ECT4GRY	Gray	45.7x52.8x1.2 [1.80x2.08x0.05]	KN-T4	25	$14.00	***KN-ECMGRN***	Green Yellow	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-MG12 KN-MG10	10	$6.50
KN-ECT4BLU	Blue			10	$6.00	***KN-ECG12SP4***	Green Yellow	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-G12SP4	10	$5.00
KN-ECDGRY	Gray	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	25	$15.00	***KN-ECT12SP4***	Gray	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-T12SP4	25	$13.00
KN-ECDBLU	Blue			10	$7.00	***KN-ECF10***	Gray	27.3x59.6x1.2 [1.07x2.35x0.05]	KN-F10	25	$16.00
KN-ECDBLK	Black				$7.00	***KN-ECKBD***	Gray	37.1x53.5x1.2 [1.46x2.11x0.05]	KN-KDB10	10	$6.50
KN-ECDGRN	Green				$7.00						

KONNECT-IT® Accessories

Separators

Separators are used to segment banks of terminal blocks. Allows you to maintain a single row of terminal blocks, but have separate power source clusters.

Separators Ordering Information

Part Number	Color	Works With	Dimensions - mm [in]			Qty	Price
			Height	Length	Thickness		
KN-ST1GRY	Gray	KN-T12 KN-T10 KN-T8 KN-T6	39.0 [1.54]	42.5 [1.67]	1.2 [0.05]	25	$12.50
KN-ST1BLU	Blue					10	$4.75
KN-ST1BLK	Black						$4.75
KN-ST1BRN	Brown						$4.75
KN-ST1GRN	Green						$4.75
KN-ST1ORG	Orange						$4.75
KN-ST1RED	Red						$4.75
KN-ST1WHT	White						$4.75
KN-ST1YEL	Yellow						$4.75
KN-ST2GRY	Gray	KN-T4	52.5 [2.07]	50.5 [1.99]	1.5 [0.06]	25	$16.00
KN-ST2BLU	Blue					10	$16.00
KN-ST3GRY	Gray	KN-T2	62.6 [2.46]	53.1 [2.09]	1.5 [0.06]		$8.00
KN-ST3BLU	Blue						$8.00

KN-ST1GRY

Top Covers and Label Holders

Top Covers and Label Holders Ordering Information

Part Number	Description	Works With	Dimensions - mm [in]			Qty	Price
			Height	Length	Width		
KN-TC-1	Top cover for Konnect-It terminal block, blank, white	KN-T12 KN-T10 KN-T8 KN-T6	6.8 [0.27]	29.0 [1.14]	5.8 [0.23]	25	$9.75
KN-TC-1S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	$14.00
KN-TC-2	Top cover for Konnect-It terminal block, blank, white	KN-T4 KN-T2	7.3 [0.29]	35.8 [1.41]	9.0 [0.35]	25	$25.00
KN-TC-2S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	$25.00
KN-MA-1	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top. Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).	KN-EB4	46.2 [1.82]	46.0 [1.81]	11.4 [0.45]	25	$23.50
KN-MA-1-10						10	$10.50
KN-MA-2	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top. Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).	KN-EB7	37.5 [1.48]	46.2 [1.82]	9.5 [0.37]	50	$59.00
KN-MA-2-10						10	$14.00
KN-MA-3	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T4 KN-T2	9.3 [0.36]	36.0 [1.42]	9.0 [0.35]	25	$15.50
KN-MA-4	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T12 KN-T10 KN-T8 KN-T6	9.0 [0.35]	29.0 [1.14]	5.7 [0.22]	25	$14.00
KN-MA-5	Label holder for terminal block group. Label media included. Max label dimensions: 10 x 38mm (0.39 x 1.50 in). Thickness 0.30 mm (0.01 in)	Attaches to any 35mm DIN rail	46.4 [1.83]	44.5 [1.75]	10.0 [0.39]	50	$48.00
KN-MA-5-25						25	$29.50

KN-MA-1

KN-MA-2

KN-MA-5

KN-TC-1 / KN-TC-2

KN-TC-1S / KN-TC-2S

KN-MA-3

KN-MA-4



KONNECT-IT® Accessories

Marking Tags 5 x 5mm

Use with any KONNECT-IT series terminal blocks.







5 x 5mm Marking Tags Ordering Information

250 Pieces per Package						500 Pieces per Package					
Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price
KN-L5-BLANK-250	Blank	$13.00	KN-L5-A-250	A	$13.00	KN-L5-BLANK	Blank	$20.00	KN-L5-A	A	$24.00
KN-L5-0-250	0	$13.00	KN-L5-B-250	B	$13.00	KN-L5-0	0	$24.00	KN-L5-B	B	$24.00
KN-L5-1-250	1	$13.00	KN-L5-C-250	C	$13.00	KN-L5-1	1	$24.00	KN-L5-C	C	$24.00
KN-L5-2-250	2	$13.00	KN-L5-D-250	D	$13.00	KN-L5-2	2	$24.00	KN-L5-D	D	$24.00
KN-L5-3-250	3	$13.00	KN-L5-E-250	E	$13.00	KN-L5-3	3	$24.00	KN-L5-E	E	$24.00
KN-L5-4-250	4	$13.00	KN-L5-F-250	F	$13.00	KN-L5-4	4	$24.00	KN-L5-F	F	$24.00
KN-L5-5-250	5	$13.00	KN-L5-G-250	G	$13.00	KN-L5-5	5	$24.00	KN-L5-G	G	$24.00
KN-L5-6-250	6	$13.00	KN-L5-H-250	H	$13.00	KN-L5-6	6	$24.00	KN-L5-H	H	$24.00
KN-L5-7-250	7	$13.00	KN-L5-I-250	I	$13.00	KN-L5-7	7	$24.00	KN-L5-I	I	$24.00
KN-L5-8-250	8	$13.00	KN-L5-J-250	J	$13.00	KN-L5-8	8	$24.00	KN-L5-J	J	$25.00
KN-L5-9-250	9	$13.00	KN-L5-K-250	K	$13.00	KN-L5-9	9	$24.00	KN-L5-K	K	$25.00
KN-L5-10-250	10	$13.00	KN-L5-L-250	L	$12.50	KN-L5-10	10	$24.00	KN-L5-L	L	$24.00
KN-L5-1-10-250	1-10	$13.00	KN-L5-M-250	M	$13.00	KN-L5-1-10	1-10	$24.00	KN-L5-M	M	$25.00
KN-L5-11-20-250	11-20	$13.00	KN-L5-N-250	N	$12.50	KN-L5-11-20	11-20	$24.00	KN-L5-N	N	$24.00
KN-L5-21-30-250	21-30	$13.00	KN-L5-O-250	O	$12.50	KN-L5-21-30	21-30	$24.00	KN-L5-O	O	$24.00
KN-L5-31-40-250	31-40	$13.00	KN-L5-P-250	P	$13.00	KN-L5-31-40	31-40	$24.00	KN-L5-P	P	$25.00
KN-L5-41-50-250	41-50	$13.00	KN-L5-Q-250	Q	$13.00	KN-L5-41-50	41-50	$24.00	KN-L5-Q	Q	$25.00
KN-L5-1-50-250	1-50	$13.00	KN-L5-R-250	R	$12.50	KN-L5-1-50	1-50	$24.00	KN-L5-R	R	$24.00
KN-L5-51-100-250	51-100	$13.00	KN-L5-S-250	S	$12.50	KN-L5-51-100	51-100	$24.00	KN-L5-S	S	$24.00
KN-L5-101-150-250	101-150	$13.00	KN-L5-T-250	T	$12.50	KN-L5-101-150	101-150	$24.00	KN-L5-T	T	$24.00
KN-L5-151-200-250	151-200	$13.00	KN-L5-U-250	U	$13.00	KN-L5-151-200	151-200	$24.00	KN-L5-U	U	$25.00
KN-L5-201-250-250	201-250	$13.00	KN-L5-V-250	V	$12.50	KN-L5-201-250	201-250	$24.00	KN-L5-V	V	$24.00
KN-L5-251-300-250	251-300	$13.00	KN-L5-W-250	W	$13.00	KN-L5-251-300	251-300	$24.00	KN-L5-W	W	$25.00
KN-L5-301-350-250	301-350	$13.00	KN-L5-X-250	X	$12.50	KN-L5-301-350	301-350	$24.00	KN-L5-X	X	$24.00
KN-L5-351-400-250	351-400	$13.00	KN-L5-Y-250	Y	$12.50	KN-L5-351-400	351-400	$24.00	KN-L5-Y	Y	$24.00
KN-L5-401-450-250	401-450	$13.00	KN-L5-Z-250	Z	$13.00	KN-L5-401-450	401-450	$24.00	KN-L5-Z	Z	$25.00
KN-L5-451-500-250	451-500	$13.00	KN-L5-POS-250	+	$12.50	KN-L5-451-500	451-500	$24.00	KN-L5-POS	+	$24.00
KN-L5-L1-250	L1	$12.50	KN-L5-NEG-250	-	$12.50	KN-L5-L1	L1	$24.00	KN-L5-NEG	-	$24.00
KN-L5-L2-250	L2	$12.50	KN-L5-GND-250	GND	$13.00	KN-L5-L2	L2	$24.00	KN-L5-GND	GND	$24.00
KN-L5-L3-250	L3	$12.50				KN-L5-L3	L3	$24.00			

KONNECT-IT® Accessories

Marking Tags
6 x 11.5 mm

Use with Konnect-It series terminal blocks 6.5mm or wider.

Marking Tags 6 x 11.5mm			
Part Number	***Description***	***Qty***	***Price***
KN-L6P5-BLNK	Blank	500	Retired
KN-L6P5-BLNK-250	Blank	250	Retired
KN-L6P5-BLNK-300	Blank	300	$15.00
KN-L6P5-1-10	Numbered 1-10	500	$57.00
KN-L6P5-1-10-250	Numbered 1-10	250	$31.50
KN-L6P5-1-10-300	Numbered 1-10	300	$34.00
KN-L6P5-11-20	Numbered 11-20	500	$57.00
KN-L6P5-11-20-250	Numbered 11-20	250	$31.50
KN-L6P5-11-20-300	Numbered 11-20	300	$34.00
KN-L6P5-21-30	Numbered 21-30	500	$57.00
KN-L6P5-21-30-250	Numbered 21-30	250	$31.50
KN-L6P5-21-30-300	Numbered 21-30	300	$34.00
KN-L6P5-31-40	Numbered 31-40	500	$57.00
KN-L6P5-31-40-250	Numbered 31-40	250	$31.50
KN-L6P5-31-40-300	Numbered 31-40	300	$34.00
KN-L6P5-41-50	Numbered 41-50	500	$57.00
KN-L6P5-41-50-250	Numbered 41-50	250	$31.50
KN-L6P5-41-50-300	Numbered 41-50	300	$34.00
KN-L6P5-51-60	Numbered 51-60	500	$57.00
KN-L6P5-51-60-250	Numbered 51-60	250	$31.50
KN-L6P5-51-60-300	Numbered 51-60	300	$34.00
KN-L6P5-61-70	Numbered 61-70	500	$57.00
KN-L6P5-61-70-250	Numbered 61-70	250	$31.50
KN-L6P5-61-70-300	Numbered 61-70	300	$34.00
KN-L6P5-71-80	Numbered 71-80	500	$57.00
KN-L6P5-71-80-250	Numbered 71-80	250	$31.50
KN-L6P5-71-80-300	Numbered 71-80	300	$34.00
KN-L6P5-81-90	Numbered 81-90	500	$58.00
KN-L6P5-81-90-250	Numbered 81-90	250	$32.00
KN-L6P5-91-100	Numbered 91-100	500	$58.00
KN-L6P5-91-100-250	Numbered 91-100	250	$32.00

Marking Tags
5 x 10mm, 6 x 10mm, 10 x 10mm

Use with Konnect-It series terminal blocks 5 x 10mm, 6 x 10mm, and 10 x 10mm.



Marking Tags			
Part Number*	***Description***	***Qty***	***Price***
KN-L5X-BLNK	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	440	$21.50
KN-L5X-BLNK-220	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	220	$11.50
KN-L6X-BLNK	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	360	$18.50
KN-L6X-BLNK-180	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	180	$9.75
KN-L10X-BLNK	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	200	$29.00
KN-L10X-BLNK-100	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	100	$16.00

***Does not fit any KN-T1/0xx or KN-G1/0 series block**