

NEMA 12 and 13 Small Continuous Hinge Wall-Mount



Applications

Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Provides protection from dust, dirt, oil, and water.



Construction

- Bodies fabricated from 14-gauge steel
- Doors fabricated from 16-gauge steel
- Continuously-welded seams ground smooth, less knockouts or holes
- Lids are sealed with closed-cell oil-resistant neoprene gasket
- External mounting plates on top and bottom of enclosure
- Weldnuts provided for mounting optional subpanels securely on models 6 x 4 in [152 x 102 mm] and larger
- External screw clamps are quick and easy to operate
- Standard continuous hinge
- Grounding provisions provided
- Uses WAN12RA clamp

Finish


- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 50, 12 and 13 [UL Files E6924]
- NEMA/EEMAC 12 and 13
- JIC EL-1-71



Dimensions



NOTES:

1. PANELS ARE 14GA STEEL.
2. PANEL SCREWS ARE #10-32 PAN HEAD.
3. TWO CLAMPS ARE USED IF W=8" OR MORE.

NEMA 12 and 13 Small Continuous Hinge Wall-Mount



NEMA 12 and 13 Small Continuous Hinge Wall-Mount				
Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Stainless Steel Subpanel
B040403CH	\$63.00	4.31 x 4.31 x 3.14 [109 x 109 x 80]	—	—
B040404CH	\$65.00	4.31 x 4.31 x 4.14 [109 x 109 x 105]	—	—
B060403CH	\$72.00	6.31 x 4.31 x 3.14 [160 x 109 x 80]	P0604	P0604SS
B060404CH	\$76.00	6.31 x 4.31 x 4.14 [160 x 109 x 105]	P0604	P0604SS
B060604CH	\$81.00	6.31 x 6.31 x 4.14 [160 x 160 x 105]	P0606	P0606SS
B080603CH	\$86.00	8.31 x 6.31 x 3.64 [211 x 160 x 92]	P0806	P0806SS
B080606CH	\$102.00	8.31 x 6.31 x 6.14 [211 x 160 x 156]	P0806	P0806SS
B080804CH	\$98.00	8.31 x 8.31 x 4.14 [211 x 211 x 105]	P0808	—
B100804CH	\$107.00	10.31 x 8.31 x 4.14 [262 x 211 x 105]	P1008	P1008SS
B100804CHS	\$106.00	8.31 x 10.31 x 4.14 [211 x 262 x 105]	P1008	P1008SS
B100806CH	\$121.00	10.31 x 8.31 x 6.14 [262 x 211 x 156]	P1008	P1008SS
B101006CH	\$133.00	10.31 x 10.31 x 6.14 [262 x 262 x 156]	P1010	—
B120604CH	\$107.00	12.31 x 6.31 x 4.14 [313 x 160 x 105]	P1206	—
B121005CH	\$137.00	12.31 x 10.31 x 5.14 [313 x 262 x 131]	P1210	P1210SS
B121005CHS	\$135.00	10.31 x 12.31 x 5.14 [262 x 313 x 131]	P1210	P1210SS
B121008CH	\$167.00	12.31 x 10.31 x 8.14 [313 x 262 x 207]	P1210	P1210SS
B121206CH	\$159.00	12.31 x 12.31 x 6.14 [313 x 313 x 156]	P1212	P1212SS
B140806CH	\$146.00	14.31 x 8.31 x 6.14 [363 x 211 x 156]	P1408	—
B141206CH	\$176.00	14.31 x 12.31 x 6.14 [363 x 313 x 156]	P1412	P1412SS
B141206CHS	\$171.00	12.31 x 14.31 x 6.14 [313 x 363 x 156]	P1412	P1412SS
B141208CH	\$198.00	14.31 x 12.31 x 8.14 [363 x 313 x 207]	P1412	P1412SS
B161006CH	\$175.00	16.31 x 10.31 x 6.14 [414 x 262 x 156]	P1610	—
B161406CH	\$204.00	16.31 x 14.31 x 6.14 [414 x 363 x 156]	P1614	P1614SS
B161406CHS	\$202.00	14.31 x 16.31 x 6.14 [363 x 414 x 156]	P1614	P1614SS
B161408CH	\$226.00	16.31 x 14.31 x 8.14 [414 x 363 x 207]	P1614	P1614SS
B161410CH	\$256.00	16.31 x 14.31 x 10.14 [414 x 363 x 258]	P1614	P1614SS
Notes: Subpanels must be ordered separately. Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings.				

Enclosure Subpanels



Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B_CH, BN4, BN4_CH, BN4_CHQT, BN4_SS, BN4_CHSS, BN4_CHSSA, BN4_CHQTSS, BN4_CHQTSSA ("_" refers to dimensions).



Subpanels for B and BN4 Enclosures					
Painted Steel	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<u>P0604</u>	\$5.00	<u>P0604SS</u>	\$16.75	6 x 4	4.88 x 2.88 [124 x 73]
<u>P0606</u>	\$6.00	<u>P0606SS</u>	\$20.50	6 x 6	4.88 x 4.88 [124 x 124]
<u>P0806</u>	\$6.75	<u>P0806SS</u>	\$24.50	8 x 6	6.88 x 4.88 [175 x 124]
<u>P0808</u>	\$8.00	—	—	8 x 8	6.88 x 6.88 [175 x 175]
<u>P1008</u>	\$8.75	<u>P1008SS</u>	\$35.50	10 x 8	8.88 x 6.88 [226 x 175]
<u>P1010</u>	\$11.00	—	—	10 x 10	8.88 x 8.88 [226 x 226]
<u>P1206</u>	\$8.75	—	—	12 x 6	10.88 x 4.88 [276 x 124]
<u>P1210</u>	\$12.75	<u>P1210SS</u>	\$50.00	12 x 10	10.88 x 8.88 [276 x 226]
<u>P1212</u>	\$15.00	<u>P1212SS</u>	\$58.00	12 x 12	10.88 x 10.88 [276 x 276]
<u>P1408</u>	\$12.00	—	—	14 x 8	12.88 x 6.88 [327 x 175]
<u>P1412</u>	\$16.50	<u>P1412SS</u>	\$67.00	14 x 12	12.88 x 10.88 [327 x 276]
<u>P1610</u>	\$16.25	—	—	16 x 10	14.88 x 8.88 [378 x 226]
<u>P1614</u>	\$22.00	<u>P1614SS</u>	\$88.00	16 x 14	14.88 x 12.88 [378 x 327]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing.					

Dimensions

