

# NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



## Applications

Designed to house electrical and electronic controls, terminals, and instruments in areas that are regularly hosed down or are otherwise very wet. Enclosures are also suitable for outdoor applications.



## Construction

- Bodies and doors fabricated from 12-gauge 304 stainless steel
- Continuously-welded seams ground smooth
- "Uni-strut" mounting channels are welded horizontally to interior body sides (top, bottom and center)
- Optional swing, half, full, and rack panels can be mounted anywhere along "uni-strut" channel
- Rolled lip around three sides of door and along top of enclosure's opening excludes liquids and contaminants from entering
- 3-point 316L SS padlocking handle
- Heavy gauge continuous hinge
- Pull hinge pin to remove doors
- Removable print pocket is provided
- Heavy-duty removable lifting eyes
- Doors are sealed with poured-in-place polyurethane gasket
- Grounding provisions provided
- Uses WAL3\_SS series handles

## Finish

- Smooth-grained stainless steel finish

## Listings

- UL 5083, 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 3, 4, 4X, and 12



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

## NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door Enclosures with 3-Point Handle

| Part Number                              | Price      | Enclosure SizeHxWxD                      |
|------------------------------------------|------------|------------------------------------------|
| <a href="#"><u>WA602418SSFSN43PT</u></a> | \$3,446.00 | 60.12 x 24.12 x 19.23 [1527 x 613 x 488] |
| <a href="#"><u>WA603624SSFSN43PT</u></a> | \$4,877.00 | 60.13 x 36.12 x 25.23 [1527 x 917 x 641] |
| <a href="#"><u>WA722424SSFSN43PT</u></a> | \$4,649.00 | 72.13 x 24.13 x 25.23 [1832 x 613 x 641] |
| <a href="#"><u>WA723018SSFSN43PT</u></a> | \$4,680.00 | 72.13 x 30.13 x 19.23 [1832 x 765 x 488] |
| <a href="#"><u>WA723618SSFSN43PT</u></a> | \$4,931.00 | 72.12 x 36.12 x 19.23 [1832 x 917 x 488] |
| <a href="#"><u>WA723624SSFSN43PT</u></a> | \$5,296.00 | 72.13 x 36.12 x 25.23 [1832 x 917 x 641] |
| <a href="#"><u>WA723636SSFSN43PT</u></a> | \$6,796.00 | 72.12 x 36.12 x 37.23 [1832 x 917 x 946] |
| <a href="#"><u>WA903620SSFSN43PT</u></a> | \$6,136.00 | 90.13 x 36.12 x 21.23 [2289 x 917 x 539] |
| <a href="#"><u>WA903624SSFSN43PT</u></a> | \$6,486.00 | 90.13 x 36.12 x 25.23 [2289 x 917 x 641] |

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters];  
Letters in table correspond to letters on dimensional drawings.

# NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



| Standard Subpanels                       |                                  |                                   |                                  |                                   |
|------------------------------------------|----------------------------------|-----------------------------------|----------------------------------|-----------------------------------|
| Enclosures                               | Full Height                      |                                   | Half Height                      |                                   |
|                                          | Painted Steel                    | Galvanized                        | Painted Steel                    | Galvanized                        |
| <a href="#"><u>WA602418SSFSN43PT</u></a> | <a href="#"><u>WA60P24F1</u></a> | –                                 | <a href="#"><u>WA60P24F2</u></a> | –                                 |
| <a href="#"><u>WA603624SSFSN43PT</u></a> | <a href="#"><u>WA60P36F1</u></a> | <a href="#"><u>WA60P36F1G</u></a> | <a href="#"><u>WA60P36F2</u></a> | <a href="#"><u>WA60P36F2G</u></a> |
| <a href="#"><u>WA722424SSFSN43PT</u></a> | <a href="#"><u>WA72P24F1</u></a> | <a href="#"><u>WA72P24F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA723018SSFSN43PT</u></a> | <a href="#"><u>WA72P30F1</u></a> | <a href="#"><u>WA72P30F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA723618SSFSN43PT</u></a> | <a href="#"><u>WA72P36F1</u></a> | <a href="#"><u>WA72P36F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA723624SSFSN43PT</u></a> | <a href="#"><u>WA72P36F1</u></a> | <a href="#"><u>WA72P36F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA723636SSFSN43PT</u></a> | <a href="#"><u>WA72P36F1</u></a> | <a href="#"><u>WA72P36F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA903620SSFSN43PT</u></a> | <a href="#"><u>WA90P36F1</u></a> | <a href="#"><u>WA90P36F1G</u></a> | –                                | –                                 |
| <a href="#"><u>WA903624SSFSN43PT</u></a> | <a href="#"><u>WA90P36F1</u></a> | <a href="#"><u>WA90P36F1G</u></a> | –                                | –                                 |

# NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle




## Side-Mount Panels for NEMA 3, 4, 4X, and 12 SS Freestanding Single-Door Enclosures with 3-Point Handle

| <i>Enclosures</i>                        | <i>Painted Steel</i>             |                                  |
|------------------------------------------|----------------------------------|----------------------------------|
| <u><a href="#">WA722424SSFSN43PT</a></u> | <u><a href="#">WA72SMP14</a></u> | <u><a href="#">WA72SMP20</a></u> |
| <u><a href="#">WA723018SSFSN43PT</a></u> | <u><a href="#">WA72SMP14</a></u> |                                  |
| <u><a href="#">WA723618SSFSN43PT</a></u> | <u><a href="#">WA72SMP14</a></u> |                                  |
| <u><a href="#">WA723624SSFSN43PT</a></u> | <u><a href="#">WA72SMP14</a></u> | <u><a href="#">WA72SMP20</a></u> |
| <u><a href="#">WA723636SSFSN43PT</a></u> | <u><a href="#">WA72SMP14</a></u> | <u><a href="#">WA72SMP20</a></u> |


# NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



## Dimensions



# WA-F1/F2 Panels for Single-Door Freestanding Enclosures



## Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories

| <i>Painted Steel</i>    | <i>Price</i> | <i>Galvanized</i>        | <i>Price</i> | <i>Steel Gauge</i> | <i>Panel Size HxW</i>      | <i>Subpanel Type</i> |
|-------------------------|--------------|--------------------------|--------------|--------------------|----------------------------|----------------------|
| <b><u>WA60P24F1</u></b> | \$342.00     | —                        | —            | 12                 | 48.00 x 20.00 [1219 x 508] | Full                 |
| <b><u>WA60P24F2</u></b> | \$246.00     | —                        | —            | 10                 | 24.88 x 20.00 [632 x 508]  | Half                 |
| <b><u>WA60P36F1</u></b> | \$441.00     | <b><u>WA60P36F1G</u></b> | \$441.00     | 12                 | 48.00 x 32.00 [1219 x 813] | Full                 |
| <b><u>WA60P36F2</u></b> | \$278.00     | <b><u>WA60P36F2G</u></b> | \$278.00     | 12                 | 24.88 x 32.00 [632 x 813]  | Half                 |
| <b><u>WA72P24F1</u></b> | \$383.00     | <b><u>WA72P24F1G</u></b> | \$383.00     | 12                 | 60.00 x 20.00 [1524 x 508] | Full                 |
| <b><u>WA72P30F1</u></b> | \$445.00     | <b><u>WA72P30F1G</u></b> | \$482.00     | 12                 | 60.00 x 26.00 [1524 x 660] | Full                 |
| <b><u>WA72P36F1</u></b> | \$507.00     | <b><u>WA72P36F1G</u></b> | \$507.00     | 12                 | 60.00 x 32.00 [1524 x 813] | Full                 |
| <b><u>WA90P24F1</u></b> | \$445.00     | <b><u>WA90P24F1G</u></b> | \$445.00     | 12                 | 78.00 x 20.00 [1981 x 508] | Full                 |
| <b><u>WA90P36F1</u></b> | \$607.00     | <b><u>WA90P36F1G</u></b> | \$607.00     | 12                 | 78.00 x 32.00 [1981 x 813] | Full                 |


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.


If used in a two-door enclosure, a center panel support must be ordered.

Suffix F1= full panel, F2 = half panel

## Dimensions



# WA-SMP Series Side-Mount Panels for Freestanding Enclosures



## Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

| Painted Steel    | Price    | Panel Size AxB             |
|------------------|----------|----------------------------|
| <b>WA72SMP14</b> | \$236.00 | 60.00 x 14.00 [1524 x 356] |
| <b>WA72SMP20</b> | \$288.00 | 60.00 x 20.00 [1524 x 508] |

Note: Dimensions in inches [millimeters].

## Dimensions

