

NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



Applications

Designed to house electrical and electronic controls, terminals, and instruments in areas that are regularly hosed down or are otherwise very wet. Enclosures are also suitable for outdoor applications.



Construction

- Bodies and doors fabricated from 12-gauge 304 stainless steel
- Continuously-welded seams ground smooth
- "Uni-strut" mounting channels are welded horizontally to interior body sides (top, bottom and center)
- Optional swing, half, full, and rack panels can be mounted anywhere along "uni-strut" channel
- Rolled lip around three sides of door and along top of enclosure's opening excludes liquids and contaminants from entering
- 3-point 316L SS padlocking handle
- Heavy gauge continuous hinge
- Pull hinge pin to remove doors
- Removable print pocket is provided
- Heavy-duty removable lifting eyes
- Doors are sealed with poured-in-place polyurethane gasket
- Grounding provisions provided
- Uses WAL3_SS series handles

Finish

- Smooth-grained stainless steel finish

Listings

- UL 5083, 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 3, 4, 4X, and 12



Note: For current listings, please see www.automationdirect.com

NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door Enclosures with 3-Point Handle

Part Number	Price	Enclosure SizeHxWxD
<u>WA602418SSFSN43PT</u>	\$3,661.00	60.12 x 24.12 x 19.23 [1527 x 613 x 488]
<u>WA603624SSFSN43PT</u>	\$5,254.00	60.13 x 36.12 x 25.23 [1527 x 917 x 641]
<u>WA722424SSFSN43PT</u>	\$5,119.00	72.13 x 24.13 x 25.23 [1832 x 613 x 641]
<u>WA723018SSFSN43PT</u>	\$5,087.00	72.13 x 30.13 x 19.23 [1832 x 765 x 488]
<u>WA723618SSFSN43PT</u>	\$5,317.00	72.12 x 36.12 x 19.23 [1832 x 917 x 488]
<u>WA723624SSFSN43PT</u>	\$5,423.00	72.13 x 36.12 x 25.23 [1832 x 917 x 641]
<u>WA723636SSFSN43PT</u>	\$7,319.00	72.12 x 36.12 x 37.23 [1832 x 917 x 946]
<u>WA903620SSFSN43PT</u>	\$6,673.00	90.13 x 36.12 x 21.23 [2289 x 917 x 539]
<u>WA903624SSFSN43PT</u>	\$7,131.00	90.13 x 36.12 x 25.23 [2289 x 917 x 641]

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters];
Letters in table correspond to letters on dimensional drawings.

NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



Standard Subpanels				
Enclosures	Full Height		Half Height	
	Painted Steel	Galvanized	Painted Steel	Galvanized
<u>WA602418SSFSN43PT</u>	<u>WA60P24F1</u>	–	<u>WA60P24F2</u>	–
<u>WA603624SSFSN43PT</u>	<u>WA60P36F1</u>	<u>WA60P36F1G</u>	<u>WA60P36F2</u>	<u>WA60P36F2G</u>
<u>WA722424SSFSN43PT</u>	<u>WA72P24F1</u>	<u>WA72P24F1G</u>	–	–
<u>WA723018SSFSN43PT</u>	<u>WA72P30F1</u>	<u>WA72P30F1G</u>	–	–
<u>WA723618SSFSN43PT</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	–	–
<u>WA723624SSFSN43PT</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	–	–
<u>WA723636SSFSN43PT</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	–	–
<u>WA903620SSFSN43PT</u>	<u>WA90P36F1</u>	<u>WA90P36F1G</u>	–	–
<u>WA903624SSFSN43PT</u>	<u>WA90P36F1</u>	<u>WA90P36F1G</u>	–	–

NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle




Side-Mount Panels for NEMA 3, 4, 4X, and 12 SS Freestanding Single-Door Enclosures with 3-Point Handle		
Enclosures	Painted Steel	
<u>WA722424SSFSN43PT</u>	<u>WA72SMP14</u>	<u>WA72SMP20</u>
<u>WA723018SSFSN43PT</u>	<u>WA72SMP14</u>	
<u>WA723618SSFSN43PT</u>	<u>WA72SMP14</u>	
<u>WA723624SSFSN43PT</u>	<u>WA72SMP14</u>	<u>WA72SMP20</u>
<u>WA723636SSFSN43PT</u>	<u>WA72SMP14</u>	<u>WA72SMP20</u>


NEMA 3, 4, 4X, and 12 Stainless Steel Freestanding Single-Door with 3-Point Handle



Dimensions



WA-F1/F2 Panels for Single-Door Freestanding Enclosures



Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories

Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size HxW	Subpanel Type
<u>WA60P24F1</u>	\$359.00	—	—	12	48.00 x 20.00 [1219 x 508]	Full
<u>WA60P24F2</u>	\$259.00	—	—	10	24.88 x 20.00 [632 x 508]	Half
<u>WA60P36F1</u>	\$463.00	<u>WA60P36F1G</u>	\$463.00	12	48.00 x 32.00 [1219 x 813]	Full
<u>WA60P36F2</u>	\$292.00	<u>WA60P36F2G</u>	\$292.00	12	24.88 x 32.00 [632 x 813]	Half
<u>WA72P24F1</u>	\$402.00	<u>WA72P24F1G</u>	\$402.00	12	60.00 x 20.00 [1524 x 508]	Full
<u>WA72P30F1</u>	\$468.00	<u>WA72P30F1G</u>	\$506.00	12	60.00 x 26.00 [1524 x 660]	Full
<u>WA72P36F1</u>	\$533.00	<u>WA72P36F1G</u>	\$533.00	12	60.00 x 32.00 [1524 x 813]	Full
<u>WA90P24F1</u>	\$468.00	<u>WA90P24F1G</u>	\$468.00	12	78.00 x 20.00 [1981 x 508]	Full
<u>WA90P36F1</u>	\$637.00	<u>WA90P36F1G</u>	\$637.00	12	78.00 x 32.00 [1981 x 813]	Full


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.


If used in a two-door enclosure, a center panel support must be ordered.

Suffix F1= full panel, F2 = half panel

Dimensions



WA-SMP Series Side-Mount Panels for Freestanding Enclosures



Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

Painted Steel	Price	Panel Size AxB
WA72SMP14	\$248.00	60.00 x 14.00 [1524 x 356]
WA72SMP20	\$303.00	60.00 x 20.00 [1524 x 508]

Note: Dimensions in inches [millimeters].

Dimensions

