


PATLITE® 30mm LED Signal Towers

Features

- Prism-cut lens design for enhanced visibility from any direction
- Double-insulated construction for enhanced durability and safety in the work environment.
- Direct mount installation with just a single hole.
- Interchangeable modules do not need re-wiring, even after installation
- Main body is constructed of superior impact and heat resistant ABS resin (not recommended for outdoor use).
- Lens is made of superior weather resistant and light translucent AS resin.
- Optional MP-B buzzer available. Please see accessories section for ordering information.
- UL recognized File No. E215660
- IP65 ingress protection rating



30mm LED Signal Towers Selection																	
Part Number	Price	Drawing Link	Modules			Polarity	Light Function	Wiring	Body Style	Mounting							
			#	LED													
MPS-102-R	\$94.00	PDF	1	Red	-	NPN/PNP	Continuous light	1000mm pigtail	Short body	Direct mount installation							
MPS-202-RG	\$123.00	PDF	2	Red, Green													
MPS-302-RYG	\$154.00	PDF	3	Red, Amber, Green													
MPS-402-RYGB	\$183.00	PDF	4	Red, Amber, Green, Blue													
MPS-102-RZ	\$94.00	PDF	1	Red	Clear lens												
MPS-202-RGZ	\$128.00	PDF	2	Red, Green													
MPS-302-RYGZ	\$158.00	PDF	3	Red, Amber, Green													
MPS-402-RYGBZ	\$187.00	PDF	4	Red, Amber, Green, Blue													
MPS-102C-R	\$94.00	PDF	1	Red	-			NPN/PNP	Continuous light		M12 Connector	Standard body	Direct mount installation				
MPS-202C-RG	\$116.00	PDF	2	Red, Green													
MPS-302C-RYG	\$153.00	PDF	3	Red, Amber, Green													
MP-102-R	\$94.00	PDF	1	Red							1180mm pigtail						
MP-202-RG	\$130.00	PDF	2	Red, Green	Clear lens												
MP-302-RYG	\$153.00	PDF	3	Red, Amber, Green													
MP-402-RYGB	\$185.00	PDF	4	Red, Amber, Green, Blue													
MP-102-RZ	\$101.00	PDF	1	Red													
MP-202-RGZ	\$130.00	PDF	2	Red, Green													
MP-302-RYGZ	\$164.00	PDF	3	Red, Amber, Green													
MP-402-RYGBZ	\$189.00	PDF	4	Red, Amber, Green, Blue													
MP-102C-R	\$94.00	PDF	1	Red	-						NPN/PNP			Continuous light	M12 Connector	Standard body	Direct mount installation
MP-202C-RG	\$130.00	PDF	2	Red, Green													
MP-302C-RYG	\$159.00	PDF	3	Red, Amber, Green													

Note: Please see the accessories section of this section for optional and/or replacement components.
Colors in order from left to right.

PATLITE® 30mm LED Signal Towers


Specifications

30mm LED Signal Towers Technical Specifications							
# of Tiers	Part Number		Rated Voltage	Operating Voltage	Power Consumption	Weight g [oz]	
1	MPS-102-R		24V AC/DC	±10%	0.7 W	110 [3.88]	
	MPS-102-RZ						
	MPS-102C-R		24VDC			210 [7.41]	
	MP-102-R		24V AC/DC				
	MP-102-RZ						
	MP-102C-R		24VDC				
2	MPS-202-RG		24V AC/DC		±10%	1.4 W	130 [4.59]
	MPS-202-RGZ						
	MPS-202C-RG		24VDC				230 [8.11]
	MP-202-RG		24V AC/DC				
	MP-202-RGZ						
	MP-202C-RG		24VDC				
3	MPS-302-RYG		24V AC/DC		±10%	2.0 W	150 [5.29]
	MPS-302-RYGZ						
	MPS-302C-RYG		24VDC				250 [8.82]
	MP-302-RYG		24V AC/DC				
	MP-302-RYGZ						
	MP-302C-RYG		24VDC				
4	MPS-402-RYGB		24V AC/DC		±10%	2.6 W	170 [6.0]
	MPS-402-RYGBZ						
	MP-402-RYGB						270 [9.52]
	MP-402-RYGBZ						
Signal wire current (Rated Current Consumption)		LED Unit	Red	Amber		Green	Blue
		Typical	29.0 mA	29.5 mA		17.1 mA	17.1 mA
		Max	32.7 mA	34.5 mA	21.4 mA	21.4 mA	
Luminosity			550mcd	650mcd	1900mcd	700mcd	
Wire Size			22AWG				
Operating ambient temperature			-30 to +60°C [-22 to +140°F]				
Operating ambient humidity			Less than 90% (no condensation)				
Vibration resistance			19.6 m/s² @ 30Hz				
Insulation resistance			More than 1MΩ at 500VDC between the terminals and the chassis				
Withstand voltage			500VAC applied for 1 min between terminals and chassis without breaking insulation				
Ingress protection rating			IP65 (IEC 60529)				
Conformity standards *			UL 508, CSA-C22.2 No.14, RoHs Directive (EN 50581)				

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Easily add or replace LED modules

When adding or removing modules, the center screw that matches the number of tiers has to be purchased.



Interchangeable LED Modules

Color sequence is changeable by adding or removing up to 5 color modules even after installation.

NOTE: LED modules of the same color within a signal tower will light up simultaneously.

Wiring does not change

The LED module colors correspond to the wiring, so re-wiring is not necessary.



PATLITE® 30mm LED Signal Towers

Accessories

Accessories for Patlite® 30mm Signal Towers			
Part Number	Price	Drawing Link	Description
<u>MP-B</u>	\$70.00	PDF	80dB @ 1 meter / 3,000Hz add-on alarm; activated by red module
<u>B72100182-1F1</u>	\$41.50	PDF	Red LED module
<u>B72100182-2F1</u>	\$41.50	PDF	Amber LED module
<u>B72100182-3F1</u>	\$41.50	PDF	Green LED module
<u>B72100182-4F1</u>	\$41.50	PDF	Blue LED module
<u>B72100182-7F1</u>	\$41.50	PDF	Clear/white LED module
<u>B72100192-1F1</u>	\$41.50	PDF	Red LED module with clear lens
<u>B72100192-2F1</u>	\$41.50	PDF	Amber LED module with clear lens
<u>B72100192-3F1</u>	\$41.50	PDF	Green LED module with clear lens
<u>B72100192-4F1</u>	\$41.50	PDF	Blue LED module with clear lens
<u>S33552120-0355F1</u>	\$6.00	N/A	1-tier center screw, zinc plated steel
<u>S33552120-0390F1</u>	\$6.00	N/A	2-tier center screw, zinc plated steel
<u>S33552120-03125F1</u>	\$7.25	N/A	3-tier center screw, zinc plated steel
<u>S33552120-03160F1</u>	\$7.25	N/A	4-tier center screw, zinc plated steel
<u>B25110032-F1</u>	\$7.25	N/A	LED module o-ring, silicone
<u>SZ-904</u>	\$18.00	PDF	22mm to 3/4"FNPT adapter, aluminum
<u>SZ-150</u>	\$23.00	PDF	220mm extension pole, ABS plastic
<u>B32310025-F1</u>	\$9.50	PDF	30mm diameter cap, ABS plastic



MP-B



B72100xxx-xF1



SZ-150



SZ-904



S33552120-03xxxxx



B32310025-F1




B25110032-F1


PATLITE® 30mm LED Signal Towers

Wiring




Contact/Switch



NPN M12 Connector



PNP M12 Connector




PATLITE® Slim Design LED Signal Towers



MES-A and ME-A 25mm Super Slim Signal Towers

These rust-free aluminum body signal towers are designed to be direct mounted. LED module lenses are clear and change color when activated. The super slim design is ideal for tight spaces.



MPS and MP 30mm Signal Towers

These LED towers offer superior impact and heat resistance and have an ABS resin main body. They are designed for direct mounting and have a double insulation for enhanced durability and safety.



LR4 40mm Signal Towers

The LR4 Series feature low maintenance and energy efficiency using LED technology.



LS7 70mm Signal Towers

The LS7 Series feature a smooth body surface that reduces adhesion of water and dust. There are no exposed screws, shafts or other metals making these signal towers adaptable in many environments. This model is suitable for high pressure and high temperature wash down environments. An available model with a buzzer has a sound frequency that cuts through loud environments.

Accessories

