

RHINO PSC Series Power Supplies

Specifications

NEC Class 2 Compliant Supplies

The RHINO PSC series power supplies are plastic low-profile housed switching supplies available in 5, 12 and 24 VDC adjustable output models. There are 8 models with power ratings from 12W to 90W. They have an integral DIN rail mounting adapter and feature universal 120/240 VAC input voltage, adjustable DC output, DC-OK LED indication, and output current limitation.

The RHINO PSC series of switching power supplies provide tightly regulated output voltage for sensitive loads in industrial, commercial and residential environments. The plastic housing is lightweight and low-profile, designed to fit in shallow depth control panels often used in the building automation industry. Screw terminals are provided for simple and speedy wiring terminations.

The RHINO PSC series is both UL508 listed for demanding industrial applications and UL1310 recognized for NEC Class 2 compliance in industrial, commercial and residential applications.



Features

- Low-profile housing - only 2.15 inches (55mm) deep (MCB form factor)
- 5, 12, 24VDC adjustable outputs
- Output power ratings from 12 to 90W
- Integral DIN rail mounting adapter
- Universal input voltage range 120/240 VAC
- Tight output voltage regulation
- DC-OK LED indication
- UL508 Listed
- UL1310 Recognized for NEC Class 2 compliance
- CE compliant
- RoHS compliant



**PSC-05-012, PSC-12-015,
PSC-24-015**



PSC-12-030, PSC-24-030



PSC-12-060, PSC-24-060



PSC-24-090

Input Specifications

Part Number	Input Voltage Range	Input Frequency Range	Input Current [Typical] at full load		Efficiency [Typ @ 115VAC]	C-Curve Circuit Breaker or Slow-blow Fuse
			115 VAC	230 VAC		
PSC-05-012	100-240VAC - Nominal 85 to 264VAC - Universal [output power derating 5% / V for operation below 90 VAC]	47-63 Hz	0.25A typ.	0.17A typ.	76%	6.0 A
PSC-12-015			0.29A typ.	0.20A typ.	78%	
PSC-24-015					79%	
PSC-12-030			0.57A typ.	0.39A typ.	81%	
PSC-24-030					84%	
PSC-12-060			1.00A typ.	0.68A typ.	83%	
PSC-24-060			1.10A typ.	0.70A typ.	85%	
PSC-24-090			1.60A typ.	1.07A typ.	87%	

Output Specifications

Output Specifications									
Part Number	Price	Drawing Link	Output Voltage	Output Volt. Adjust. Range	Max Output Current [A]	Max Output Power [W]	Hold-Up Time		MTBF [IEC 1709 @ 25°C]
							115 VAC	230 VAC	
PSC-05-012	\$56.00	PDF	5.0VDC	5.0 to 5.2VDC	2.4	12	minimum 10 ms	minimum 20 ms	1,600,000 hours
PSC-12-015	\$56.00	PDF	12.0VDC	12.0 to 16.0VDC	1.25	15			
PSC-24-015	\$54.00	PDF	24.0VDC	24.0 to 28.0VDC	0.63				
PSC-12-030	\$57.00	PDF	12.0VDC	12.0 to 16.0VDC	2.5	30			2,100,000 hours
PSC-24-030	\$72.00	PDF	24.0VDC	24.0 to 28.0VDC	1.25				
PSC-12-060	\$72.00	PDF	12.0VDC	12.0 to 16.0VDC	4.5	54			
PSC-24-060	\$86.00	PDF	24.0VDC	24.0 to 28.0VDC	2.5	60			
PSC-24-090	\$106.00	PDF	24.0VDC		3.75	90			1,300,000 hours

RHINO PSC Series Power Supplies

Specifications

General Specifications		
Temperature	Operating: -25 to 60°C [-13 to 140°F] max at nominal load, above +60°C [+140°F] 2.5% / °C derating up to +70°C [+185°F] Storage: -25 to 85°C [-13 to 185°F] max	
Humidity	95% [non-condensing] relative humidity max.	
Output Regulation	1%	
Protection Class II	to IEC/EN 60536	
Safety Standards	UL508, UL1310, Class 2 IEC/EN 60950-1, UL60950-1, EN50178 EN60204, EN61558-2-8	
Output Voltage Ripple	<100 mV peak-to-peak	
Output Protection	Current limitation at 100 - 150% typ. [automatic recovery]	
Electromagnetic Compatibility (EMC)	Emissions - EN61000-6-3 Conducted RI suppression on input - EN55032 class B Radiated RI suppression - EN55032 class B FCC Class B	Immunity - EN61000-6-2 EN61000-4-X
Enclosure Rating	IP 20 [IEC 60529]	
Enclosure Material	Plastic FR2010-110C [UL 94V-0 rated]	
Mounting	DIN rails as per EN50022-35x15/735 [snap-on with self-locking springs]	
Connection	Screw terminals with combi-type screw heads for wire size 24 to 12AWG [0.20 to 3.30mm²]	
Agency Approvals	UL508 Listed, File No. E197592 UL1310 Class 2 Recognized, File No. E198298	

Wiring		
Input/Output	Description	Wire size
AC Input	all models: L, N only [2 pin terminal]	24 -12AWG / 3.30mm² max
DC Output	15 -30 Watt models: single + and - terminals	24 -12AWG / 3.30mm² max
DC Output	60 - 90 Watt models: double + and - terminals	24 -12AWG / 3.30mm² max

Weight	
Part No.	Weight oz [g]
PSC-05-012	3.53 [100]
PSC-12-015	3.53 [100]
PSC-24-015	3.53 [100]
PSC-12-030	5.64 [160]
PSC-24-030	5.64 [160]
PSC-12-060	8.11 [230]
PSC-24-060	8.11 [230]
PSC-24-090	12.0 [340]