

EPSON® LabelWorks PX Series Printers

LW-PX300 Portable Label Printer

The LW-PX300 is a low-cost, compact wire-marking, bar-code and general-identification label printer for creating custom and compliant labels up to 18mm [3/4 in] wide. Identify wires and equipment, organize tool cribs and storage bins, tag assets, and more. This portable, easy-to-use label maker offers flexibility and durability at an affordable price. With the LW-PX300, you can print on a variety of materials such as magnetic tape, heat shrink tube and super strong adhesive tape.

Features

- Thermal Transfer Technology
- Prints on supplies 3 to 18mm [1/8 to 3/4 inch]
- 6mm/second max print speed (with AC power adapter)
- Resolution 180dpi
- 140 x 80 dot back-lit monochrome LCD
- Manual full-cut label cutter
- Over 800 industrial and professional symbols
- Prints custom and compliant labels
- Great for barcodes, shrink tube, magnetic labels and more
- Low cost and portable printer for use in the field or workplace
- Requires 6 AA Batteries (not included)
- Lifetime warranty

System Contents

The LW-PX300 portable label printer comes standard with:

- EPSON LW-PX300 printer
- 212VTBW PX 12mm [1/2 in] black on white tape cartridge
- User manual

The kit adds the following:

- Bumper guard
- AC power adapter
- Industrial carrying case



LW-PX300



LW-PX300VP

LW-PX300 Label Printer and Accessories		
Part Number	Price	Description
LW-PX300	\$55.00	Epson LabelWorks PX series portable label printer, prints labels up to 18mm (3/4in) wide or 5mm (3/16in) nominal diameter, thermal transfer, 180dpi, back-lit monochrome LCD, manual label cutter. For use with Epson LabelWorks PX series label cartridges.
LW-PX300VP	\$85.00	Epson LabelWorks PX series portable label printer kit, prints labels up to 18mm (3/4in) wide or 5mm (3/16in) nominal diameter, thermal transfer, 180dpi, back-lit monochrome LCD, manual label cutter. For use with Epson LabelWorks PX series label cartridges.
APT0615	\$50.25	Epson LabelWorks PX series AC power adapter, replacement. For use with Epson LabelWorks LW-PX300 portable label printer.
LWCS1000	\$66.75	Epson LabelWorks PX series carrying case, replacement. For use with Epson LabelWorks LW-PX300 portable label printer.
LWRG300	\$41.25	Epson LabelWorks PX series bumper guard, replacement. For use with Epson LabelWorks LW-PX300 portable label printer.



APT0615



LWCS1000



LWRG300

EPSON® LabelWorks PX Series Printers

LW-PX400 Portable Label Printer

The [LW-PX400](#) offers power and versatility in a small, light and flexible printer that prints labels up to 24mm [1in] wide. Connect your iOS or Android mobile device to the [LW-PX400](#) via Bluetooth™ to make labels effortlessly via the free mobile apps. Or use Epson's Label Editor software to create professional labels, self-laminating wire wraps, and heat shrink wire markers.

Features

- Thermal Transfer Technology
- Prints on supplies 3 to 24mm [1/8 to 1in]
- 15mm/second maximum print speed (with AC power adapter)
- Portable and wireless printing capabilities powered by AC adapter or 6AA batteries (not included)
- Resolution 180dpi
- Automatic full-cut label cutter
- Bluetooth compatible with mobile device and Windows PC
- Prints custom and compliant labels and wire markings
- Low cost and portable printer for use in the field or workplace
- Lifetime warranty

Connectivity

- Interface: USB, Bluetooth™
- Software download: Epson Label Editor: Windows 7, 8, 8.1, 10, 11, Epson Label Editor Mobile
- Epson Datacom app
- Label Editor Lite for iOS

System Contents

The [LW-PX400](#) portable label printer comes standard with:

- EPSON [LW-PX400](#) printer
- [212VTBWPX](#) 12mm [1/2 in] black on white tape cartridge
- Drop-guard cover
- AC power adapter
- USB cable 1m [3.28 ft]
- User manual



LW-PX400

LW-PX400 Label Printer and Accessories

Part Number	Price	Description
LW-PX400	\$165.00	Epson LabelWorks PX series portable label printer, prints labels up to 24mm (1in) wide or 14mm (9/16in) nominal diameter, thermal transfer, 180dpi, Android/iOS, automatic label cutter. For use with Epson LabelWorks PX series label cartridges.
AST1116	\$50.25	Epson LabelWorks PX series AC power adapter, replacement. For use with Epson LabelWorks LW-PX400 and LW-PX700 portable label printers.
LWRG400	\$41.25	Epson LabelWorks PX series bumper guard, replacement. For use with Epson LabelWorks LW-PX400 portable label printer.



AST1116



LWRG400

EPSON® LabelWorks PX Series Printers

LW-PX700 Portable Label Printer

LW-PX700 offers you a portable label and wire marker solution with exclusive time and cost saving features for creating custom and compliant labels up to 24mm [1in] wide. Type your message in multiple languages and choose between horizontal and vertical labels. Never lose a label with the special "Drop-Stop" feature; it is especially handy with the "Pick-and-Print" mode. The printer will print a label, cut it, hold it, and then automatically print the next label in a batch when the label is removed.

Features

- Thermal Transfer Technology
- Prints on supplies 3 to 24mm [1/8 to 1in]
- 30mm/second maximum print speed (with AC power adapter)
- Portable printing capabilities
- Resolution 180dpi
- 140 x 80 dot back-lit monochrome LCD
- Automatic full- and half-cut label cutter
- Application specific hot keys
- Mixed-length printing for variable length labels
- Powered by AC Adapter included with printer, 6 AA batteries not included, or Lithium-ion battery included in kit or sold separately
- Lifetime warranty

Connectivity

- USB
- Software download: Epson Label Editor: Windows 7, 8, 8.1, 10, 11

System Contents

The LW-PX700 portable label printer comes standard with:

- EPSON LW-PX700 printer
- 212VTBWXP 12mm [1/2 in] black on white tape cartridge
- AC power adapter
- User manual

The kit adds the following:

- Label Editor software download
- USB cable 1m [3.28 ft]
- Lithium-ion battery
- Industrial carrying case
- Attachable magnetic feet



LW-PX700



LW-PX700PCD

LW-PX700 Label Printer and Accessories

Part Number	Price	Description
<u>LW-PX700</u>	\$124.00	Epson LabelWorks PX series portable label printer, prints labels up to 24mm (1in) wide or 14mm (9/16in) nominal diameter, thermal transfer, 180dpi, back-lit monochrome LCD, automatic label cutter. For use with Epson LabelWorks PX series label cartridges.
<u>LW-PX700PCD</u>	\$189.00	Epson LabelWorks PX series portable label printer kit, prints labels up to 24mm (1in) wide or 14mm (9/16in) nominal diameter, thermal transfer, 180dpi, back-lit monochrome LCD, automatic label cutter. For use with Epson LabelWorks PX series label cartridges.
<u>AST1116</u>	\$50.25	Epson LabelWorks PX series AC power adapter, replacement. For use with Epson LabelWorks LW-PX400 and LW-PX700 portable label printers.
<u>LWCS1200</u>	\$50.25	Epson LabelWorks PX series carrying case, replacement. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.
<u>LWPXLION</u>	\$78.75	Epson LabelWorks PX series battery, replacement. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.
<u>LWPXMAG</u>	\$21.00	Epson LabelWorks PX series mounting magnets, replacement. Package of 2. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.



AST1116



LWCS1200



LWPXLION



LWPXMAG

EPSON® LabelWorks PX Series Printers

LW-PX900 Portable Label Printer

Designed with innovative features that save time and tape, the **LW-PX900** features high-speed 360dpi print output that creates highly visible and detailed labels, bar codes and wire identification on a variety of supplies up to 36mm [1-1/2 in] wide. Never lose a label with the special "Drop-Stop" feature; it is especially handy with the "Pick-and-Print" mode. The printer will print a label, cut it, hold it, and then automatically print the next label in a batch when the label is removed.

Features

- Thermal Transfer Technology
- Prints on supplies 3 to 36mm [1/8 to 1-1/2 in]
- 35mm/second maximum print speed (with AC power adapter)
- Portable printing capabilities
- Resolution 360dpi
- 140 x 80 dot back-lit monochrome LCD
- Application specific hot keys
- Mixed-length printing for variable length labels
- Powered by AC Adapter included with printer, 6 AA batteries not included, or Lithium-ion battery included in kit or sold separately
- Lifetime warranty

Connectivity

- USB
- Software download: Epson Label Editor: Windows 7, 8, 8.1, 10, 11

System Contents

The **LW-PX900** portable label printer comes standard with:

- EPSON **LW-PX900** printer
- 212VTBW PX 12mm [1/2 in] black on white tape cartridge
- AC power adapter
- User manual

The kit adds the following:

- Label Editor software download
- USB cable 1m [3.28 ft]
- Lithium-ion battery
- Industrial carrying case
- Attachable magnetic feet



LW-PX900



LW-PX900PCD

LW-PX900 Label Printer and Accessories

Part Number	Price	Description
LW-PX900	\$290.00	Epson LabelWorks PX series portable label printer, prints labels up to 36mm (1-1/2in) wide or 21mm (7/8in) nominal diameter, thermal transfer, 360dpi, back-lit monochrome LCD, automatic label cutter. For use with Epson LabelWorks PX series label cartridges.
LW-PX900PCD	\$368.00	Epson LabelWorks PX series portable label printer kit, prints labels up to 36mm (1-1/2in) wide or 21mm (7/8in) nominal diameter, thermal transfer, 360dpi, back-lit monochrome LCD, automatic label cutter. For use with Epson LabelWorks PX series label cartridges.
AST1527	\$50.25	Epson LabelWorks PX series AC power adapter, replacement. For use with Epson LabelWorks LW-PX900 portable label printer.
LWCS1200	\$50.25	Epson LabelWorks PX series carrying case, replacement. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.
LWPXLION	\$78.75	Epson LabelWorks PX series battery, replacement. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.
LWPXMAG	\$21.00	Epson LabelWorks PX series mounting magnets, replacement. Package of 2. For use with Epson LabelWorks LW-PX700 and LW-PX900 portable label printers.



AST1527



LWCS1200



LWPXLION



LWPXMAG

EPSON® LabelWorks PX Series Labels

Polyester Standard Label Cartridge

Standard label cartridges (polyester) are for general identification for indoor/outdoor usage, barcode label, caution or warning label. The polyester standard cartridges have acrylic adhesive and are available in white, yellow, blue, red, clear, black, orange, purple, and green background colors. The standard label tape cartridges can withstand service temperatures from -55 to 125°C [-67 to 257°F].

Polyester Standard Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
204BWPX	\$18.75	Standard label tape cartridge	4 [1/6]	Polyester	Black	White	30ft [9.1 m] roll
206BBPX	\$18.75		6 [1/4]		Black	Blue	
206BCPX	\$18.75				Black	Clear	
206BGPX	\$18.75				Black	Green	
206BRPX	\$18.75				Black	Red	
206BWPX	\$18.75				Black	White	
206BYPX	\$18.75				Black	Yellow	
206WBPX	\$18.75				White	Black	
209BBPX	\$18.75		9 [3/8]		Black	Blue	
209BCPX	\$18.75				Black	Clear	
209BGPX	\$18.75				Black	Green	
209BRPX	\$18.75				Black	Red	
209BWPX	\$18.75				Black	White	
209BYPX	\$18.75				Black	Yellow	
209WBPX	\$18.75				White	Black	
212BBPX	\$18.75		12 [1/2]		Black	Blue	
212BCPX	\$18.75				Black	Clear	
212BGPX	\$18.75				Black	Green	
212BOPX	\$18.75				Black	Orange	
212BRPX	\$18.75				Black	Red	
212BWPX	\$18.75				Black	White	
212BYPX	\$18.75				Black	Yellow	
212RWPX	\$18.75				Red	White	
212WBPX	\$18.75				White	Black	
212WCPX	\$18.75				White	Clear	
212WGPX	\$18.75				White	Green	
212WLPX	\$18.75				White	Blue	
212WRPX	\$18.75				White	Red	
218BBPX	\$22.50		18 [3/4]		Black	Blue	
218BCPX	\$22.50				Black	Clear	
218BGPX	\$22.50				Black	Green	
218BOPX	\$22.50				Black	Orange	
218BRPX	\$22.50	Black		Red			
218BVPX	\$22.50	Black		Purple			
218BWPX	\$22.50	Black		White			
218BYPX	\$22.50	Black		Yellow			
218WBPX	\$22.50	White		Black			
218WCPX	\$22.50	White		Clear			
218WGPX	\$22.50	White		Green			
218WLPX	\$22.50	White		Blue			
218WRPX	\$22.50	White		Red			

*Inches shown as nominal
Continued on following page



204BWPX



206BYPX



209BGPX



212BOPX



218BVPX

EPSON® LabelWorks PX Series Labels

Continued from previous page

Polyester Standard Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
224BBPX	\$22.50	Standard label tape cartridge	24 [1]	Polyester	Black	Blue	30ft [9.1 m] roll
224BCPX	\$22.50				Black	Clear	
224BGPX	\$22.50				Black	Green	
224BOPX	\$22.50				Black	Orange	
224BRPX	\$22.50				Black	Red	
224BWPX	\$22.50				Black	White	
224BYPX	\$22.50				Black	Yellow	
224WBPX	\$22.50				White	Black	
224WCPX	\$22.50				White	Clear	
224WGPX	\$22.50				White	Green	
224WLPX	\$22.50				White	Blue	
224WRPX	\$22.50				White	Red	
236BBPX	\$30.75		36 [1-1/2]		Black	Blue	
236BCPX	\$30.75				Black	Clear	
236BGPX	\$30.75				Black	Green	
236BOPX	\$30.75				Black	Orange	
236BRPX	\$30.75				Black	Red	
236BWPX	\$30.75				Black	White	
236BYPX	\$30.75				Black	Yellow	
236WBPX	\$30.75				White	Black	
236WLPX	\$30.75				White	Blue	
236WRPX	\$30.75				White	Red	

*Inches shown as nominal

**224WCPX****236BBPX**

Vinyl Standard Label Cartridge

Vinyl standard label cartridges are ideal for wire and cable labeling that require elasticity (wrinkle resistant), and weather resistance for outdoor use. Strong and long-lasting, LabelWorks PX vinyl labels adhere smoothly even on multi-faceted surfaces and stay firmly attached while providing excellent resistance to smearing, scratching, fading, and peeling. The standard vinyl series can withstand operating temperatures from -40 to 90°C [-40 to 194°F].

Vinyl Standard Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
212VTBWPX	\$15.00	Standard label tape cartridge	12 [1/2]	Vinyl	Black	White	22.9 ft [6.97 m] roll
212VTBYPX	\$15.00				Black	Yellow	
218VTBWPX	\$18.75		18 [3/4]		Black	White	
218VTBYPX	\$18.75				Black	Yellow	
224VTBWPX	\$18.75		24 [1]		Black	White	
224VTBYPX	\$18.75				Black	Yellow	
236VTBWPX	\$26.25		36 [1-1/2]		Black	White	
236VTBYPX	\$26.25				Black	Yellow	

*Inches shown as nominal

**212VTBWPX****236VTBYPX**

EPSON® LabelWorks PX Series Labels

Polyester Industrial Adhesive Label Cartridge

Polyester industrial adhesive labels are offered in five different fluorescent background colors and will help with applications that need to make a bold statement. These labels are popular in the medical field and labs for making announcements, warnings and statements.

Polyester Industrial Adhesive Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
218FGPX	\$27.75	Industrial adhesive label cartridge	18 [3/4]	Polyester	Black	Fluorescent Green	30ft [9.1 m] roll
218FOPX	\$27.75				Black	Fluorescent Orange	
218FPPX	\$27.75				Black	Fluorescent Pink	
218FRPX	\$27.75				Black	Fluorescent Red	
218FYPX	\$27.75				Black	Fluorescent Yellow	

*Inches shown as nominal



218FGPX

Strong Adhesive Label Cartridge

Strong adhesive labels are designed for challenging applications where secure bonding is required for porous, curved, or textured surfaces. The slow-set adhesive allows the labels to be easily repositioned before the bond becomes strong and permanent. The strong adhesive bond creates long-lasting, durable labels that can survive the harshest environments.

Strong Adhesive Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
209IBWPX	\$18.75	Strong adhesive label cartridge	9 [3/8]	Polyester	Black	White	30ft [9.1 m] roll
209IBYPX	\$18.75				Black	Yellow	
212GBPX	\$18.75		12 [1/2]		Gold	Black	
212GCPX	\$18.75				Gold	Clear	
212IBWPX	\$18.75				Black	White	
212IBYPX	\$18.75				Black	Yellow	
218IBWPX	\$22.50		18 [3/4]		Black	White	
218IBYPX	\$22.50				Black	Yellow	
224IBWPX	\$22.50		24 [1]		Black	White	
224IBYPX	\$22.50				Black	Yellow	
236IBWPX	\$30.75		36 [1-1/2]		Black	White	
236IBYPX	\$30.75				Black	Yellow	

*Inches shown as nominal



218IBWPX



218IBYPX

Removable Adhesive Label Cartridge

Removable adhesive labels, commonly used in labs and medical industries, stay put where and when you want them. They can easily be removed without surface cleaners and can withstand temperatures from 5 to 35°C [41 to 95°F] at 30 to 80% RH.

Removable Adhesive Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
212RAPX	\$18.75	Removable adhesive label cartridge	12 [1/2]	Polyester	Black	White	30ft [9.1 m] roll

*Inches shown as nominal



212RAPX

EPSON® LabelWorks PX Series Labels

Extra-Tough Nylon Cloth Label Cartridge

Extra-tough labels made of nylon cloth with a matte finish and acrylic adhesive are available in three widths: 12, 18, and 24mm. The extra-tough series are used in wire/cable labeling applications and can withstand operating temperatures from -54 to 135°C [-65 to 275°F].

Extra-Tough Nylon Cloth Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
<u>212NYLBWPX</u>	\$21.00	Extra-tough label cartridge	12 [1/2]	Nylon cloth	Black	White	19ft [5.29 m] roll
<u>218NYLBWPX</u>	\$25.50		18 [3/4]		Black	White	
<u>224NYLBWPX</u>	\$30.00		24 [1]		Black	White	

*Inches shown as nominal



224NYLBWPX

Silver Matte Label Cartridge

Silver matte label cartridges offer a versatile specialty tape with a professional finish making them the perfect solution for barcode labels and scanner applications.

Silver Matte Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
<u>209SMPX</u>	\$18.75	Matte label cartridge	9 [3/8]	Polyester	Black	Silver	30ft [9.1 m] roll
<u>212SMPX</u>	\$18.75		12 [1/2]		Black	Silver	
<u>218SMPX</u>	\$22.50		18 [3/4]		Black	Silver	
<u>224SMPX</u>	\$22.50		24 [1]		Black	Silver	
<u>236SMPX</u>	\$36.00		36 [1-1/2]		Black	Silver	

*Inches shown as nominal



236SMPX

Vinyl Self-Lamination Cable Wrap Label Cartridge

Self-lamination labels provide long-lasting legibility for labels required for cable and wire identification and other applications. These specialty labels, featuring highly legible text and a clear wrap-around protective covering, can withstand temperatures from 5 to 35°C [41 to 95°F], chemicals, and solvents. These vinyl self-laminating labels are highly resistant to smearing, wrinkling, and scratching, and they ensure cables and wires are identifiable for years.

Vinyl Self-Lamination Cable Wrap Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
<u>224VSLPX</u>	\$25.50	Self-lamination cable wrap label cartridge	24 [1]	Vinyl	Black	White	26.2 ft [7.98 m] roll
<u>236VSLPX</u>	\$31.50		36 [1-1/2]		Black	White	

*Inches shown as nominal



236VSLPX

EPSON® LabelWorks PX Series Labels

Magnetic Label Tape Cartridge

Magnetic labels are suited for applications that require temporary, reusable and movable labels. Magnetic labels can withstand extremes in temperature 15°C [39°F] and more, and humidity 30 to 80% RH. The magnetic labels are perfect for metal shelving, toolboxes, metal signs, heavy equipment and many other applications.

Magnetic Label Cartridge							
Part Number	Price	Description	Width mm [in]*	Material	Text Color	Background Color	Length
212MTBBPX-4.9	\$9.00	Magnetic label tape cartridge	12 [1/2]	Polyester- laminated magnet	Black	Blue	4.9 ft [1.49 m] roll
212MTBGPX-4.9	\$9.00				Black	Green	
212MTBRPX-4.9	\$9.00				Black	Red	
212MTBWPX-4.9	\$9.00				Black	White	
212MTBYPX-4.9	\$9.00				Black	Yellow	
218MTBBPX-4.9	\$9.75		18 [3/4]		Black	Blue	
218MTBGPX-4.9	\$9.75				Black	Green	
218MTBRPX-4.9	\$9.75				Black	Red	
218MTBWPX-4.9	\$9.75				Black	White	
218MTBYPX-4.9	\$9.75				Black	Yellow	
224MTBBPX-4.9	\$9.75		24 [1]		Black	Blue	
224MTBGPX-4.9	\$9.75				Black	Green	
224MTBRPX-4.9	\$9.75				Black	Red	
224MTBWPX-4.9	\$9.75				Black	White	
224MTBYPX-4.9	\$9.75				Black	Yellow	
236MTBBPX-4.9	\$12.75		36 [1-1/2]		Black	Blue	
236MTBGPX-4.9	\$12.75				Black	Green	
236MTBRPX-4.9	\$12.75				Black	Red	
236MTBWPX-4.9	\$12.75				Black	White	
236MTBYPX-4.9	\$12.75				Black	Yellow	

*Inches shown as nominal



[212MTBBPX-4.9](#)



[218MTBGPX-4.9](#)



[224MTBYPX-4.9](#)



[236MTBRPX-4.9](#)

EPSON® LabelWorks PX Series Labels

Heat-Shrink Tube Label Cartridge

Heat-shrink tube label cartridges provide insulation when shrunk down and ensure a secure fit on wires and cables with a 2:1 or 3:1 shrink ratio. They are constructed of flame-retardant polyolefin and are available in sizes from 3mm [1/8 in] to 21mm [7/8 in] nominal diameter, with black or white text on a white, yellow, red, black, or blue background.



Heat-Shrink Tube Label Cartridge																											
Part Number	Price	Text Color	Background Color	Nominal Diameter mm [in]	Internal Diameter as Supplied mm [in]	Range of Wire Diameter mm [in] *	Shrink Ratio	AWG *	Works With	Material	Length																
203YLBWPX	\$29.25	Black	White	3 [1/8]	3.4 [0.133]	1.11-2.90 [0.044 - 0.114]	3:1	16-22	LW-PX300 LW-PX400 LW-PX700 LW-PX900	Polyolefin	98in [2.48 m] roll																
203YLBYPX	\$28.50	Black	Yellow					22-14																			
203B20BWPX	Retired	Black	White		3.8 [0.150]	1.40 - 3.30 [0.055 - 0.150]																					
203B20BYPX	Retired	Black	Yellow																								
205STBRPX	\$28.50	Black	Red	5 [3/16]	5.7 [0.224]	3.30 - 5.20 [0.130 - 0.205]	2:1	12-8				LW-PX300 LW-PX400 LW-PX700 LW-PX900	Polyolefin	98in [2.48 m] roll													
205STBWPX	\$28.50	Black	White																								
205STBYPX	\$28.50	Black	Yellow																								
205STWBPX	\$28.50	White	Black																								
205YLBBPX	\$28.50	Black	Blue	6 [1/4]	5.4 [0.213]	1.90 - 5.20 [0.075 - 0.205]	3:1	18-10			LW-PX300 LW-PX400 LW-PX700 LW-PX900				Polyolefin	98in [2.48 m] roll											
208B20BWPX	\$31.50	Black	White					18-6																			
208B20BYPX	\$31.50	Black	Yellow																								
210STBWPX-90	\$36.75	Black	White	10 [3/8]	9.5 [0.374]	3.50 - 8.00 [0.138 - 0.315]	2:1	12-4									LW-PX300 LW-PX400 LW-PX700 LW-PX900	Polyolefin	90in [2.28 m] roll								
211STBRPX	\$36.75	Black	Red	11 [1/2]				8-2						98in [2.48 m] roll													
211STBWPX	\$36.75	Black	White																								
211STBYPX	\$36.75	Black	Yellow																								
211STWBPX	\$36.75	White	Black																								
214STBWPX	\$39.75	Black	White	14 [9/16]	13 [0.512]	7.70 - 12.50 [0.303 - 0.492]		5-0								LW-PX300 LW-PX400 LW-PX700 LW-PX900			Polyolefin	98in [2.48 m] roll							
221STBWPX	\$42.00	Black	White	21 [7/8]				1-0000																			
221STBYPX	\$42.00	Black	Yellow																								

* Due to manufacturing variances in insulation thickness, these attributes listed are approximate.



[203YLBWPX](#)



[205STBRPX](#)



[208B20BYPX](#)



[211STWBPX](#)

EPSON® LabelWorks PX Series Labels

Metallic Label Cartridge

Metallic labels are great for barcode labels, asset identification, and applications that require nameplate-like quality. They are available in silver with black text, an 18mm [3/4 in] width, and are made of polyethylene terephthalate. This tape offers a perfect touch for labeling projects.

Metallic Label Cartridge								
Part Number	Price	Description	Width mm [in]	Material	Text Color	Background Color	Length	Works With
<u>218BMETSPX</u>	\$14.75	Metallic label tape cartridge	18 [3/4]	Polyethylene terephthalate	Black	Silver	30ft [9.14 m] roll	LW-PX300 LW-PX400 LW-PX700 LW-PX900

**218BMETSPX**

Printable Ribbon Label Cartridge

Printable ribbon is available in four color combinations in 12mm [1/2 in] cartridges. Create personalized, custom ribbons for cable flags, tool identification, and much more using a wide variety of fonts, industry-standard images and designs. Printable ribbon is compatible in ALL Epson LabelWorks printers and is recommended for use with the Epson Label Editor Software and Label Editor Mobile App for best results.

Printable Ribbon Label Cartridge								
Part Number	Price	Description	Width mm [in]	Material	Text Color	Background Color	Length	Works With
<u>212RBGPX</u>	\$9.75	Printable ribbon label cartridge	12 [1/2]	Polyester	Black	Gold	16ft [4.87 m] roll	LW-PX300 LW-PX400 LW-PX700 LW-PX900
<u>212GRGPX</u>	\$9.75				Gold	Red		
<u>212RBBPX</u>	\$9.75				Black	Blue		
<u>212RBPPX</u>	\$9.75				Black	Pink		

**212RGRPX**

Craft Paper Tape Label Cartridge

Think packaging and labeling with textured and uncoated kraft paper material. Great for tough packaging labels and small business labeling. Available in 12mm [1/2 in], 18mm [3/4 in], and 24mm [1 in] widths.

Craft Paper Tape Label Cartridge								
Part Number	Price	Description	Width mm [in]	Material	Text Color	Background Color	Length	Works With
<u>212CPBBEPX</u>	\$14.75	Craft paper tape label cartridge	12 [1/2]	Kraft paper	Black	Brown	16.5 ft [5.02 m] roll	LW-PX300 LW-PX400 LW-PX700 LW-PX900
<u>218CPBBEPX</u>	\$14.75		18 [3/4]		Black	Brown		
<u>224CPBBEPX</u>	\$14.75		24 [1]		Black	Brown		

**212CPBBEPX**

EPSON® LabelWorks PX Series Labels

EPSON Label Standards Guide

The graphic below provides examples of label configurations and how they meet ANSI and ISO standards.

STANDARDS ↓ COLORS				
	ANSI Z535 Visual Workplace	ISO 3864 Visual Workplace	ISO 7010 Graphical Symbols	ANSI A13.1 Pipemarking
Black on White	General ID	Supplementary Information	—	—
White on Red	Danger	Danger, Prohibition, Fire Safety	Prohibition, Fire Safety	Fire Quenching
Black on Orange	Warning	Warning	—	Toxic and Corrosive Fluid
Black on Yellow	Caution	Caution, Triangular Warning Symbols	Warning	Flammable Fluids
White on Green	Instruction	Safe Conditions	Safe Conditions	Potable Water
White on Blue	Notice	Mandatory Action	Mandatory Action	Compressed Air
White on Black	General ID	—	—	—