

NEMA 3R, 12, and 13 Stainless Steel Desk Consoles



Your Enclosure Source®



Applications

Intended for indoor use to provide a degree of protection to personnel against access to hazardous parts, also to provide a degree of protection for the equipment inside the enclosure against ingress of solid foreign objects and falling dirt, to provide a degree of protection with respect to harmful effects on the equipment due to the ingress of water, splashing water. Designed for use in standing or sitting position with single and dual access and top that opens for easy accessibility.

Construction

- 14-gauge stainless steel Type 304 and 316/316L
- 25° slope top
- Door props on sloped door to hold in the open position
- Oil- and water-resistant gasket
- Flange trough collar around all sides of door opening
- Concealed hinges
- Removable doors
- Removable print pocket
- Ground studs on door and body
- Rubber pads with provision for leveling pads on bottom of enclosure
- Black, 1/4-turn latches on top door
- Keylocking, black 3-point flush swing handle in front door of single access, front and rear doors on dual access
- Mounting studs welded on interior back for mounting optional subpanels on single access console
- Mounting channels welded on sides of interior body for mounting optional subpanels on dual access console
- Mounting hardware is included for one optional subpanel.
- Optional tamper-resistant inserts or padlocking handles are available.

Finish

- #4 brushed finish on all exterior surfaces
- Optional panels are powder coated white.

Listings

- NEMA Type 3R, 12, and 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



NEMA 3R, 12, and 13 Stainless Steel Desk Consoles



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

304 Stainless Steel Desk Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
Single-Access Single-Door					
SCE-463719SDCSS	\$5,302.00	47.18 x 37.25 x 24.50 [1198 x 946 x 622]	PDF	SCE-36P36	\$185.00
Dual-Access Single-Door					
SCE-463719DCSS6	\$5,716.00	47.18 x 37.25 x 24.50 [1198 x 946 x 622]	PDF	SCE-36P36	\$185.00
Single-Access Double-Door					
SCE-464919SDCSS	\$6,132.00	47.18 x 49.25 x 24.50 [1198 x 1251 x 622]	PDF	SCE-48P36	\$240.00
SCE-466019SDCSS	\$7,939.00	47.18 x 59.88 x 24.50 [1198 x 1521 x 622]	PDF	SCE-60PC36	\$282.00
Dual-Access Double-Door					
SCE-464919DCSS	\$6,449.00	47.18 x 49.25 x 25.57 [1198 x 1251 x 649]	PDF	SCE-48P36	\$240.00
SCE-466019DCSS	\$8,572.00	47.18 x 59.88 x 25.57 [1198 x 1521 x 649]	PDF	SCE-60PC36	\$282.00

Note: Dimensions in inches [millimeters].

316 Stainless Steel Desk Consoles

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
Single-Access Single-Door					
SCE-463719SDCSS6	\$5,412.00	47.18 x 37.25 x 25.57 [1198 x 946 x 649]	PDF	SCE-36P36	\$185.00
Dual-Access Single-Door					
SCE-463719DCSS	\$5,600.00	47.18 x 37.25 x 25.57 [1198 x 946 x 649]	PDF	SCE-36P36	\$185.00
Single-Access Double-Door					
SCE-464919SDCSS6	\$6,260.00	47.18 x 49.25 x 24.50 [1198 x 1251 x 622]	PDF	SCE-48P36	\$240.00
SCE-466019SDCSS6	\$8,104.00	47.18 x 59.88 x 24.50 [1198 x 1521 x 622]	PDF	SCE-60PC36	\$282.00
Dual-Access Double-Door					
SCE-464919DCSS6	\$6,583.00	47.18 x 49.25 x 25.57 [1198 x 1251 x 649]	PDF	SCE-48P36	\$240.00
SCE-466019DCSS6	\$8,751.00	47.18 x 59.88 x 25.57 [1198 x 1521 x 649]	PDF	SCE-60PC36	\$282.00

Note: Dimensions in inches [millimeters].