

NEMA 3R and 12, and, 13 Double-Door Floor-Mounted



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor and outdoor locations. Provides protection from dust, oil and water. For outdoor applications a drip shield is recommended.

Construction

- 12-gauge carbon steel
- Seams continuously welded and ground smooth—no holes or knockouts
- Strong, rigid construction with body stiffeners
- Gasketed overlapping doors eliminate need for a center post
- Black zinc diecast keylocking/padlocking handle
- 3-point latching mechanism
- Latch rods ramp shoes for easier door closing.
- Concealed hinges
- Removable print pocket
- 12in [305mm] removable floor stands
- Heavy-duty lifting eyes
- Panel supports
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanel
- Ground stud on door and body
- Provisions for light kit
- Hole plugs are provided to seal holes in bottom of enclosure.

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R and 12, and Type 13
- cULus Listed Type 3R and 12 [File E69392]
- IEC 60529 IP55



NEMA 3R and 12, and, 13 Double-Door Floor-Mounted

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.



Your Enclosure Source®

NEMA 3R and 12, and, 13 Double-Door Floor-Mounted					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-604808LP	\$2,026.00	60.00 x 48.00 x 9.05 [1524 x 1219 x 230]	PDF	SCE-60P48	\$373.00
SCE-604810LP	\$2,091.00	60.00 x 48.00 x 11.05 [1524 x 1219 x 281]	PDF	SCE-60P48	\$373.00
SCE-604812LP	\$2,156.00	60.00 x 48.00 x 13.05 [1524 x 1219 x 331]	PDF	SCE-60P48	\$373.00
SCE-604816LP	\$2,284.00	60.00 x 48.00 x 17.05 [1524 x 1219 x 433]	PDF	SCE-60P48	\$373.00
SCE-604824LP	\$2,545.00	60.00 x 48.00 x 25.05 [1524 x 1219 x 636]	PDF	SCE-60P48	\$373.00
SCE-606010LP	\$2,342.00	60.00 x 60.00 x 11.05 [1524 x 1524 x 281]	PDF	SCE-60P60	\$460.00
SCE-606012LP	\$2,414.00	60.00 x 60.00 x 13.05 [1524 x 1524 x 331]	PDF	SCE-60P60	\$460.00
SCE-606016LP	\$2,559.00	60.00 x 60.00 x 17.05 [1524 x 1524 x 433]	PDF	SCE-60P60	\$460.00
SCE-606024LP	\$2,848.00	60.00 x 60.00 x 25.05 [1524 x 1524 x 636]	PDF	SCE-60P60	\$460.00
SCE-726010ULP	\$2,679.00	72.00 x 60.00 x 11.05 [1829 x 1524 x 281]	PDF	SCE-72P60	\$548.00
SCE-726012ULP	\$2,762.00	72.00 x 60.00 x 13.05 [1829 x 1524 x 331]	PDF	SCE-72P60	\$548.00
SCE-726016ULP	\$2,923.00	72.00 x 60.00 x 17.05 [1829 x 1524 x 433]	PDF	SCE-72P60	\$548.00
SCE-726024ULP	\$3,253.00	72.00 x 60.00 x 25.05 [1829 x 1524 x 636]	PDF	SCE-72P60	\$548.00
SCE-727210ULP	\$2,985.00	72.00 x 72.00 x 11.05 [1829 x 1829 x 281]	PDF	SCE-72P72	\$654.00
SCE-727212ULP	\$3,075.00	72.00 x 72.00 x 13.05 [1829 x 1829 x 331]	PDF	SCE-72P72	\$654.00
SCE-727216ULP	\$3,253.00	72.00 x 72.00 x 17.05 [1829 x 1829 x 433]	PDF	SCE-72P72	\$654.00
SCE-727224ULP	\$3,611.00	72.00 x 72.00 x 25.05 [1829 x 1829 x 636]	PDF	SCE-72P72	\$654.00

Note: Dimensions in inches [millimeters].

NEMA 3R and 12, and, 13 Double-Door Floor-Mounted



Dimensions

