

# NEMA 4, 12, and 13 Wall-Mount Pushbutton



## Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

## Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

## Finish

- ANSI 61 gray or RAL 1018 yellow powder coated inside and out

## Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



## Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 4, 12, and 13 Wall-Mount Pushbutton

| ANSI 61 Gray               |                           |          | RAL 1018 Yellow                 |          | Size<br>HxWxD                        | Holes | Drawing Link        |
|----------------------------|---------------------------|----------|---------------------------------|----------|--------------------------------------|-------|---------------------|
| 22mm                       | 30mm                      | Price    | 30mm                            | Price    |                                      |       |                     |
| <a href="#">SCE-1PBI</a>   | <a href="#">SCE-1PB</a>   | \$56.00  | <a href="#">SCE-1PB-RAL1018</a> | \$69.00  | 3.81 x 3.56 x 2.91 [97 x 90 x 74]    | 1     | <a href="#">PDF</a> |
| <a href="#">SCE-2PBI</a>   | <a href="#">SCE-2PB</a>   | \$65.00  | <a href="#">SCE-2PB-RAL1018</a> | \$79.00  | 6.06 x 3.56 x 2.91 [154 x 90 x 74]   | 2     | <a href="#">PDF</a> |
| <a href="#">SCE-3PBI</a>   | <a href="#">SCE-3PB</a>   | \$73.00  | <a href="#">SCE-3PB-RAL1018</a> | \$89.00  | 8.31 x 3.56 x 2.91 [211 x 90 x 74]   | 3     | <a href="#">PDF</a> |
| <a href="#">SCE-4PBI</a>   | <a href="#">SCE-4PB</a>   | \$81.00  | <a href="#">SCE-4PB-RAL1018</a> | \$98.00  | 10.56 x 3.56 x 2.91 [268 x 90 x 74]  | 4     | <a href="#">PDF</a> |
| <a href="#">SCE-4SPBI</a>  | <a href="#">SCE-4SPB</a>  | \$90.00  | —                               | —        | 7.56 x 6.56 x 3.16 [192 x 167 x 80]  | 4     | <a href="#">PDF</a> |
| <a href="#">SCE-5PBI</a>   | <a href="#">SCE-5PB</a>   | \$89.00  | <a href="#">SCE-5PB-RAL1018</a> | \$108.00 | 12.81 x 3.56 x 2.91 [325 x 90 x 74]  | 5     | <a href="#">PDF</a> |
| <a href="#">SCE-6PBI</a>   | <a href="#">SCE-6PB</a>   | \$103.00 | —                               | —        | 9.81 x 6.56 x 3.16 [249 x 167 x 80]  | 6     | <a href="#">PDF</a> |
| <a href="#">SCE-6PBVLI</a> | <a href="#">SCE-6PBVL</a> | \$97.00  | —                               | —        | 15.06 x 3.56 x 2.91 [383 x 90 x 74]  | 6     | <a href="#">PDF</a> |
| <a href="#">SCE-8PBI</a>   | <a href="#">SCE-8PB</a>   | \$116.00 | —                               | —        | 20.56 x 3.56 x 2.91 [522 x 90 x 74]  | 8     | <a href="#">PDF</a> |
| <a href="#">SCE-9PBI</a>   | <a href="#">SCE-9PB</a>   | \$119.00 | —                               | —        | 9.81 x 8.81 x 3.16 [249 x 224 x 80]  | 9     | <a href="#">PDF</a> |
| <a href="#">SCE-12PBI</a>  | <a href="#">SCE-12PB</a>  | \$134.00 | —                               | —        | 12.06 x 8.81 x 3.16 [306 x 224 x 80] | 12    | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# NEMA 4, 12, and 13 Wall-Mount Pushbutton



## Dimensions

