

# NEMA 1 Single-Door Wall-Mount



## Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust tight protection.

## Construction

- 14-gauge, 16-gauge, or 18-gauge carbon steel depending on size
  - See drawings for details
- Spot weld construction
- Standoffs are provided for mounting optional subpanels.
- Butt hinge
- Doors open 180°
- Black, 1/4-turn latches
- Latches are opened or closed with a screwdriver.
- Ground stud on door and body
- Mounting holes in back of enclosure
- Subpanel mounting hardware included
- Optional mounting straps are available.

## Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 1
- cULus Listed Type 1
- IEC 60529 IP30



# NEMA 1 Single-Door Wall-Mount



## Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 1 Single-Door Wall-Mount

| Part Number                   | Price    | Size<br>HxWxD                           | Drawing<br>Link     | Optional<br>Subpanel        | Price    |
|-------------------------------|----------|-----------------------------------------|---------------------|-----------------------------|----------|
| <a href="#">SCE-6N604LP</a>   | \$45.50  | 6.38 x 6.38 x 4.12 [162 x 162 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-6N6MP</a>   | \$4.25   |
| <a href="#">SCE-8N604LP</a>   | \$50.00  | 8.38 x 6.38 x 4.12 [213 x 162 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-8N6MP</a>   | \$5.00   |
| <a href="#">SCE-8N804LP</a>   | \$55.00  | 8.38 x 8.38 x 4.12 [213 x 213 x 105]    | <a href="#">PDF</a> | <a href="#">SCE-8N8MP</a>   | \$5.75   |
| <a href="#">SCE-8N806LP</a>   | \$62.00  | 8.38 x 8.38 x 6.12 [213 x 213 x 155]    | <a href="#">PDF</a> | <a href="#">SCE-8N8MP</a>   | \$5.75   |
| <a href="#">SCE-10N804LP</a>  | \$61.00  | 10.38 x 8.38 x 4.12 [264 x 213 x 105]   | <a href="#">PDF</a> | <a href="#">SCE-10N8MP</a>  | \$6.75   |
| <a href="#">SCE-10N806LP</a>  | \$69.00  | 10.38 x 8.38 x 6.12 [264 x 213 x 155]   | <a href="#">PDF</a> | <a href="#">SCE-10N8MP</a>  | \$6.75   |
| <a href="#">SCE-10N1004LP</a> | \$62.00  | 10.38 x 10.38 x 4.12 [264 x 264 x 105]  | <a href="#">PDF</a> | <a href="#">SCE-10N10MP</a> | \$8.00   |
| <a href="#">SCE-10N1006LP</a> | \$76.00  | 10.38 x 10.38 x 6.12 [264 x 264 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-10N10MP</a> | \$8.00   |
| <a href="#">SCE-12N1004LP</a> | \$73.00  | 12.38 x 10.38 x 4.12 [314 x 264 x 105]  | <a href="#">PDF</a> | <a href="#">SCE-12N10MP</a> | \$9.00   |
| <a href="#">SCE-12N1006LP</a> | \$83.00  | 12.38 x 10.38 x 6.12 [314 x 264 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-12N10MP</a> | \$9.00   |
| <a href="#">SCE-12N1204LP</a> | \$80.00  | 12.38 x 12.38 x 4.12 [314 x 314 x 105]  | <a href="#">PDF</a> | <a href="#">SCE-12N12MP</a> | \$10.75  |
| <a href="#">SCE-12N1206LP</a> | \$91.00  | 12.38 x 12.38 x 6.12 [314 x 314 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-12N12MP</a> | \$10.75  |
| <a href="#">SCE-12N1208LP</a> | \$101.00 | 12.38 x 12.38 x 8.12 [314 x 314 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-12N12MP</a> | \$10.75  |
| <a href="#">SCE-14N1204LP</a> | \$87.00  | 14.38 x 12.38 x 4.12 [365 x 314 x 105]  | <a href="#">PDF</a> | <a href="#">SCE-14N12MP</a> | \$12.00  |
| <a href="#">SCE-14N1206LP</a> | \$99.00  | 14.38 x 12.38 x 6.12 [365 x 314 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-14N12MP</a> | \$12.00  |
| <a href="#">SCE-14N1208LP</a> | \$110.00 | 14.38 x 12.38 x 8.12 [365 x 314 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-14N12MP</a> | \$12.00  |
| <a href="#">SCE-16N1206LP</a> | \$148.00 | 16.38 x 12.38 x 6.12 [416 x 314 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-16N12MP</a> | \$17.50  |
| <a href="#">SCE-16N1208LP</a> | \$161.00 | 16.38 x 12.38 x 8.12 [416 x 314 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-16N12MP</a> | \$17.50  |
| <a href="#">SCE-16N1606LP</a> | \$165.00 | 16.38 x 16.38 x 6.12 [416 x 416 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-16N16MP</a> | \$29.00  |
| <a href="#">SCE-16N1608LP</a> | \$180.00 | 16.38 x 16.38 x 8.12 [416 x 416 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-16N16MP</a> | \$29.00  |
| <a href="#">SCE-16N2006LP</a> | \$183.00 | 16.38 x 20.38 x 6.12 [416 x 518 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-20N16MP</a> | \$32.50  |
| <a href="#">SCE-20N1606LP</a> | \$183.00 | 20.38 x 16.38 x 6.12 [518 x 416 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-20N16MP</a> | \$32.50  |
| <a href="#">SCE-20N1608LP</a> | \$200.00 | 20.38 x 16.38 x 8.12 [518 x 416 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-20N16MP</a> | \$32.50  |
| <a href="#">SCE-20N2006LP</a> | \$201.00 | 20.38 x 20.38 x 6.12 [518 x 518 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-20N20MP</a> | \$42.00  |
| <a href="#">SCE-20N2008LP</a> | \$220.00 | 20.38 x 20.38 x 8.12 [518 x 518 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-20N20MP</a> | \$42.00  |
| <a href="#">SCE-20N2010LP</a> | \$239.00 | 20.38 x 20.38 x 10.12 [518 x 518 x 257] | <a href="#">PDF</a> | <a href="#">SCE-20N20MP</a> | \$42.00  |
| <a href="#">SCE-24N1606LP</a> | \$199.00 | 24.38 x 16.38 x 6.12 [619 x 416 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-24N16MP</a> | \$34.50  |
| <a href="#">SCE-24N2006LP</a> | \$222.00 | 24.38 x 20.38 x 6.12 [619 x 518 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-24N20MP</a> | \$48.00  |
| <a href="#">SCE-24N2008LP</a> | \$243.00 | 24.38 x 20.38 x 8.12 [619 x 518 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-24N20MP</a> | \$48.00  |
| <a href="#">SCE-24N2406LP</a> | \$225.00 | 24.38 x 24.38 x 6.12 [619 x 619 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-24N24MP</a> | \$56.00  |
| <a href="#">SCE-24N2408LP</a> | \$248.00 | 24.38 x 24.38 x 8.12 [619 x 619 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-24N24MP</a> | \$56.00  |
| <a href="#">SCE-24N2010LP</a> | \$264.00 | 24.38 x 20.38 x 10.12 [619 x 518 x 257] | <a href="#">PDF</a> | <a href="#">SCE-24N20MP</a> | \$48.00  |
| <a href="#">SCE-24N2412LP</a> | \$293.00 | 24.38 x 24.38 x 12.12 [619 x 619 x 308] | <a href="#">PDF</a> | <a href="#">SCE-24N24MP</a> | \$56.00  |
| <a href="#">SCE-30N2406LP</a> | \$250.00 | 30.38 x 24.38 x 6.12 [772 x 619 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-30N24MP</a> | \$66.00  |
| <a href="#">SCE-30N2408LP</a> | \$278.00 | 30.38 x 24.38 x 8.12 [772 x 619 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-30N24MP</a> | \$66.00  |
| <a href="#">SCE-30N2412LP</a> | \$327.00 | 30.38 x 24.38 x 12.12 [772 x 619 x 308] | <a href="#">PDF</a> | <a href="#">SCE-30N24MP</a> | \$66.00  |
| <a href="#">SCE-30N3008LP</a> | \$314.00 | 30.38 x 30.38 x 8.12 [772 x 772 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-30N30MP</a> | \$88.00  |
| <a href="#">SCE-36N2406LP</a> | \$291.00 | 36.38 x 24.38 x 6.12 [924 x 619 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-36N24MP</a> | \$80.00  |
| <a href="#">SCE-36N2408LP</a> | \$320.00 | 36.38 x 24.38 x 8.12 [924 x 619 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-36N24MP</a> | \$80.00  |
| <a href="#">SCE-36N2412LP</a> | \$370.00 | 36.38 x 24.38 x 12.12 [924 x 619 x 308] | <a href="#">PDF</a> | <a href="#">SCE-36N24MP</a> | \$80.00  |
| <a href="#">SCE-36N3006LP</a> | \$319.00 | 36.38 x 30.38 x 6.12 [924 x 772 x 155]  | <a href="#">PDF</a> | <a href="#">SCE-36N30MP</a> | \$106.00 |
| <a href="#">SCE-36N3008LP</a> | \$350.00 | 36.38 x 30.38 x 8.12 [924 x 772 x 206]  | <a href="#">PDF</a> | <a href="#">SCE-36N30MP</a> | \$106.00 |
| <a href="#">SCE-36N3012LP</a> | \$413.00 | 36.38 x 30.38 x 12.12 [924 x 772 x 308] | <a href="#">PDF</a> | <a href="#">SCE-36N30MP</a> | \$106.00 |

Note: Dimensions in inches [millimeters].