

# NEMA 1 Screw Cover Galvanized Steel Wall-Mount



SC080806G



SC080806GNK

## Applications

These enclosures are designed for use as junction boxes and pull boxes in commercial and general industrial applications.

## Construction

- Bodies and doors fabricated from G-90 pre-galvanized steel
- Flat, removable covers fastened with plated steel screws
- Cover design permits easy removal without extracting cover screws
- Mounting holes on back of enclosure
- Available with or without knockouts
- Removable concentric knockouts on all four sides of standard enclosures with knockouts

## Finish

- G-90 pre-galvanized steel

## Listings

- UL 50, 1 [UL File E6924]
- Meets NEMA/EEMAC 1 requirements

## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## NEMA 1 Screw Cover Wall-Mount Galvanized Steel

| Galvanized     |         |                   |         | Body/Door Steel Gauge | Enclosure SizeHxD                     | Knockout Pattern |             |
|----------------|---------|-------------------|---------|-----------------------|---------------------------------------|------------------|-------------|
| With Knockouts | Price   | Without Knockouts | Price   |                       |                                       | Width Side       | Height Side |
| SC040404G*     | \$11.25 | SC040404GNK*      | \$11.25 | 16/16                 | 4.13 x 4.13 x 4.47 [105 x 105 x 114]  | A                | A           |
| SC040604G*     | \$13.50 | SC040604GNK*      | \$13.50 | 16/16                 | 6.13 x 4.13 x 4.47 [156 x 105 x 114]  | A                | A-B-A       |
| SC060604G      | \$16.00 | SC060604GNK       | \$16.00 | 16/16                 | 6.13 x 6.13 x 4.47 [156 x 156 x 114]  | A-B-A            | A-B-A       |
| SC060606G      | \$19.25 | SC060606GNK       | \$19.25 | 16/16                 | 6.13 x 6.13 x 6.47 [156 x 156 x 164]  | A-B-A            | A-B-A       |
| SC060804G      | \$18.75 | SC060804GNK       | \$18.75 | 16/16                 | 8.13 x 6.13 x 4.47 [207 x 156 x 114]  | A-B-A            | A-B-A       |
| SC060806G      | \$21.50 | SC060806GNK       | \$21.50 | 16/16                 | 8.13 x 6.13 x 6.47 [207 x 156 x 164]  | A-B-A            | A-B-A       |
| SC061204G      | \$25.00 | SC061204GNK       | \$25.00 | 16/16                 | 12.13 x 6.13 x 4.47 [308 x 156 x 114] | A-B-A            | B-A-F-F-A-B |
| SC061206G      | \$27.00 | SC061206GNK       | \$27.00 | 16/16                 | 12.13 x 6.13 x 6.47 [308 x 156 x 164] | A-B-A            | B-A-F-F-A-B |
| SC080804G      | \$22.00 | SC080804GNK       | \$22.00 | 16/16                 | 8.13 x 8.13 x 4.47 [207 x 207 x 114]  | A-B-A            | A-B-A       |
| SC080806G      | \$26.50 | SC080806GNK       | \$26.50 | 16/16                 | 8.13 x 8.13 x 6.47 [207 x 207 x 164]  | A-B-A            | A-B-A       |
| SC080808G      | \$30.00 | SC080808GNK       | \$30.00 | 16/16                 | 8.00 x 8.13 x 8.13 [203 x 207 x 207]  | A-B-A            | A-B-A       |
| SC081004G      | \$25.00 | SC081004GNK       | \$25.00 | 16/16                 | 10.13 x 8.13 x 4.47 [257 x 207 x 114] | A-B-A            | B-A-F-F-A   |
| SC081006G      | \$30.00 | SC081006GNK       | \$30.00 | 16/16                 | 10.13 x 8.13 x 6.47 [257 x 207 x 164] | A-B-A            | B-A-F-F-A   |
| SC081204G      | \$28.50 | SC081204GNK       | \$28.50 | 16/16                 | 12.13 x 8.13 x 4.47 [308 x 207 x 114] | A-B-A            | B-A-F-F-A-B |
| SC081206G      | \$32.50 | SC081206GNK       | \$32.50 | 16/16                 | 12.13 x 8.13 x 6.47 [308 x 207 x 164] | A-B-A            | B-A-F-F-A-B |

Notes: Dimensions in inches [millimeters].

\*Not UL listed.

Table continued on next page

# NEMA 1 Screw Cover Galvanized Steel Wall-Mount



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Table continued from previous page

| NEMA 1 Screw Cover Wall-Mount Galvanized Steel                |          |                             |          |                       |                                         |                  |                 |
|---------------------------------------------------------------|----------|-----------------------------|----------|-----------------------|-----------------------------------------|------------------|-----------------|
| Galvanized                                                    |          |                             |          | Body/Door Steel Gauge | Enclosure SizeHxWxD                     | Knockout Pattern |                 |
| With Knockouts                                                | Price    | Without Knockouts           | Price    |                       |                                         | Width Side       | Height Side     |
| <a href="#">SC101004G</a>                                     | \$29.00  | <a href="#">SC101004GNK</a> | \$29.00  | 16/16                 | 10.13 x 10.13 x 4.47 [257 x 257 x 114]  | B-A-F-F-A        | B-A-F-F-A       |
| <a href="#">SC101006G</a>                                     | \$34.50  | <a href="#">SC101006GNK</a> | \$34.50  | 16/16                 | 10.13 x 10.13 x 6.47 [257 x 257 x 164]  | B-A-F-F-A        | B-A-F-F-A       |
| <a href="#">SC101204G</a>                                     | \$32.50  | <a href="#">SC101204GNK</a> | \$32.50  | 16/16                 | 12.13 x 10.13 x 4.47 [308 x 257 x 114]  | B-A-F-F-A        | B-A-F-F-A-B     |
| <a href="#">SC101206G</a>                                     | \$39.00  | <a href="#">SC101206GNK</a> | \$39.00  | 16/16                 | 12.13 x 10.13 x 6.47 [308 x 257 x 164]  | B-A-F-F-A        | B-A-F-F-A-B     |
| <a href="#">SC121204G</a>                                     | \$37.00  | <a href="#">SC121204GNK</a> | \$37.00  | 16/16                 | 12.13 x 12.13 x 4.47 [308 x 308 x 114]  | B-A-F-F-A-B      | B-A-F-F-A-B     |
| <a href="#">SC121206G</a>                                     | \$43.50  | <a href="#">SC121206GNK</a> | \$43.50  | 16/16                 | 12.13 x 12.13 x 6.47 [308 x 308 x 164]  | B-A-F-F-A-B      | B-A-F-F-A-B     |
| <a href="#">SC121208G</a>                                     | \$46.00  | <a href="#">SC121208GNK</a> | \$46.00  | 16/16                 | 12.00 x 12.13 x 8.13 [305 x 308 x 207]  | B-A-F-F-A-B      | B-A-F-F-A-B     |
| <a href="#">SC121210G</a>                                     | \$49.50  | <a href="#">SC121210GNK</a> | \$49.50  | 16/16                 | 12.00 x 12.13 x 10.13 [305 x 308 x 257] | B-A-F-F-A-B      | B-A-F-F-A-B     |
| <a href="#">SC121212G</a>                                     | \$76.00  | <a href="#">SC121212GNK</a> | \$76.00  | 16/16                 | 12.00 x 12.13 x 12.13 [305 x 308 x 308] | B-A-F-F-A-B      | B-A-F-F-A-B     |
| <a href="#">SC121504G</a>                                     | \$43.00  | <a href="#">SC121504GNK</a> | \$43.00  | 16/16                 | 15.13 x 12.13 x 4.47 [384 x 308 x 114]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121506G</a>                                     | \$50.00  | <a href="#">SC121506GNK</a> | \$50.00  | 16/16                 | 15.13 x 12.13 x 6.47 [384 x 308 x 164]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121608G</a>                                     | \$62.00  | <a href="#">SC121608GNK</a> | \$62.00  | 16/16                 | 16.00 x 12.13 x 8.13 [406 x 308 x 207]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121804G</a>                                     | \$50.00  | <a href="#">SC121804GNK</a> | \$50.00  | 16/16                 | 18.13 x 12.13 x 4.47 [461 x 308 x 114]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121806G</a>                                     | \$58.00  | <a href="#">SC121806GNK</a> | \$58.00  | 16/16                 | 18.13 x 12.13 x 6.47 [461 x 308 x 164]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121808G</a>                                     | \$61.00  | <a href="#">SC121808GNK</a> | \$61.00  | 16/16                 | 18.00 x 12.13 x 8.13 [457 x 308 x 207]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC121810G</a>                                     | \$81.00  | <a href="#">SC121810GNK</a> | \$81.00  | 16/16                 | 18.00 x 12.13 x 10.13 [457 x 308 x 257] | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC122404G</a>                                     | \$64.00  | <a href="#">SC122404GNK</a> | \$64.00  | 16/16                 | 24.12 x 12.13 x 4.47 [613 x 308 x 114]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC122406G</a>                                     | \$74.00  | <a href="#">SC122406GNK</a> | \$74.00  | 16/16                 | 24.12 x 12.13 x 6.47 [613 x 308 x 164]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC122408G</a>                                     | \$87.00  | <a href="#">SC122408GNK</a> | \$87.00  | 16/16                 | 24.00 x 12.13 x 8.13 [610 x 308 x 207]  | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC122410G</a>                                     | \$74.00  | <a href="#">SC122410GNK</a> | \$74.00  | 16/16                 | 24.00 x 12.13 x 10.13 [610 x 308 x 257] | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC122412G</a>                                     | \$77.00  | <a href="#">SC122412GNK</a> | \$77.00  | 16/16                 | 24.00 x 12.13 x 12.13 [610 x 308 x 308] | B-A-F-F-A-B      | A-B-A-F-F-A-B-A |
| <a href="#">SC151504G</a>                                     | \$52.00  | <a href="#">SC151504GNK</a> | \$52.00  | 16/16                 | 15.13 x 15.13 x 4.47 [384 x 384 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC151506G</a>                                     | \$58.00  | <a href="#">SC151506GNK</a> | \$58.00  | 16/16                 | 15.13 x 15.13 x 6.47 [384 x 384 x 164]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC151804G</a>                                     | \$64.00  | <a href="#">SC151804GNK</a> | \$64.00  | 16/16                 | 18.13 x 15.13 x 4.47 [461 x 384 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC151806G</a>                                     | \$67.00  | <a href="#">SC151806GNK</a> | \$67.00  | 16/16                 | 18.13 x 15.13 x 6.47 [461 x 384 x 164]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC181804G</a>                                     | \$67.00  | <a href="#">SC181804GNK</a> | \$67.00  | 16/16                 | 18.13 x 18.13 x 4.47 [461 x 461 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC181806G</a>                                     | \$78.00  | <a href="#">SC181806GNK</a> | \$78.00  | 16/16                 | 18.13 x 18.13 x 6.47 [461 x 461 x 164]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC181808G</a>                                     | \$87.00  | <a href="#">SC181808GNK</a> | \$87.00  | 16/16                 | 18.00 x 18.13 x 8.13 [457 x 461 x 207]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC181810G</a>                                     | \$113.00 | <a href="#">SC181810GNK</a> | \$113.00 | 16/16                 | 18.00 x 18.13 x 10.13 [457 x 461 x 257] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC181812G</a>                                     | \$97.00  | <a href="#">SC181812GNK</a> | \$97.00  | 16/16                 | 18.00 x 18.13 x 12.13 [457 x 461 x 308] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC182404G</a>                                     | \$103.00 | <a href="#">SC182404GNK</a> | \$103.00 | 16/16                 | 24.12 x 18.13 x 4.47 [613 x 461 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC182406G</a>                                     | \$122.00 | <a href="#">SC182406GNK</a> | \$122.00 | 16/16                 | 24.12 x 18.13 x 6.47 [613 x 461 x 164]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC182408G</a>                                     | \$131.00 | <a href="#">SC182408GNK</a> | \$131.00 | 16/16                 | 24.00 x 18.13 x 8.13 [610 x 461 x 207]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC182410G</a>                                     | \$201.00 | <a href="#">SC182410GNK</a> | \$201.00 | 16/16                 | 24.00 x 18.13 x 10.13 [610 x 461 x 257] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC182412G</a>                                     | \$219.00 | <a href="#">SC182412GNK</a> | \$219.00 | 16/16                 | 24.00 x 18.13 x 12.13 [610 x 461 x 308] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <a href="#">SC183004G</a>                                     | \$127.00 | <a href="#">SC183004GNK</a> | \$127.00 | 16/16                 | 30.12 x 18.13 x 4.47 [765 x 461 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| Notes: Dimensions in inches [millimeters].<br>*Not UL listed. |          |                             |          |                       |                                         |                  |                 |

Table continued on next page

# NEMA 1 Screw Cover Galvanized Steel Wall-Mount



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Table continued from previous page

| NEMA 1 Screw Cover Wall-Mount Galvanized Steel |          |                    |          |                          |                                         |                  |                 |
|------------------------------------------------|----------|--------------------|----------|--------------------------|-----------------------------------------|------------------|-----------------|
| Galvanized                                     |          |                    |          | Body/Door<br>Steel Gauge | Enclosure SizeHxWxD                     | Knockout Pattern |                 |
| With Knockouts                                 | Price    | Without Knockouts  | Price    |                          |                                         | Width Side       | Height Side     |
| <b>SC242404G</b>                               | \$135.00 | <b>SC242404GNK</b> | \$135.00 | 14/14                    | 24.12 x 24.13 x 4.49 [613 x 613 x 114]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC242406G</b>                               | \$157.00 | <b>SC242406GNK</b> | \$157.00 | 14/14                    | 24.12 x 24.13 x 6.49 [613 x 613 x 165]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC242408G</b>                               | \$174.00 | <b>SC242408GNK</b> | \$174.00 | 14/14                    | 24.00 x 24.15 x 8.15 [610 x 613 x 207]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC242410G</b>                               | \$247.00 | <b>SC242410GNK</b> | \$247.00 | 14/14                    | 24.00 x 24.15 x 10.15 [610 x 613 x 258] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC242412G</b>                               | \$268.00 | <b>SC242412GNK</b> | \$268.00 | 14/14                    | 24.00 x 24.15 x 12.15 [610 x 613 x 309] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243006G</b>                               | \$189.00 | <b>SC243006GNK</b> | \$189.00 | 14/14                    | 30.00 x 24.15 x 6.15 [762 x 613 x 156]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243008G</b>                               | \$248.00 | <b>SC243008GNK</b> | \$248.00 | 14/14                    | 30.00 x 24.15 x 8.15 [762 x 613 x 207]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243010G</b>                               | \$293.00 | <b>SC243010GNK</b> | \$293.00 | 14/14                    | 30.00 x 24.15 x 10.15 [762 x 613 x 258] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243012G</b>                               | \$328.00 | <b>SC243012GNK</b> | \$328.00 | 14/14                    | 30.00 x 24.15 x 12.15 [762 x 613 x 309] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243608G</b>                               | \$241.00 | <b>SC243608GNK</b> | \$241.00 | 14/14                    | 36.00 x 24.15 x 8.15 [914 x 613 x 207]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243610G</b>                               | \$333.00 | <b>SC243610GNK</b> | \$333.00 | 14/14                    | 36.00 x 24.15 x 10.15 [914 x 613 x 258] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| <b>SC243612G</b>                               | \$358.00 | <b>SC243612GNK</b> | \$358.00 | 14/14                    | 36.00 x 24.15 x 12.15 [914 x 613 x 309] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303008GNK</b> | \$322.00 | 12/12                    | 30.00 x 30.19 x 8.19 [762 x 767 x 208]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303010GNK</b> | \$381.00 | 12/12                    | 30.00 x 30.19 x 10.19 [762 x 767 x 259] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303012GNK</b> | \$418.00 | 12/12                    | 30.00 x 30.19 x 12.19 [762 x 767 x 310] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303608GNK</b> | \$369.00 | 12/12                    | 36.00 x 30.19 x 8.19 [914 x 767 x 208]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303610GNK</b> | \$382.00 | 12/12                    | 36.00 x 30.19 x 10.19 [914 x 767 x 259] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC303612GNK</b> | \$430.00 | 12/12                    | 36.00 x 30.19 x 12.19 [914 x 767 x 310] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC363608GNK</b> | \$350.00 | 12/12                    | 36.00 x 36.19 x 8.19 [914 x 919 x 208]  | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC363610GNK</b> | \$387.00 | 12/12                    | 36.00 x 36.19 x 10.19 [914 x 919 x 259] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| —                                              | —        | <b>SC363612GNK</b> | \$498.00 | 12/12                    | 36.00 x 36.19 x 12.19 [914 x 919 x 310] | A-B-A-F-F-A-B-A  | A-B-A-F-F-A-B-A |
| Notes: Dimensions in inches [millimeters].     |          |                    |          |                          |                                         |                  |                 |
| *Not UL listed.                                |          |                    |          |                          |                                         |                  |                 |

# NEMA 1 Screw Cover Galvanized Steel Wall-Mount



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## Grounding Kit

| Part Number   | Description   | Price  |
|---------------|---------------|--------|
| <b>WGNDKT</b> | Grounding Kit | \$3.25 |

**Note:** Field grounding kit includes necessary parts to properly ground enclosure..

## Dimensions

