



# Stripping & Crimping Tools

## Overview

Southwire’s cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.

## Features

- MP61**
- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
  - Crimps: insulated and non-insulated terminals/connectors
  - Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws

- S1020SOLUS**
- Strips and cuts up to 10-20 AWG solid and 12-22 AWG stranded wire
  - Double-dipped grip for comfortable fit
  - Serrated nose holds cable for easy twisting and pulling
  - Spring-loaded for self-opening action



S1020SOLUS



MP61

| Cable Shears and Pliers |                                                                                                                                                      |             |         |              |         |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|---------|--------------|---------|
| Part Number             | Description                                                                                                                                          | Tool Length | Qty/Pkg | Weight (lbs) | Price   |
| MP61                    | Southwire multi-purpose crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors. | 9in         | 1       | 0.49         | \$22.00 |
| S1020SOLUS              | Southwire multi-purpose cutting and stripping tool, beveled cutting edges, 22-10 AWG capacity.                                                       | 6in         | 1       | 0.31         | \$12.50 |