

# **Wera** Screwdrivers

## Insulated Screwdrivers

As with all other Wera tools, safety is a top priority for series 100 VDE screwdrivers. All Wera insulated screwdrivers are individually tested at 10,000V, in accordance with IEC 60900, ensuring safe working up to 1,000V. The quality of the blades exceeds current standards with respect to hardness and torque strength.



| Insulated Screwdrivers              |                                                                                     |                                                                                             |          |                   |                  |                   |               |                 |         |
|-------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|----------|-------------------|------------------|-------------------|---------------|-----------------|---------|
| Part Number                         | Part Image                                                                          | Type                                                                                        | Tip Size | Overall Length    | Shaft Length     | Shaft Diameter    | Reduced Shank | Handle Length   | Price   |
| <a href="#"><u>05006440055*</u></a> |    |  Slotted | 3.5mm    | 7.1in<br>(180mm)  | 3.9in<br>(100mm) | 0.14in<br>(3.5mm) | Yes           | 3.2in<br>(81mm) | \$9.00  |
| <a href="#"><u>05006441055*</u></a> |   |                                                                                             | 4.0mm    | 7.8in<br>(198mm)  |                  | 0.20in<br>(5.1mm) |               | 3.9in<br>(99mm) | \$10.00 |
| <a href="#"><u>05006442055*</u></a> |  |                                                                                             | 5.5mm    | 8.8in<br>(223mm)  | 4.9in<br>(125mm) | 0.24in<br>(6.1mm) |               |                 | \$11.00 |
| <a href="#"><u>TW-SD-VSL-1</u></a>  |  |                                                                                             | 2.5mm    | 8.7in<br>(220mm)  | 3.1in<br>(80mm)  | 0.20in<br>(5.1mm) | No            | 3.2in<br>(81mm) | \$6.00  |
| <a href="#"><u>TW-SD-VSL-2</u></a>  |  |                                                                                             | 3.0mm    | 9.4in<br>(240mm)  | 3.9in<br>(100mm) | 0.12in<br>(3.0mm) |               |                 | \$6.00  |
| <a href="#"><u>TW-SD-VSL-3</u></a>  |  |                                                                                             | 4.0mm    | 10.0in<br>(255mm) |                  | 0.24in<br>(6.1mm) |               | 3.9in<br>(99mm) | \$7.00  |
| <a href="#"><u>TW-SD-VSL-4</u></a>  |  |                                                                                             | 5.5mm    | 11.0in<br>(280mm) | 4.9in<br>(125mm) | 0.22in<br>(5.6mm) |               |                 | \$9.00  |

\*Does not have a Lasertip laser-etched non-slip tip.



| Insulated Screwdrivers - Cont'd     |                                                                                   |            |          |                  |                  |                   |               |                  |         |
|-------------------------------------|-----------------------------------------------------------------------------------|------------|----------|------------------|------------------|-------------------|---------------|------------------|---------|
| Part Number                         | Part Image                                                                        | Type       | Tip Size | Overall Length   | Shaft Length     | Shaft Diameter    | Reduced Shank | Handle Length    | Price   |
| <a href="#"><u>05006450055*</u></a> |  | + Phillips | #1       | 7.0in<br>(177mm) | 3.1in<br>(80mm)  | 0.16in<br>(4.0mm) | Yes           | 3.9in<br>(99mm)  | \$10.00 |
| <a href="#"><u>05006451055*</u></a> |  |            | #2       | 8.1in<br>(205mm) | 3.9in<br>(100mm) | 0.24in<br>(6.1mm) |               | 4.1in<br>(104mm) | \$13.00 |
| <a href="#"><u>TW-SD-VPH-1*</u></a> |  |            | #1       | 9.3in<br>(236mm) | 3.1in<br>(80mm)  | 0.16in<br>(4.0mm) |               | 3.2in<br>(81mm)  | \$8.00  |
| <a href="#"><u>TW-SD-VPH-2</u></a>  |  |            | #2       | 8.1in<br>(205mm) | 3.9in<br>(100mm) | 0.24in<br>(6.1mm) | No            | 4.1in<br>(104mm) | \$10.00 |

\*Does not have a Lasertip laser-etched non-slip tip.

| Insulated Screwdriver Sets         |                  |                                                                                     |            |                                  |                                                                                                                        |         |
|------------------------------------|------------------|-------------------------------------------------------------------------------------|------------|----------------------------------|------------------------------------------------------------------------------------------------------------------------|---------|
| Part Number                        | Number of Pieces | Part Image                                                                          | Type       | Tip Size                         | Set Includes                                                                                                           | Price   |
| <a href="#"><u>TW-SD-SET-2</u></a> | 6                |  | + Phillips | #1<br>#2                         | (4) insulated slotted screwdrivers (2.5, 3.5, 4, 5.5mm), (2) insulated Phillips screwdrivers (#1, #2), wall mount rack | \$39.00 |
|                                    |                  |                                                                                     | — Slotted  | 2.5mm<br>3.5mm<br>4.0mm<br>5.5mm |                                                                                                                        |         |