



Wera Screwdrivers

Medium Ratcheting Multi-Bit Screwdrivers

Wera's Rapidaptor ratcheting multi-bit screwdrivers feature a packed bitholding screwdriver built into a small footprint. The driver's Rapidaptor quick-release chuck allows lightning-fast bit changes without any extra tools. The ratchet mechanism with fine toothing is integrated in the handle (36 teeth/return angle 10°). This innovative function eases and accelerates screwdriving without having to reposition the tool, boasting three positions (clockwise/counterclockwise/no ratcheting).



Directional Ratchet Switch



Take-it-Easy Tool Finder

Medium Ratcheting Rapidaptor Multi-Bit Screwdrivers

Part Number	Number of Pieces	Part Image	Type	Bit Size	Overall Length	Handle Type	Set Includes	Price
05051493001	1		n/a		4.8in (122mm)	Kraftform ergonomic handle	Handle only	\$34.00
05051061001	15		 Phillips	#1, #2, #3			(1) Kraftform Kompakt Rapidaptor bit holding ratcheting screwdriver, (14) 3.5in standard bits (Phillips: #1, #2, #3 Pozidriv: #1, #2, #3, torx: T10, T15, T20, T25, hex: 3mm, 4mm, 5mm, slotted: 5.5mm), (1) robust textile pouch, (1) hook and loop fastener strip for storage	\$86.00
			 Slotted	5.5mm				
			 External Hex	3mm, 4mm, 5mm				
			 Torx	T10, T15, T20, T25				
			 Pozidriv	#1, #2, #3				
05051066001	15		 Phillips	#1, #2, #3	(1) Kraftform Kompakt Rapidaptor bit holding ratcheting screwdriver, (14) 3.5in standard bits (Phillips: #1, #2, #3, torx: T10, T15, T20, T25, hex: 1/8in, 5/32in, 3/16in, square: #1, #2, #3, slotted: 5.5mm), (1) robust textile pouch, (1) hook and loop fastener strip for storage	\$86.00		
			 Slotted	5.5mm				
			 External Hex	1/8in, 5/32in, 3/16in				
			 Torx	T10, T15, T20, T25				
			 Square	#1, #2, #3				

—

 Slotted

⬢

 External Hex

⬢

 Torx

⬢

 Square

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.